

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1315067

Luminaire Tested: LDSQA3D02R129735DE010 3LSQPHR1MMS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1315067
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-24)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LDSQA3D02R129735DE010 3LSQPHR1MMS
Description: 3in Adjustable LED luminaire with, R12 optic, 3500K CCT AND, 97CRI , 3LSQPHR1MMS TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 291.0 lumens
Efficiency: N/A
Efficacy: 78.6 lumens/watt
Spacing Criteria (0/90/45): 0.22 / 0.22 / 0.22
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1315067
CATALOG NUMBER: LDSQA3D02R129735DE010 3LSQPHR1MMS

Luminous Intensity Polar Plot





TEST NUMBER: P1315067
 CATALOG NUMBER: LDSQA3D02R129735DE010 3LSQPHR1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20		
RC	80				70				50				30				10		0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10		0
RCR																			
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102		100
1	116	114	113	111	114	112	111	109	108	107	106	104	104	103	101	101	100		98
2	113	110	108	106	111	108	106	104	105	104	102	103	101	100	100	99	98		97
3	110	107	104	102	109	105	103	101	103	101	99	101	99	98	99	98	96		95
4	108	104	101	98	107	103	100	98	101	99	97	99	97	96	98	96	95		94
5	106	102	98	96	105	101	98	96	99	97	95	98	96	94	97	95	93		92
6	104	99	96	94	103	99	96	94	98	95	93	96	94	93	95	93	92		91
7	102	98	94	92	101	97	94	92	96	93	92	95	93	91	94	92	91		90
8	101	96	93	91	100	95	93	90	95	92	90	94	92	90	93	91	90		89
9	99	94	91	89	98	94	91	89	93	91	89	93	90	89	92	90	88		88
10	98	93	90	88	97	93	90	88	92	90	88	91	89	88	91	89	87		87

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	738336
5°	477064
10°	134605
15°	38067
20°	15908
25°	7050
30°	3599
35°	1892
40°	809
45°	219
50°	241
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 50°
 Luminance: 241 cd/sqm



TEST NUMBER: P1315067

CATALOG NUMBER: LDSQA3D02R129735DE010 3LSQPHR1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	194.4	66.8
10°-20°	70.5	24.2
20°-30°	18.9	6.5
30°-40°	5.9	2.0
40°-50°	1.1	0.4
50°-60°	0.1	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	283.9	97.5
0°-40°	289.8	99.6
0°-60°	291.0	100.0
0°-90°	291.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	291.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4287	
5°	2760	194
15°	214	71
25°	37	19
35°	9	6
45°	1	1
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1315067

CATALOG NUMBER: LDSQA3D02R129735DE010 3LSQPHR1MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	4287.1
1°	4214.8
2°	4011.3
3°	3663.0
4°	3230.7
5°	2759.5
6°	2268.4
7°	1828.8
8°	1407.3
9°	1047.4
10°	769.7
11°	567.1
12°	426.9
13°	331.0
14°	262.3
15°	213.5
17.5°	135.7
20°	86.8
22.5°	56.1
25°	37.1
27.5°	25.3
30°	18.1
32.5°	12.7
35°	9.0
37.5°	6.3
40°	3.6
42.5°	1.8
45°	0.9
47.5°	0.9
50°	0.9
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0



TEST NUMBER: P1315067
CATALOG NUMBER: LDSQA3D02R129735DE010 3LSQPHR1MMS

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)