

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1315110

Luminaire Tested: LDSQA3D02R259735DE010 3LSQCDR1MMS

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1315110
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-23)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LDSQA3D02R259735DE010 3LSQCDR1MMS
Description: 3in Adjustable LED luminaire with, R25 optic, 3500K CCT AND, 97CRI , 3LSQCDR1MMS TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 296.0 lumens
Efficiency: N/A
Efficacy: 82.2 lumens/watt
Spacing Criteria (0/90/45): 0.44 / 0.45 / 0.41
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1315110
CATALOG NUMBER: LDSQA3D02R259735DE010 3LSQCDR1MMS

Luminous Intensity Polar Plot



0% Up
100% Dn

— 0°-180° - - 45°-225° - · - · 90°-270°



TEST NUMBER: P1315110
 CATALOG NUMBER: LDSQA3D02R259735DE010 3LSQCDR1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	99	99
1	115	113	111	110	113	111	110	108	107	106	105	103	103	102	100	99	99	97	97	97
2	112	108	105	103	110	107	104	102	104	102	100	101	99	98	98	97	96	94	94	94
3	108	104	101	98	107	103	100	97	100	98	96	98	96	94	96	94	93	92	92	92
4	105	100	97	94	104	99	96	93	97	95	92	96	93	91	94	92	90	89	89	89
5	103	97	93	90	101	96	93	90	95	92	89	93	91	89	92	90	88	87	87	87
6	100	94	90	87	99	93	90	87	92	89	87	91	88	86	90	87	85	84	84	84
7	97	91	87	85	96	91	87	84	90	86	84	89	86	84	88	85	83	82	82	82
8	95	89	85	82	94	88	85	82	87	84	82	87	84	82	86	83	81	80	80	80
9	93	86	83	80	92	86	82	80	85	82	80	85	82	80	84	81	79	78	78	78
10	91	84	81	78	90	84	80	78	83	80	78	83	80	78	82	79	77	77	77	77

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	244901	244901	244901
5°	225817	226335	226802
10°	175334	175964	176926
15°	86653	90290	90326
20°	29177	31139	29764
25°	12086	13416	12428
30°	4733	5966	4793
35°	1240	2439	1282
40°	450	967	450
45°	49	268	49
50°	0	54	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°
 Vertical Angle: 45°
 Luminance: 268 cd/sqm



TEST NUMBER: P1315110

CATALOG NUMBER: LDSQA3D02R259735DE010 3LSQCDR1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	115.2	38.9
10°-20°	139.4	47.1
20°-30°	34.0	11.5
30°-40°	6.6	2.2
40°-50°	0.7	0.3
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	288.6	97.5
0°-40°	295.2	99.7
0°-60°	296.0	100.0
0°-90°	296.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	296.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1422	1422	1422	1422	1422	
5°	1306	1308	1309	1315	1312	115
15°	486	498	506	511	507	137
25°	64	67	71	68	65	32
35°	6	8	12	8	6	5
45°	0	1	1	1	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P1315110
 CATALOG NUMBER: LDSQA3D02R259735DE010 3LSQCDR1MMS

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1422.0	1422.0	1422.0	1422.0	1422.0
1°	1416.6	1417.5	1417.7	1419.1	1416.4
2°	1403.6	1403.9	1404.5	1407.3	1404.8
3°	1379.8	1381.4	1381.6	1385.2	1385.9
4°	1347.3	1348.2	1350.0	1356.2	1350.7
5°	1306.2	1308.0	1309.2	1314.8	1311.9
6°	1255.3	1255.8	1258.3	1264.9	1260.8
7°	1203.6	1203.3	1203.6	1208.8	1207.7
8°	1141.1	1140.0	1143.6	1150.0	1154.3
9°	1075.9	1077.5	1079.8	1085.9	1080.9
10°	1002.6	1006.9	1006.2	1006.7	1011.7
11°	918.1	919.5	919.7	924.5	923.8
12°	818.9	818.9	826.4	834.1	831.6
13°	718.7	725.8	720.8	722.4	732.4
14°	602.0	607.5	614.3	620.6	615.6
15°	486.0	497.6	506.4	511.4	506.6
17.5°	278.4	282.3	289.8	290.7	287.7
20°	159.2	164.0	169.9	168.0	162.4
22.5°	100.1	101.5	107.4	104.5	103.1
25°	63.6	67.0	70.6	67.7	65.4
27.5°	39.5	41.8	45.6	42.5	40.0
30°	23.8	25.9	30.0	25.7	24.1
32.5°	12.5	15.4	18.8	15.7	12.5
35°	5.9	8.4	11.6	8.4	6.1
37.5°	3.6	4.5	7.0	4.5	3.6
40°	2.0	3.0	4.3	3.0	2.0
42.5°	0.9	1.6	2.0	1.6	1.1
45°	0.2	0.7	1.1	0.7	0.2
47.5°	0.0	0.0	0.7	0.2	0.0
50°	0.0	0.0	0.2	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1315110
CATALOG NUMBER: LDSQA3D02R259735DE010 3LSQCDR1MMS

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)