

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1314864

Luminaire Tested: LDSQA3D17R609730DE010 3LSQCDR1MMS

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1314864
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-29)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LDSQA3D17R609730DE010 3LSQCDR1MMS
Description: 3in Adjustable LED luminaire with, R60 optic, 3000K CCT AND, 97CRI , 3LSQCDR1MMS TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1448.0 lumens
Efficiency: N/A
Efficacy: 68.3 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.93 / 0.9
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1314864
CATALOG NUMBER: LDSQA3D17R609730DE010 3LSQCDR1MMS

Luminous Intensity Polar Plot



— 0°-180° - - - 45°-225° - - - 90°-270°



TEST NUMBER: P1314864

CATALOG NUMBER: LDSQA3D17R609730DE010 3LSQCDR1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	96	96	96	94
2	108	104	100	97	106	102	98	95	99	96	93	96	93	91	93	91	89	89	89	89	88
3	103	97	92	88	101	96	91	88	93	89	86	91	88	85	88	86	84	84	84	84	82
4	98	91	86	81	96	90	85	81	88	83	80	86	82	79	84	81	78	78	78	78	77
5	93	85	80	76	92	84	79	75	83	78	75	81	77	74	79	76	73	73	73	73	72
6	89	80	74	70	87	79	74	70	78	73	70	77	72	69	75	72	69	69	69	69	67
7	85	76	70	66	83	75	69	65	74	69	65	72	68	65	71	67	64	64	64	64	63
8	81	71	66	62	79	71	65	61	70	65	61	69	64	61	68	64	61	61	61	61	59
9	77	67	62	58	76	67	61	58	66	61	57	65	61	57	64	60	57	57	57	57	56
10	73	64	58	54	72	63	58	54	63	58	54	62	57	54	61	57	54	54	54	54	53

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	281412	281412	281412
5°	266513	267913	268311
10°	276659	276257	277866
15°	281247	280837	282888
20°	248888	248888	249310
25°	213286	206920	208687
30°	170627	164422	166948
35°	105858	108045	105606
40°	46470	51147	47774
45°	560	16586	1413
50°	0	1849	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°
 Vertical Angle: 45°
 Luminance: 16586 cd/sqm



TEST NUMBER: P1314864

CATALOG NUMBER: LDSQA3D17R609730DE010 3LSQCDR1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	149.2	10.3
10°-20°	432.6	29.9
20°-30°	502.2	34.7
30°-40°	316.3	21.8
40°-50°	47.5	3.3
50°-60°	0.2	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1084.0	74.9
0°-40°	1400.3	96.7
0°-60°	1448.0	100.0
0°-90°	1448.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1448.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1634	1634	1634	1634	1634	
5°	1542	1547	1550	1553	1552	149
15°	1577	1572	1575	1586	1587	432
25°	1122	1110	1089	1094	1098	510
35°	504	505	514	504	502	314
45°	2	22	68	29	6	31
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P1314864

CATALOG NUMBER: LDSQA3D17R609730DE010 3LSQCDR1MMS

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1634.0	1634.0	1634.0	1634.0	1634.0
1°	1621.3	1625.9	1625.9	1627.0	1625.9
2°	1599.3	1606.2	1606.2	1609.7	1607.4
3°	1577.4	1583.2	1584.3	1588.9	1587.8
4°	1553.1	1562.4	1565.8	1568.1	1567.0
5°	1541.6	1547.4	1549.7	1553.1	1552.0
6°	1537.0	1541.6	1543.9	1547.4	1547.4
7°	1540.4	1543.9	1547.4	1549.7	1547.4
8°	1550.8	1554.3	1554.3	1558.9	1555.4
9°	1565.8	1567.0	1567.0	1572.8	1569.3
10°	1582.0	1579.7	1579.7	1587.8	1588.9
11°	1595.9	1593.5	1592.4	1600.5	1602.8
12°	1603.9	1599.3	1599.3	1609.7	1610.9
13°	1605.1	1599.3	1599.3	1609.7	1613.2
14°	1595.9	1588.9	1590.1	1601.6	1605.1
15°	1577.4	1571.6	1575.1	1585.5	1586.6
17.5°	1489.6	1486.2	1488.5	1495.4	1496.5
20°	1358.0	1355.7	1358.0	1358.0	1360.3
22.5°	1227.5	1221.7	1210.2	1217.1	1218.3
25°	1122.4	1109.7	1088.9	1093.5	1098.2
27.5°	1006.9	990.8	968.8	974.6	975.8
30°	858.0	849.9	826.8	832.6	839.5
32.5°	662.8	684.8	670.9	669.8	670.9
35°	503.5	504.6	513.9	503.5	502.3
37.5°	352.2	353.4	360.3	348.7	349.9
40°	206.7	221.7	227.5	222.9	212.5
42.5°	64.7	114.3	129.3	112.0	71.6
45°	2.3	21.9	68.1	28.9	5.8
47.5°	0.0	1.2	32.3	2.3	0.0
50°	0.0	0.0	6.9	0.0	0.0
52.5°	0.0	0.0	1.2	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1314864
CATALOG NUMBER: LDSQA3D17R609730DE010 3LSQCDR1MMS

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)