

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1314911

Luminaire Tested: LDSQA3D20R159730D010 3LSQPHRLP1MW

Issue Date: 1/29/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1314911  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-11)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LDSQA3D20R159730D010 3LSQPHRLP1MW  
Description: 3in Adjustable LED luminaire with, R15 optic, 3000K CCT AND, 97CRI , 3LSQPHRLP1MW TRIM  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 836.0 lumens  
Efficiency: N/A  
Efficacy: 29.0 lumens/watt  
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.63  
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 28.8  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1314911  
CATALOG NUMBER: LDSQA3D20R159730D010 3LSQPHRLP1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P1314911

CATALOG NUMBER: LDSQA3D20R159730D010 3LSQPHRLP1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	111	108	104	101	109	105	102	100	101	99	96	97	95	94	94	92	91	91	91	91	89
2	104	98	93	88	102	96	91	87	93	89	85	90	86	83	87	84	82	82	82	82	80
3	98	90	84	79	96	88	83	78	86	81	77	83	79	76	81	77	74	74	74	74	73
4	92	83	76	71	90	82	76	71	80	74	70	77	73	69	75	71	68	68	68	68	66
5	87	77	70	65	85	76	70	65	74	69	64	72	68	64	71	67	63	63	63	63	61
6	82	72	65	60	81	71	65	60	70	64	60	68	63	59	67	62	59	59	59	59	57
7	78	68	61	56	77	67	60	56	66	60	56	64	59	55	63	58	55	55	55	55	53
8	74	64	57	52	73	63	57	52	62	56	52	61	56	52	60	55	52	52	52	52	50
9	71	60	54	49	70	60	53	49	59	53	49	58	53	49	57	52	49	49	49	49	47
10	68	57	51	47	67	57	51	47	56	50	46	55	50	46	54	49	46	46	46	46	45

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	214779	214779	214779
5°	201717	201976	201976
10°	170385	169860	170910
15°	134009	132119	134276
20°	104137	99427	102744
25°	78614	73141	77455
30°	58466	53336	57253
35°	41734	38874	41103
40°	28282	28620	27945
45°	21044	22140	21044
50°	18273	18273	18273
55°	17745	16845	17745
60°	18256	16706	17739
65°	19764	17279	19764
70°	23667	17574	23667
75°	30276	18166	30276
80°	37589	19538	36101
85°	30036	17982	33000

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 80°  
 Luminance: 37589 cd/sqm



TEST NUMBER: P1314911

CATALOG NUMBER: LDSQA3D20R159730D010 3LSQPHRLP1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	105.2	12.6
10°-20°	207.9	24.9
20°-30°	183.8	22.0
30°-40°	120.7	14.4
40°-50°	70.6	8.4
50°-60°	51.9	6.2
60°-70°	44.3	5.3
70°-80°	36.5	4.4
80°-90°	15.1	1.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	496.9	59.4
0°-40°	617.6	73.9
0°-60°	740.1	88.5
0°-90°	836.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	836.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1247	1247	1247	1247	1247	
5°	1167	1167	1168	1170	1168	105
15°	752	752	741	750	753	210
25°	414	400	385	396	408	191
35°	198	191	185	189	196	125
45°	86	88	91	88	86	70
55°	59	58	56	58	59	53
65°	48	44	42	44	48	48
75°	46	33	27	35	46	46
85°	15	17	9	15	17	17
90°	0	0	0	0	0	



TEST NUMBER: P1314911  
 CATALOG NUMBER: LDSQA3D20R159730D010 3LSQPHRLP1MW

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1247.1	1247.1	1247.1	1247.1	1247.1
1°	1242.5	1244.0	1244.0	1245.5	1245.5
2°	1230.4	1233.4	1234.9	1234.9	1234.9
3°	1215.2	1216.8	1218.3	1219.8	1219.8
4°	1194.0	1195.5	1195.5	1198.6	1200.1
5°	1166.8	1166.8	1168.3	1169.8	1168.3
6°	1134.9	1134.9	1136.4	1136.4	1136.4
7°	1097.0	1098.6	1100.1	1101.6	1100.1
8°	1056.1	1057.7	1062.2	1062.2	1060.7
9°	1015.2	1016.7	1016.7	1021.3	1021.3
10°	974.3	974.3	971.3	974.3	977.3
12.5°	863.7	862.2	857.6	862.2	865.2
15°	751.6	751.6	741.0	750.1	753.1
17.5°	660.7	647.0	636.4	645.5	653.1
20°	568.2	554.6	542.5	551.6	560.6
22.5°	484.9	474.3	459.1	468.2	478.8
25°	413.7	400.0	384.9	395.5	407.6
27.5°	354.6	336.4	321.2	333.4	344.0
30°	294.0	281.8	268.2	277.3	287.9
32.5°	242.4	233.4	222.7	230.3	239.4
35°	198.5	190.9	184.9	189.4	195.5
37.5°	159.1	156.1	153.0	154.6	154.6
40°	125.8	127.3	127.3	127.3	124.3
42.5°	103.0	104.6	107.6	104.6	103.0
45°	86.4	87.9	90.9	87.9	86.4
47.5°	75.8	77.3	78.8	75.8	75.8
50°	68.2	68.2	68.2	68.2	68.2
52.5°	63.6	62.1	62.1	62.1	63.6
55°	59.1	57.6	56.1	57.6	59.1
57.5°	54.5	53.0	51.5	53.0	54.5
60°	53.0	50.0	48.5	50.0	51.5
62.5°	50.0	47.0	45.5	47.0	50.0
65°	48.5	43.9	42.4	43.9	48.5
67.5°	47.0	40.9	37.9	40.9	47.0
70°	47.0	37.9	34.9	39.4	47.0
72.5°	45.5	36.4	30.3	36.4	45.5
75°	45.5	33.3	27.3	34.9	45.5
77.5°	42.4	30.3	22.7	31.8	42.4
80°	37.9	27.3	19.7	28.8	36.4
82.5°	27.3	22.7	15.2	22.7	27.3
85°	15.2	16.7	9.1	15.2	16.7
87.5°	1.5	4.5	3.0	9.1	7.6
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)