

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1315168

Luminaire Tested: LDSQA3D02R459735DE010 3LSQCA45R 1MW

Issue Date: 1/29/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1315168  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-84)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LDSQA3D02R459735DE010 3LSQCA45R 1MW  
Description: 3in Adjustable LED luminaire with, R45 optic, 3500K CCT AND, 97CRI , 3LSQCA45R 1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 275.0 lumens  
Efficiency: N/A  
Efficacy: 76.4 lumens/watt  
Spacing Criteria (0/90/45): 3.81 / 0.82 / 1.83  
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 3.6  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1315168  
CATALOG NUMBER: LDSQA3D02R459735DE010 3LSQCA45R 1MW

### Luminous Intensity Polar Plot



— 0°-180°    - - - 45°-225°    ····· 90°-270°



TEST NUMBER: P1315168

CATALOG NUMBER: LDSQA3D02R459735DE010 3LSQCA45R 1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	110	106	102	99	107	104	100	97	99	97	94	96	93	91	92	90	88	88	88	88	86
2	100	93	86	81	98	91	85	80	87	83	78	84	80	77	81	78	75	75	75	75	73
3	91	81	73	67	89	80	72	66	77	70	65	74	69	64	71	67	63	63	63	63	61
4	83	71	62	56	81	70	62	55	67	60	55	65	59	54	63	58	53	53	53	53	51
5	76	63	53	47	73	61	53	46	59	52	46	57	51	45	55	50	45	45	45	45	43
6	69	55	46	39	67	54	46	39	52	45	39	51	44	39	49	43	38	38	38	38	36
7	63	49	40	34	61	48	40	33	47	39	33	45	38	33	44	37	33	33	33	33	31
8	58	44	35	29	56	43	35	29	42	34	29	40	33	28	39	33	28	28	28	28	26
9	53	39	31	25	52	39	30	25	38	30	25	36	29	25	35	29	24	24	24	24	22
10	49	36	27	22	48	35	27	22	34	27	21	33	26	21	32	26	21	21	21	21	19

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°	135°	180°
0°	2738	2738	2738	2738	2738
5°	3267	3025	2714	2507	2507
10°	5211	3533	2536	2378	2378
15°	12962	4743	2318	2229	2318
20°	34144	7074	1998	2126	2254
25°	68562	10489	1729	1995	2204
30°	101083	14060	1392	1949	2267
35°	127514	16483	1198	1913	2334
40°	136039	16659	1079	2001	2496
45°	141338	13883	999	2168	2704
50°	141119	9672	965	2304	3054
55°	119954	4294	1021	2582	3333
60°	80600	861	1033	2893	3823
65°	21394	367	1019	3138	4360
70°	554	453	1007	3424	4935
75°	466	466	1065	3660	5590
80°	496	694	1091	3868	6347
85°	395	988	1778	3952	6323

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 10°  
 Vertical Angle: 47.5°  
 Luminance: 144974 cd/sqm



TEST NUMBER: P1315168

CATALOG NUMBER: LDSQA3D02R459735DE010 3LSQCA45R 1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	1.6	0.6
10°-20°	7.8	2.8
20°-30°	32.0	11.6
30°-40°	67.4	24.5
40°-50°	83.2	30.2
50°-60°	62.3	22.7
60°-70°	16.0	5.8
70°-80°	3.3	1.2
80°-90°	1.4	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	41.3	15.0
0°-40°	108.8	39.5
0°-60°	254.3	92.5
0°-90°	275.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	275.0	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	16	16	16	16	16	
5°	19	18	16	14	14	2
15°	73	27	13	12	13	27
25°	361	55	9	10	12	168
35°	606	78	6	9	11	370
45°	580	57	4	9	11	444
55°	400	14	3	9	11	345
65°	52	1	2	8	11	76
75°	1	1	2	6	8	1
85°	0	0	1	2	3	0
90°	0	0	0	0	0	



TEST NUMBER: P1315168

CATALOG NUMBER: LDSQA3D02R459735DE010 3LSQCA45R 1MW

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	45°	67.5°	90°	112.5°
0°	15.9	15.9	15.9	15.9	15.9	15.9	15.9	15.9	15.9	15.9	15.9
2.5°	16.8	16.8	16.8	16.8	16.8	16.8	16.8	16.6	16.4	15.9	15.5
5°	18.9	18.6	18.6	18.6	18.4	18.2	18.2	17.5	16.6	15.7	15.0
7.5°	22.3	22.3	22.0	21.6	21.4	20.9	20.5	18.6	16.6	15.2	14.3
10°	29.8	29.3	28.6	28.2	27.0	25.4	24.3	20.2	16.4	14.5	13.9
12.5°	44.5	45.4	43.2	40.9	37.7	34.8	31.1	22.9	16.4	13.9	13.2
15°	72.7	74.3	70.0	65.4	57.7	50.4	43.6	26.6	15.9	13.0	12.3
17.5°	118.8	120.9	113.6	102.9	90.9	76.3	63.9	31.6	15.5	12.0	11.6
20°	186.3	186.1	172.0	158.6	135.4	114.1	90.7	38.6	14.8	10.9	10.9
22.5°	269.3	270.2	252.9	228.8	195.9	161.6	124.3	46.8	13.9	10.0	10.2
25°	360.8	353.1	332.7	303.3	261.3	213.8	164.7	55.2	13.0	9.1	9.5
27.5°	437.2	429.7	406.3	371.5	326.3	269.9	205.9	63.6	11.8	8.2	8.9
30°	508.3	498.8	470.6	431.3	377.4	316.5	244.5	70.7	10.5	7.0	8.2
32.5°	566.9	558.3	526.3	480.6	422.0	356.5	277.2	76.1	9.1	6.4	7.7
35°	606.5	597.6	568.1	517.8	454.0	385.6	303.8	78.4	8.0	5.7	7.5
37.5°	615.6	610.8	589.7	542.6	476.0	404.2	320.8	77.7	6.6	5.2	7.0
40°	605.1	606.2	596.2	557.2	487.9	412.2	327.9	74.1	5.5	4.8	6.8
42.5°	591.7	594.7	594.0	563.1	492.9	412.6	324.9	66.8	4.3	4.3	6.6
45°	580.3	583.3	587.4	560.6	489.4	406.7	315.6	57.0	3.2	4.1	6.6
47.5°	559.7	562.8	568.7	540.6	472.2	391.5	298.8	46.4	2.3	3.9	6.4
50°	526.7	528.3	526.7	495.1	439.0	367.0	271.5	36.1	1.6	3.6	6.4
52.5°	492.9	489.7	476.5	436.5	386.3	328.1	237.2	25.7	1.1	3.4	6.1
55°	399.5	394.5	384.7	360.2	331.5	280.4	191.8	14.3	1.1	3.4	5.9
57.5°	278.4	281.1	284.5	279.5	266.3	220.9	145.7	6.4	1.1	3.2	5.9
60°	234.0	231.8	232.0	228.8	207.0	161.1	100.2	2.5	1.1	3.0	5.7
62.5°	139.7	141.3	144.3	145.0	123.4	90.0	52.5	1.1	1.1	2.7	5.5
65°	52.5	55.0	48.2	41.8	33.2	24.3	12.3	0.9	1.4	2.5	5.0
67.5°	1.6	1.8	2.3	2.0	2.0	1.8	1.4	0.9	1.4	2.3	4.8
70°	1.1	1.1	1.1	1.1	1.1	0.9	0.9	0.9	1.1	2.0	4.3
72.5°	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	1.1	1.8	3.9
75°	0.7	0.9	0.7	0.7	0.7	0.7	0.7	0.7	1.1	1.6	3.2
77.5°	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.9	1.4	2.7
80°	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.7	0.9	1.1	2.3
82.5°	0.5	0.5	0.5	0.2	0.5	0.5	0.5	0.5	0.9	0.9	1.8
85°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.5	0.7	0.9	1.1
87.5°	0.0	0.0	0.0	0.0	0.2	0.2	0.2	0.5	0.7	0.7	0.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1315168

CATALOG NUMBER: LDSQA3D02R459735DE010 3LSQCA45R 1MW

**CANDELA DISTRIBUTION (continued):**

	135°	157.5°	180°
0°	15.9	15.9	15.9
2.5°	15.0	15.0	15.0
5°	14.5	14.5	14.5
7.5°	14.1	14.1	14.1
10°	13.6	13.6	13.6
12.5°	13.2	13.2	13.4
15°	12.5	13.0	13.0
17.5°	12.0	12.5	12.7
20°	11.6	12.0	12.3
22.5°	10.9	11.6	12.0
25°	10.5	11.4	11.6
27.5°	10.0	11.1	11.6
30°	9.8	10.9	11.4
32.5°	9.3	10.7	11.1
35°	9.1	10.7	11.1
37.5°	9.1	10.5	11.1
40°	8.9	10.5	11.1
42.5°	8.9	10.5	11.1
45°	8.9	10.5	11.1
47.5°	8.6	10.5	11.4
50°	8.6	10.7	11.4
52.5°	8.6	10.7	11.4
55°	8.6	10.7	11.1
57.5°	8.4	10.5	11.1
60°	8.4	10.5	11.1
62.5°	8.0	10.2	10.9
65°	7.7	10.0	10.7
67.5°	7.3	9.8	10.2
70°	6.8	9.1	9.8
72.5°	6.1	8.6	9.3
75°	5.5	8.0	8.4
77.5°	4.8	7.0	7.5
80°	3.9	5.9	6.4
82.5°	3.0	4.5	4.8
85°	2.0	3.0	3.2
87.5°	0.9	1.4	1.6
90°	0.0	0.0	0.0

(END OF REPORT)