

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1315547

Luminaire Tested: LDSQA3D10R129735DE010 3LSQCDR1MMS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1315547
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-24)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LDSQA3D10R129735DE010 3LSQCDR1MMS
Description: 3in Adjustable LED luminaire with, R12 optic, 3500K CCT AND, 97CRI , 3LSQCDR1MMS TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 822.0 lumens
Efficiency: N/A
Efficacy: 70.3 lumens/watt
Spacing Criteria (0/90/45): 0.22 / 0.22 / 0.22
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1315547

CATALOG NUMBER: LDSQA3D10R129735DE010 3LSQCDR1MMS

Luminous Intensity Polar Plot



TEST NUMBER: P1315547

CATALOG NUMBER: LDSQA3D10R129735DE010 3LSQCDR1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	116	114	113	111		114	112	111	109		108	107	106		104	104	103		101	101	100
2	113	110	108	106		111	108	106	104		105	104	102		103	101	100		100	99	98
3	110	107	104	102		109	105	103	101		103	101	99		101	99	98		99	98	96
4	108	104	101	98		107	103	100	98		101	99	97		99	97	96		98	96	95
5	106	102	98	96		105	101	98	96		99	97	95		98	96	94		97	95	93
6	104	99	96	94		103	99	96	94		98	95	93		96	94	93		95	93	92
7	102	98	94	92		101	97	94	92		96	93	92		95	93	91		94	92	91
8	101	96	93	91		100	95	93	90		95	92	90		94	92	90		93	91	90
9	99	94	91	89		98	94	91	89		93	91	89		93	90	89		92	90	88
10	98	93	90	88		97	93	90	88		92	90	88		91	89	88		91	89	87

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2085616
5°	1347586
10°	380223
15°	107496
20°	44957
25°	19896
30°	10162
35°	5361
40°	2293
45°	633
50°	697
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 50°

Luminance: 697 cd/sqm

TEST NUMBER: P1315547

CATALOG NUMBER: LDSQA3D10R129735DE010 3LSQCDR1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	549.2	66.8
10°-20°	199.2	24.2
20°-30°	53.3	6.5
30°-40°	16.8	2.0
40°-50°	3.2	0.4
50°-60°	0.3	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	801.8	97.5
0°-40°	818.6	99.6
0°-60°	822.0	100.0
0°-90°	822.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	822.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	12110	
5°	7795	549
15°	603	199
25°	105	53
35°	26	17
45°	3	3
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1315547

CATALOG NUMBER: LDSQA3D10R129735DE010 3LSQCDR1MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	12110.0
1°	11905.6
2°	11330.8
3°	10347.2
4°	9125.9
5°	7794.9
6°	6407.6
7°	5165.9
8°	3975.4
9°	2958.5
10°	2174.2
11°	1601.9
12°	1205.9
13°	935.1
14°	740.9
15°	602.9
17.5°	383.2
20°	245.3
22.5°	158.4
25°	104.7
27.5°	71.5
30°	51.1
32.5°	35.8
35°	25.5
37.5°	17.9
40°	10.2
42.5°	5.1
45°	2.6
47.5°	2.6
50°	2.6
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0



TEST NUMBER: P1315547

CATALOG NUMBER: LDSQA3D10R129735DE010 3LSQCDR1MMS

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)