

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1315281

Luminaire Tested: LDSQA3D05R259735DE010 3LSQPHR1MMS

Issue Date: 1/29/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1315281  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-3)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LDSQA3D05R259735DE010 3LSQPHR1MMS  
Description: 3in Adjustable LED luminaire with, R25 optic, 3500K CCT AND, 97CRI , 3LSQPHR1MMS TRIM  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 523.0 lumens  
Efficiency: N/A  
Efficacy: 72.6 lumens/watt  
Spacing Criteria (0/90/45): 0.43 / 0.43 / 0.4  
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 7.2  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1315281  
CATALOG NUMBER: LDSQA3D05R259735DE010 3LSQPHR1MMS

### Luminous Intensity Polar Plot



— 0°-180°    - - 45°-225°    - · - · 90°-270°



TEST NUMBER: P1315281

CATALOG NUMBER: LDSQA3D05R259735DE010 3LSQPHR1MMS

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	99	97
1	115	113	112	110	113	111	110	108	107	106	105	104	103	102	100	100	99	97	97	96	95
2	112	109	106	104	110	107	105	103	104	102	101	101	100	98	99	97	96	95	94	94	93
3	109	105	102	99	107	104	101	98	101	99	97	99	97	95	97	95	94	93	92	92	91
4	106	101	98	95	105	100	97	95	99	96	94	97	94	93	95	93	92	91	91	89	88
5	104	98	95	92	102	98	94	92	96	93	91	95	92	90	93	91	89	88	87	87	86
6	101	96	92	89	100	95	92	89	94	91	89	93	90	88	91	89	87	86	86	85	85
7	99	93	89	87	98	93	89	87	92	89	86	91	88	86	90	87	86	85	85	84	83
8	97	91	87	85	96	90	87	85	90	86	84	89	86	84	88	85	84	83	83	82	81
9	95	89	85	83	94	88	85	83	88	85	82	87	84	82	86	84	82	81	81	80	80
10	93	87	83	81	92	86	83	81	86	83	81	85	82	80	85	82	80	80	80	80	80

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	488062	488062	488062
5°	442280	446308	448487
10°	332481	334859	336398
15°	164623	159719	170364
20°	46497	47267	47780
25°	8057	15240	9577
30°	3162	3242	3341
35°	988	1072	1072
40°	315	427	315
45°	219	122	219
50°	134	0	134
55°	150	0	150
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 219 cd/sqm



TEST NUMBER: P1315281

CATALOG NUMBER: LDSQA3D05R259735DE010 3LSQPHR1MMS

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	225.1	43.0
10°-20°	253.9	48.5
20°-30°	39.4	7.5
30°-40°	4.0	0.8
40°-50°	0.5	0.1
50°-60°	0.1	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	518.4	99.1
0°-40°	522.4	99.9
0°-60°	523.0	100.0
0°-90°	523.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	523.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	2834	2834	2834	2834	2834	
5°	2558	2563	2582	2592	2594	223
15°	923	917	896	936	956	253
25°	42	63	80	61	50	36
35°	5	5	5	6	5	4
45°	1	0	0	0	1	1
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P1315281  
 CATALOG NUMBER: LDSQA3D05R259735DE010 3LSQPHR1MMS

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	2833.9	2833.9	2833.9	2833.9	2833.9
1°	2822.2	2826.0	2821.8	2826.4	2826.0
2°	2792.8	2796.6	2791.5	2794.2	2794.2
3°	2732.7	2740.6	2745.3	2748.5	2751.3
4°	2653.4	2662.3	2669.3	2677.7	2677.7
5°	2558.3	2562.9	2581.6	2591.9	2594.2
6°	2445.0	2463.6	2477.6	2498.1	2485.5
7°	2331.6	2347.0	2366.6	2369.9	2378.7
8°	2202.9	2219.3	2237.5	2234.2	2226.7
9°	2046.3	2070.0	2091.5	2084.5	2093.8
10°	1901.2	1915.7	1914.8	1907.8	1923.6
11°	1732.9	1736.1	1718.0	1746.4	1729.2
12°	1533.3	1536.1	1512.8	1540.8	1558.5
13°	1342.1	1335.6	1303.4	1340.2	1362.6
14°	1122.0	1124.3	1083.3	1154.6	1149.0
15°	923.3	916.8	895.8	935.9	955.5
17.5°	492.0	496.2	491.0	511.1	523.7
20°	253.7	260.7	257.9	266.3	260.7
22.5°	131.5	141.3	144.1	137.6	119.8
25°	42.4	63.0	80.2	61.1	50.4
27.5°	25.6	25.2	39.2	27.0	27.5
30°	15.9	15.4	16.3	16.3	16.8
32.5°	8.9	9.3	8.9	9.8	9.3
35°	4.7	5.1	5.1	5.6	5.1
37.5°	2.8	3.3	3.3	3.3	2.8
40°	1.4	1.9	1.9	1.4	1.4
42.5°	0.9	0.9	0.9	0.9	0.9
45°	0.9	0.5	0.5	0.5	0.9
47.5°	0.5	0.5	0.0	0.5	0.5
50°	0.5	0.5	0.0	0.5	0.5
52.5°	0.5	0.0	0.0	0.0	0.5
55°	0.5	0.0	0.0	0.0	0.5
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1315281  
CATALOG NUMBER: LDSQA3D05R259735DE010 3LSQPHR1MMS

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)