

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1315420

Luminaire Tested: LDSQA3D09R209735DE010 3LSQPHR1MB

Issue Date: 1/29/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1315420  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-2)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LDSQA3D09R209735DE010 3LSQPHR1MB  
Description: 3in Adjustable LED luminaire with, R20 optic, 3500K CCT AND, 97CRI , 3LSQPHR1MB TRIM  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 766.0 lumens  
Efficiency: N/A  
Efficacy: 69.0 lumens/watt  
Spacing Criteria (0/90/45): 0.35 / 0.36 / 0.33  
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 11.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1315420  
CATALOG NUMBER: LDSQA3D09R209735DE010 3LSQPHR1MB

### Luminous Intensity Polar Plot





TEST NUMBER: P1315420  
 CATALOG NUMBER: LDSQA3D09R209735DE010 3LSQPHR1MB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	116	114	112	111	113	112	110	109	108	107	106	104	103	102	101	100	100	100	100	100	98
2	113	109	107	105	111	108	106	104	105	103	101	102	101	99	99	98	97	97	98	97	96
3	110	106	103	100	108	105	102	100	102	100	98	100	98	97	98	96	95	95	98	96	94
4	107	103	99	97	106	102	99	96	100	97	95	98	96	94	96	95	93	96	95	93	92
5	105	100	97	94	104	99	96	94	98	95	93	96	94	92	95	93	92	95	93	92	91
6	103	98	94	92	102	97	94	91	96	93	91	95	92	90	93	91	90	93	91	90	89
7	101	95	92	90	100	95	92	89	94	91	89	93	90	89	92	90	88	92	90	88	87
8	99	93	90	88	98	93	90	88	92	89	87	91	89	87	91	88	87	91	88	87	86
9	97	92	88	86	96	91	88	86	91	88	86	90	87	86	89	87	85	89	87	85	85
10	95	90	87	85	95	90	87	85	89	86	84	88	86	84	88	86	84	88	86	84	83

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	982203	982203	982203
5°	848515	856415	859596
10°	510788	515562	541217
15°	176675	172539	186286
20°	46405	43656	43785
25°	10109	12181	13872
30°	4335	4335	4474
35°	2439	2144	2292
40°	1079	1237	1371
45°	341	487	487
50°	188	188	188
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 22.5°  
 Vertical Angle: 45°  
 Luminance: 487 cd/sqm



TEST NUMBER: P1315420

CATALOG NUMBER: LDSQA3D09R209735DE010 3LSQPHR1MB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	407.9	53.3
10°-20°	310.6	40.5
20°-30°	38.4	5.0
30°-40°	7.3	0.9
40°-50°	1.7	0.2
50°-60°	0.1	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	756.9	98.8
0°-40°	764.1	99.8
0°-60°	766.0	100.0
0°-90°	766.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	766.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	5703	5703	5703	5703	5703	
5°	4908	4905	4954	4950	4972	405
15°	991	955	968	1026	1045	310
25°	53	61	64	67	73	37
35°	12	12	10	11	11	7
45°	1	2	2	2	2	1
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P1315420  
 CATALOG NUMBER: LDSQA3D09R209735DE010 3LSQPHR1MB

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	5703.1	5703.1	5703.1	5703.1	5703.1
1°	5676.5	5669.7	5675.1	5663.5	5687.4
2°	5585.7	5578.9	5578.9	5572.1	5575.5
3°	5416.5	5427.4	5420.6	5406.2	5424.7
4°	5185.8	5198.1	5209.0	5209.7	5212.4
5°	4908.1	4904.6	4953.8	4950.4	4972.2
6°	4591.4	4587.3	4608.5	4644.0	4687.6
7°	4243.4	4193.6	4250.2	4321.8	4380.5
8°	3793.0	3805.9	3844.8	3929.5	3976.5
9°	3410.8	3335.1	3417.6	3518.6	3569.8
10°	2920.8	2859.4	2948.1	3054.6	3094.8
12.5°	1838.5	1785.2	1813.9	1925.8	1943.6
15°	990.9	955.4	967.7	1025.7	1044.8
17.5°	505.7	473.6	466.8	503.6	507.7
20°	253.2	245.7	238.2	241.6	238.9
22.5°	117.4	127.6	126.3	119.4	127.6
25°	53.2	60.7	64.1	66.9	73.0
27.5°	32.8	31.4	36.2	38.9	39.6
30°	21.8	21.2	21.8	22.5	22.5
32.5°	15.7	15.0	14.3	14.3	15.0
35°	11.6	11.6	10.2	10.9	10.9
37.5°	8.2	8.2	7.5	8.2	8.2
40°	4.8	5.5	5.5	5.5	6.1
42.5°	2.7	3.4	3.4	3.4	3.4
45°	1.4	2.0	2.0	2.0	2.0
47.5°	0.7	0.7	0.7	1.4	1.4
50°	0.7	0.7	0.7	0.7	0.7
52.5°	0.7	0.0	0.0	0.0	0.7
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)