

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1315513

Luminaire Tested: LDSQA3D09R559735DE010 3LSQCDR1MMS

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1315513
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-28)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LDSQA3D09R559735DE010 3LSQCDR1MMS
Description: 3in Adjustable LED luminaire with, R55 optic, 3500K CCT AND, 97CRI , 3LSQCDR1MMS TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 888.0 lumens
Efficiency: N/A
Efficacy: 80.0 lumens/watt
Spacing Criteria (0/90/45): 0.93 / 0.93 / 0.81
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1315513

CATALOG NUMBER: LDSQA3D09R559735DE010 3LSQCDR1MMS

Luminous Intensity Polar Plot



TEST NUMBER: P1315513

CATALOG NUMBER: LDSQA3D09R559735DE010 3LSQCDR1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	112	109	107	112	109	107	106		105	104	102		102	100	99		98	97	96
2	109	105	101	98	107	103	100	97		100	97	95		97	95	93		94	93	91
3	104	99	94	91	103	97	93	90		95	91	89		92	90	87		90	88	86
4	100	93	88	84	98	92	87	84		90	86	83		88	85	82		86	83	81
5	96	88	83	79	94	87	82	79		85	81	78		84	80	77		82	79	77
6	91	83	78	74	90	83	78	74		81	77	74		80	76	73		79	75	73
7	87	79	74	70	86	79	73	70		77	73	69		76	72	69		75	72	69
8	84	75	70	66	83	75	70	66		74	69	66		73	69	65		72	68	65
9	80	72	66	63	79	71	66	63		70	66	62		69	65	62		69	65	62
10	77	68	63	59	76	68	63	59		67	62	59		66	62	59		66	62	59

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	201156	201156	201156
5°	198864	198277	197222
10°	208439	205938	204504
15°	204971	202778	202065
20°	186703	187454	186831
25°	149779	152116	149779
30°	85970	88137	88813
35°	24515	29539	25229
40°	6295	9038	6430
45°	658	3166	487
50°	0	536	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°

Vertical Angle: 45°

Luminance: 3166 cd/sqm

TEST NUMBER: P1315513

CATALOG NUMBER: LDSQA3D09R559735DE010 3LSQCDR1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	110.9	12.5
10°-20°	316.5	35.6
20°-30°	348.6	39.3
30°-40°	104.1	11.7
40°-50°	8.0	0.9
50°-60°	0.1	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	775.9	87.4
0°-40°	880.0	99.1
0°-60°	888.0	100.0
0°-90°	888.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	888.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1168	1168	1168	1168	1168	
5°	1150	1148	1147	1142	1141	112
15°	1150	1141	1137	1133	1133	319
25°	788	788	800	799	788	345
35°	117	124	140	128	120	96
45°	3	7	13	7	2	5
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	

TEST NUMBER: P1315513

CATALOG NUMBER: LDSQA3D09R559735DE010 3LSQCDR1MMS

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1168.0	1168.0	1168.0	1168.0	1168.0
1°	1167.3	1167.3	1166.0	1165.3	1167.3
2°	1163.9	1163.9	1160.5	1159.8	1161.9
3°	1156.4	1155.8	1153.0	1151.0	1152.3
4°	1150.3	1148.9	1146.9	1143.5	1144.2
5°	1150.3	1148.3	1146.9	1142.1	1140.8
6°	1155.8	1154.4	1151.7	1146.9	1145.5
7°	1165.3	1162.6	1159.8	1153.7	1152.3
8°	1175.5	1173.5	1168.0	1161.9	1159.2
9°	1185.8	1181.0	1174.2	1168.0	1167.3
10°	1191.9	1185.1	1177.6	1170.1	1169.4
11°	1191.2	1185.1	1176.2	1169.4	1168.7
12°	1188.5	1179.6	1172.1	1163.9	1164.6
13°	1178.9	1170.8	1163.3	1157.1	1155.8
14°	1166.0	1158.5	1151.7	1145.5	1146.2
15°	1149.6	1141.4	1137.3	1132.6	1133.3
17.5°	1091.7	1089.6	1091.7	1086.2	1088.2
20°	1018.7	1016.7	1022.8	1020.1	1019.4
22.5°	917.1	919.8	931.4	928.0	921.9
25°	788.2	788.2	800.5	799.1	788.2
27.5°	620.5	625.3	632.8	636.2	628.0
30°	432.3	443.2	443.2	450.0	446.6
32.5°	241.4	264.6	270.0	273.4	259.8
35°	116.6	124.1	140.5	128.2	120.0
37.5°	55.9	59.3	75.7	61.4	57.3
40°	28.0	32.0	40.2	33.4	28.6
42.5°	11.6	17.0	21.1	17.0	11.6
45°	2.7	6.8	13.0	6.8	2.0
47.5°	0.0	0.7	6.1	1.4	0.0
50°	0.0	0.0	2.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1315513

CATALOG NUMBER: LDSQA3D09R559735DE010 3LSQCDR1MMS

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)