

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1315583

Luminaire Tested: LDSQA3D13R209735DE010 3LSQCA30R 1MW

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1315583
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-60)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LDSQA3D13R209735DE010 3LSQCA30R 1MW
Description: 3in Adjustable LED luminaire with, R20 optic, 3500K CCT AND, 97CRI , 3LSQCA30R 1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 997.9 lumens
Efficiency: N/A
Efficacy: 68.4 lumens/watt
Spacing Criteria (0/90/45): 2.3 / 0.53 / 1.19
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1315583
CATALOG NUMBER: LDSQA3D13R209735DE010 3LSQCA30R 1MW

Luminous Intensity Polar Plot



— 0°-180° - - - 45°-225° ····· 90°-270°



TEST NUMBER: P1315583

CATALOG NUMBER: LDSQA3D13R209735DE010 3LSQCA30R 1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | | | | 0 |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | 100 | 100 | 100 |
| 1 | 113 | 109 | 107 | 104 | 110 | 107 | 105 | 102 | 103 | 101 | 99 | 99 | 98 | 96 | 96 | 95 | 93 | 92 | 92 | 92 | 92 |
| 2 | 106 | 100 | 96 | 92 | 104 | 99 | 94 | 91 | 95 | 92 | 89 | 92 | 89 | 87 | 89 | 87 | 85 | 83 | 83 | 83 | 83 |
| 3 | 99 | 92 | 86 | 81 | 97 | 90 | 85 | 81 | 88 | 83 | 79 | 85 | 81 | 78 | 83 | 80 | 77 | 75 | 75 | 75 | 75 |
| 4 | 93 | 84 | 78 | 73 | 91 | 83 | 77 | 72 | 81 | 76 | 71 | 79 | 74 | 71 | 77 | 73 | 70 | 68 | 68 | 68 | 68 |
| 5 | 87 | 77 | 70 | 65 | 85 | 76 | 70 | 65 | 74 | 69 | 64 | 72 | 68 | 64 | 71 | 67 | 63 | 61 | 61 | 61 | 61 |
| 6 | 81 | 71 | 64 | 59 | 80 | 70 | 63 | 58 | 68 | 62 | 58 | 67 | 62 | 58 | 65 | 61 | 57 | 55 | 55 | 55 | 55 |
| 7 | 76 | 65 | 58 | 53 | 74 | 64 | 57 | 53 | 63 | 57 | 52 | 62 | 56 | 52 | 60 | 55 | 52 | 50 | 50 | 50 | 50 |
| 8 | 71 | 60 | 53 | 48 | 70 | 59 | 52 | 48 | 58 | 52 | 47 | 57 | 51 | 47 | 56 | 51 | 47 | 45 | 45 | 45 | 45 |
| 9 | 66 | 55 | 48 | 43 | 65 | 54 | 48 | 43 | 53 | 47 | 43 | 52 | 47 | 43 | 51 | 46 | 43 | 41 | 41 | 41 | 41 |
| 10 | 62 | 51 | 44 | 39 | 61 | 50 | 44 | 39 | 49 | 43 | 39 | 48 | 43 | 39 | 48 | 42 | 39 | 37 | 37 | 37 | 37 |

AVERAGE LUMINANCE (cd/sqm):

| | 0° | 45° | 90° | 135° | 180° |
|-----|---------|-------|------|------|------|
| 0° | 5924 | 5924 | 5924 | 5924 | 5924 |
| 5° | 13623 | 10183 | 5636 | 3440 | 2974 |
| 10° | 42915 | 17733 | 4599 | 1906 | 1417 |
| 15° | 277984 | 32771 | 3388 | 642 | 160 |
| 20° | 838999 | 56082 | 2328 | 0 | 0 |
| 25° | 1246024 | 56609 | 1368 | 0 | 0 |
| 30° | 1401207 | 43035 | 537 | 0 | 0 |
| 35° | 1208972 | 25692 | 378 | 0 | 0 |
| 40° | 696157 | 8746 | 0 | 0 | 0 |
| 45° | 169810 | 3532 | 219 | 0 | 219 |
| 50° | 20390 | 965 | 241 | 241 | 723 |
| 55° | 2732 | 0 | 540 | 540 | 1081 |
| 60° | 310 | 0 | 930 | 930 | 1550 |
| 65° | 367 | 367 | 1467 | 1467 | 2201 |
| 70° | 453 | 453 | 1813 | 1813 | 2266 |
| 75° | 0 | 599 | 2396 | 1797 | 2396 |
| 80° | 0 | 893 | 2678 | 1785 | 2678 |
| 85° | 0 | 1778 | 5335 | 1778 | 1778 |

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 2.5°
 Vertical Angle: 45°
 Luminance: 170906 cd/sqm



TEST NUMBER: P1315583

CATALOG NUMBER: LDSQA3D13R209735DE010 3LSQCA30R 1MW

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 4.6 | 0.5 |
| 10°-20° | 92.5 | 9.3 |
| 20°-30° | 403.1 | 40.4 |
| 30°-40° | 406.0 | 40.7 |
| 40°-50° | 81.4 | 8.2 |
| 50°-60° | 4.1 | 0.4 |
| 60°-70° | 2.7 | 0.3 |
| 70°-80° | 2.4 | 0.2 |
| 80°-90° | 1.2 | 0.1 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 500.2 | 50.1 |
| 0°-40° | 906.2 | 90.8 |
| 0°-60° | 991.7 | 99.4 |
| 0°-90° | 997.9 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 997.9 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | 45° | 90° | 135° | 180° | Flux |
|-----|------|-----|-----|------|------|------|
| 0° | 34 | 34 | 34 | 34 | 34 | |
| 5° | 79 | 59 | 33 | 20 | 17 | 12 |
| 15° | 1559 | 184 | 19 | 4 | 1 | 611 |
| 25° | 6557 | 298 | 7 | 0 | 0 | 2957 |
| 35° | 5750 | 122 | 2 | 0 | 0 | 3421 |
| 45° | 697 | 14 | 1 | 0 | 1 | 759 |
| 55° | 9 | 0 | 2 | 2 | 4 | 17 |
| 65° | 1 | 1 | 4 | 4 | 5 | 1 |
| 75° | 0 | 1 | 4 | 3 | 4 | 0 |
| 85° | 0 | 1 | 3 | 1 | 1 | 0 |
| 90° | 0 | 0 | 0 | 0 | 0 | |



TEST NUMBER: P1315583

CATALOG NUMBER: LDSQA3D13R209735DE010 3LSQCA30R 1MW

CANDELA DISTRIBUTION (FULL):

| | 0° | 2.5° | 5° | 7.5° | 10° | 12.5° | 15° | 17.5° | 20° | 22.5° | 45° |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|-------|
| 0° | 34.4 | 34.4 | 34.4 | 34.4 | 34.4 | 34.4 | 34.4 | 34.4 | 34.4 | 34.4 | 34.4 |
| 2.5° | 51.6 | 51.6 | 50.7 | 50.7 | 49.8 | 50.7 | 48.9 | 49.8 | 49.8 | 48.9 | 44.4 |
| 5° | 78.8 | 80.6 | 79.7 | 79.7 | 78.8 | 79.7 | 77.9 | 76.1 | 74.2 | 74.2 | 58.9 |
| 7.5° | 129.5 | 128.6 | 126.8 | 127.7 | 124.9 | 123.1 | 121.3 | 120.4 | 115.0 | 112.3 | 77.0 |
| 10° | 245.4 | 250.8 | 246.3 | 245.4 | 229.1 | 228.2 | 217.3 | 201.9 | 188.3 | 181.1 | 101.4 |
| 12.5° | 675.4 | 704.4 | 659.1 | 637.4 | 624.7 | 575.8 | 555.0 | 501.6 | 450.0 | 411.1 | 128.6 |
| 15° | 1559.1 | 1630.7 | 1539.2 | 1545.6 | 1469.5 | 1330.1 | 1207.8 | 1102.8 | 978.8 | 853.8 | 183.8 |
| 17.5° | 3054.9 | 2996.9 | 2947.2 | 2862.9 | 2708.1 | 2503.5 | 2240.0 | 1972.9 | 1742.0 | 1500.3 | 256.2 |
| 20° | 4577.8 | 4526.2 | 4413.0 | 4229.2 | 4031.8 | 3728.5 | 3415.3 | 3014.2 | 2625.7 | 2261.7 | 306.0 |
| 21° | 5102.1 | 5084.9 | 4899.2 | 4786.1 | 4481.8 | 4192.1 | 3830.8 | 3401.7 | 2964.4 | 2533.4 | 314.2 |
| 22° | 5570.2 | 5466.9 | 5367.3 | 5199.8 | 4897.4 | 4582.3 | 4180.3 | 3728.5 | 3254.1 | 2775.1 | 315.1 |
| 23° | 5894.3 | 5847.2 | 5753.1 | 5563.8 | 5263.2 | 4892.9 | 4469.2 | 3996.5 | 3496.7 | 2946.2 | 312.4 |
| 24° | 6252.8 | 6193.1 | 6055.5 | 5834.5 | 5531.2 | 5165.4 | 4681.9 | 4212.9 | 3669.7 | 3090.2 | 305.1 |
| 25° | 6557.1 | 6463.8 | 6300.8 | 6062.7 | 5731.3 | 5353.8 | 4867.6 | 4352.4 | 3790.1 | 3187.1 | 297.9 |
| 26° | 6754.5 | 6703.7 | 6494.6 | 6235.6 | 5880.7 | 5491.4 | 4995.2 | 4459.2 | 3868.0 | 3231.5 | 286.1 |
| 27° | 6960.0 | 6866.7 | 6661.2 | 6363.3 | 5978.5 | 5581.0 | 5067.6 | 4510.8 | 3895.1 | 3233.3 | 271.6 |
| 28° | 7077.7 | 6976.3 | 6743.6 | 6430.3 | 6041.9 | 5630.8 | 5109.3 | 4527.1 | 3889.7 | 3205.2 | 254.4 |
| 29° | 7114.8 | 6987.1 | 6759.9 | 6441.2 | 6057.3 | 5634.4 | 5103.0 | 4503.6 | 3841.7 | 3136.4 | 234.5 |
| 30° | 7046.0 | 6915.6 | 6700.1 | 6389.6 | 6008.4 | 5589.2 | 5044.1 | 4425.7 | 3756.6 | 3037.7 | 216.4 |
| 31° | 6895.7 | 6785.2 | 6577.0 | 6265.5 | 5899.7 | 5483.2 | 4911.0 | 4298.0 | 3611.7 | 2905.5 | 195.6 |
| 32° | 6697.4 | 6588.8 | 6384.1 | 6102.5 | 5730.4 | 5310.3 | 4729.0 | 4098.8 | 3441.5 | 2708.1 | 174.7 |
| 33° | 6399.5 | 6337.1 | 6153.3 | 5884.3 | 5512.2 | 5063.1 | 4484.6 | 3860.7 | 3198.9 | 2489.0 | 156.6 |
| 34° | 6098.0 | 6019.2 | 5890.7 | 5596.4 | 5196.2 | 4748.0 | 4165.8 | 3532.1 | 2902.8 | 2243.6 | 139.4 |
| 35° | 5750.3 | 5703.3 | 5501.3 | 5265.9 | 4863.9 | 4405.8 | 3827.2 | 3212.4 | 2557.8 | 1970.2 | 122.2 |
| 36° | 5413.5 | 5341.1 | 5111.1 | 4862.1 | 4471.9 | 3976.6 | 3405.3 | 2827.6 | 2259.9 | 1714.0 | 104.1 |
| 37° | 4924.6 | 4814.1 | 4650.3 | 4387.7 | 3931.3 | 3509.4 | 2987.9 | 2451.9 | 1893.2 | 1436.9 | 84.2 |
| 38° | 4349.6 | 4298.0 | 4070.8 | 3806.4 | 3428.8 | 3028.6 | 2512.5 | 2058.0 | 1561.9 | 1199.7 | 64.3 |
| 39° | 3671.5 | 3670.6 | 3453.3 | 3262.2 | 2892.8 | 2532.5 | 2067.1 | 1670.5 | 1289.3 | 966.1 | 49.8 |
| 40° | 3096.5 | 2989.7 | 2855.7 | 2615.8 | 2332.4 | 2026.3 | 1618.9 | 1307.4 | 1000.5 | 778.7 | 38.9 |
| 42.5° | 1623.4 | 1614.4 | 1535.6 | 1355.4 | 1197.0 | 1016.8 | 808.5 | 673.6 | 527.0 | 429.2 | 24.4 |
| 45° | 697.2 | 701.7 | 647.4 | 620.2 | 558.6 | 483.5 | 408.3 | 340.4 | 291.5 | 236.3 | 14.5 |
| 47.5° | 176.6 | 169.3 | 167.5 | 173.8 | 173.8 | 168.4 | 151.2 | 142.2 | 131.3 | 120.4 | 8.1 |
| 50° | 76.1 | 74.2 | 72.4 | 72.4 | 67.9 | 65.2 | 60.7 | 55.2 | 50.7 | 45.3 | 3.6 |
| 52.5° | 28.1 | 29.0 | 29.9 | 29.0 | 29.0 | 28.1 | 28.1 | 27.2 | 24.4 | 21.7 | 1.8 |
| 55° | 9.1 | 9.1 | 9.1 | 10.0 | 10.0 | 10.9 | 10.9 | 10.9 | 10.9 | 10.0 | 0.0 |
| 57.5° | 1.8 | 1.8 | 2.7 | 2.7 | 2.7 | 2.7 | 2.7 | 2.7 | 3.6 | 3.6 | 0.0 |
| 60° | 0.9 | 0.9 | 0.9 | 0.9 | 0.9 | 0.9 | 0.9 | 0.0 | 0.0 | 0.0 | 0.0 |
| 62.5° | 0.9 | 0.9 | 0.9 | 0.9 | 0.9 | 0.9 | 0.9 | 0.9 | 0.9 | 0.9 | 0.9 |
| 65° | 0.9 | 0.9 | 0.9 | 0.9 | 0.9 | 0.9 | 0.9 | 0.9 | 0.9 | 0.9 | 0.9 |
| 67.5° | 0.9 | 0.9 | 0.9 | 0.9 | 0.9 | 0.9 | 0.9 | 0.9 | 0.9 | 0.9 | 0.9 |
| 70° | 0.9 | 0.9 | 0.9 | 0.9 | 0.9 | 0.9 | 0.9 | 0.9 | 0.9 | 0.9 | 0.9 |
| 72.5° | 0.9 | 0.0 | 0.9 | 0.9 | 0.9 | 0.9 | 0.9 | 0.9 | 0.9 | 0.9 | 0.9 |
| 75° | 0.0 | 0.0 | 0.0 | 0.9 | 0.0 | 0.9 | 0.9 | 0.0 | 0.9 | 0.9 | 0.9 |
| 77.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.9 | 0.9 |
| 80° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.9 |



TEST NUMBER: P1315583

CATALOG NUMBER: LDSQA3D13R209735DE010 3LSQCA30R 1MW

CANDELA DISTRIBUTION (continued):

| | 0° | 2.5° | 5° | 7.5° | 10° | 12.5° | 15° | 17.5° | 20° | 22.5° | 45° |
|-------|-----|------|-----|------|-----|-------|-----|-------|-----|-------|-----|
| 82.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.9 |
| 85° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.9 |
| 87.5° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.9 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



TEST NUMBER: P1315583

CATALOG NUMBER: LDSQA3D13R209735DE010 3LSQCA30R 1MW

CANDELA DISTRIBUTION (continued):

| | 67.5° | 90° | 112.5° | 135° | 157.5° | 180° |
|-------|-------|------|--------|------|--------|------|
| 0° | 34.4 | 34.4 | 34.4 | 34.4 | 34.4 | 34.4 |
| 2.5° | 39.8 | 35.3 | 29.9 | 25.4 | 24.4 | 23.5 |
| 5° | 44.4 | 32.6 | 24.4 | 19.9 | 18.1 | 17.2 |
| 7.5° | 48.0 | 29.9 | 19.9 | 14.5 | 12.7 | 11.8 |
| 10° | 49.8 | 26.3 | 16.3 | 10.9 | 8.1 | 8.1 |
| 12.5° | 50.7 | 22.6 | 11.8 | 7.2 | 4.5 | 4.5 |
| 15° | 49.8 | 19.0 | 9.1 | 3.6 | 0.9 | 0.9 |
| 17.5° | 45.3 | 15.4 | 5.4 | 0.9 | 0.0 | 0.0 |
| 20° | 38.9 | 12.7 | 3.6 | 0.0 | 0.0 | 0.0 |
| 21° | 37.1 | 10.9 | 2.7 | 0.0 | 0.0 | 0.0 |
| 22° | 34.4 | 10.0 | 1.8 | 0.0 | 0.0 | 0.0 |
| 23° | 31.7 | 9.1 | 1.8 | 0.0 | 0.0 | 0.0 |
| 24° | 29.0 | 8.1 | 0.9 | 0.0 | 0.0 | 0.0 |
| 25° | 27.2 | 7.2 | 0.9 | 0.0 | 0.0 | 0.0 |
| 26° | 25.4 | 6.3 | 0.9 | 0.0 | 0.0 | 0.0 |
| 27° | 22.6 | 5.4 | 0.0 | 0.0 | 0.0 | 0.0 |
| 28° | 20.8 | 4.5 | 0.0 | 0.0 | 0.0 | 0.0 |
| 29° | 18.1 | 3.6 | 0.0 | 0.0 | 0.0 | 0.0 |
| 30° | 15.4 | 2.7 | 0.0 | 0.0 | 0.0 | 0.0 |
| 31° | 12.7 | 2.7 | 0.0 | 0.0 | 0.0 | 0.0 |
| 32° | 10.9 | 1.8 | 0.0 | 0.0 | 0.0 | 0.0 |
| 33° | 9.1 | 1.8 | 0.0 | 0.0 | 0.0 | 0.0 |
| 34° | 8.1 | 1.8 | 0.0 | 0.0 | 0.0 | 0.0 |
| 35° | 7.2 | 1.8 | 0.0 | 0.0 | 0.0 | 0.0 |
| 36° | 5.4 | 0.9 | 0.0 | 0.0 | 0.0 | 0.0 |
| 37° | 4.5 | 0.9 | 0.0 | 0.0 | 0.0 | 0.0 |
| 38° | 3.6 | 0.9 | 0.0 | 0.0 | 0.0 | 0.0 |
| 39° | 2.7 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 40° | 2.7 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 42.5° | 0.9 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |
| 45° | 0.0 | 0.9 | 0.0 | 0.0 | 0.9 | 0.9 |
| 47.5° | 0.0 | 0.9 | 0.0 | 0.0 | 0.9 | 1.8 |
| 50° | 0.0 | 0.9 | 0.9 | 0.9 | 1.8 | 2.7 |
| 52.5° | 0.0 | 1.8 | 0.9 | 0.9 | 2.7 | 2.7 |
| 55° | 0.9 | 1.8 | 0.9 | 1.8 | 3.6 | 3.6 |
| 57.5° | 0.9 | 1.8 | 1.8 | 2.7 | 3.6 | 4.5 |
| 60° | 1.8 | 2.7 | 2.7 | 2.7 | 4.5 | 4.5 |
| 62.5° | 1.8 | 2.7 | 3.6 | 3.6 | 4.5 | 5.4 |
| 65° | 1.8 | 3.6 | 3.6 | 3.6 | 4.5 | 5.4 |
| 67.5° | 2.7 | 3.6 | 3.6 | 3.6 | 4.5 | 5.4 |
| 70° | 2.7 | 3.6 | 3.6 | 3.6 | 4.5 | 4.5 |
| 72.5° | 2.7 | 3.6 | 2.7 | 3.6 | 3.6 | 4.5 |
| 75° | 2.7 | 3.6 | 2.7 | 2.7 | 3.6 | 3.6 |
| 77.5° | 1.8 | 2.7 | 2.7 | 1.8 | 2.7 | 2.7 |
| 80° | 1.8 | 2.7 | 1.8 | 1.8 | 2.7 | 2.7 |



TEST NUMBER: P1315583

CATALOG NUMBER: LDSQA3D13R209735DE010 3LSQCA30R 1MW

CANDELA DISTRIBUTION (continued):

| | 67.5° | 90° | 112.5° | 135° | 157.5° | 180° |
|-------|-------|-----|--------|------|--------|------|
| 82.5° | 1.8 | 2.7 | 1.8 | 0.9 | 1.8 | 1.8 |
| 85° | 1.8 | 2.7 | 1.8 | 0.9 | 0.9 | 0.9 |
| 87.5° | 1.8 | 2.7 | 1.8 | 0.9 | 0.0 | 0.9 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

(END OF REPORT)