

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1316141

Luminaire Tested: LDSQA3D02R459740DE010 3LSQCDR1MB

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1316141
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-32)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LDSQA3D02R459740DE010 3LSQCDR1MB
Description: 3in Adjustable LED luminaire with, R45 optic, 4000K CCT AND, 97CRI , 3LSQCDR1MB TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 318.0 lumens
Efficiency: N/A
Efficacy: 88.3 lumens/watt
Spacing Criteria (0/90/45): 0.72 / 0.74 / 0.67
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1316141
CATALOG NUMBER: LDSQA3D02R459740DE010 3LSQCDR1MB

Luminous Intensity Polar Plot





TEST NUMBER: P1316141
 CATALOG NUMBER: LDSQA3D02R459740DE010 3LSQCDR1MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	97	97	97	95
2	110	106	103	100	108	104	101	99	101	99	96	98	96	94	95	94	92	92	92	92	91
3	106	100	96	93	104	99	95	92	97	93	91	94	92	89	92	90	88	88	88	88	87
4	102	95	91	87	100	94	90	87	92	89	86	90	87	85	89	86	84	84	84	84	83
5	98	91	86	83	96	90	86	82	88	85	82	87	83	81	85	82	80	80	80	80	79
6	94	87	82	78	93	86	81	78	85	81	78	83	80	77	82	79	77	77	77	77	75
7	91	83	78	75	89	82	78	74	81	77	74	80	76	74	79	76	73	73	73	73	72
8	87	79	75	71	86	79	74	71	78	74	71	77	73	70	76	73	70	70	70	70	69
9	84	76	71	68	83	76	71	68	75	71	68	74	70	68	73	70	67	67	67	67	66
10	81	73	68	65	80	73	68	65	72	68	65	71	67	65	71	67	65	65	65	65	64

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	105934	105934	105934
5°	106166	106788	107843
10°	103511	103721	106449
15°	87330	87366	90237
20°	67409	68362	69498
25°	41825	41863	42129
30°	17262	18335	16963
35°	5361	6560	5172
40°	1641	2293	1551
45°	122	852	122
50°	0	134	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°
 Vertical Angle: 45°
 Luminance: 852 cd/sqm



TEST NUMBER: P1316141

CATALOG NUMBER: LDSQA3D02R459740DE010 3LSQCDR1MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	58.5	18.4
10°-20°	136.1	42.8
20°-30°	99.8	31.4
30°-40°	21.5	6.7
40°-50°	2.0	0.6
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	294.5	92.6
0°-40°	315.9	99.4
0°-60°	318.0	100.0
0°-90°	318.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	318.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	615	615	615	615	615	
5°	614	616	618	622	624	58
15°	490	489	490	498	506	135
25°	220	219	220	220	222	99
35°	26	27	31	27	25	20
45°	0	1	4	1	0	1
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P1316141
 CATALOG NUMBER: LDSQA3D02R459740DE010 3LSQCDR1MB

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	615.1	615.1	615.1	615.1	615.1
1°	613.9	615.3	615.3	616.2	616.7
2°	614.4	615.3	615.1	616.7	617.4
3°	613.6	615.3	615.8	617.7	618.8
4°	613.9	615.3	616.7	619.6	621.2
5°	614.1	615.8	617.7	621.9	623.8
6°	614.4	615.5	617.7	623.1	626.7
7°	612.0	613.6	616.0	622.9	626.7
8°	608.2	609.2	611.0	620.0	624.5
9°	601.1	600.9	603.7	613.6	618.8
10°	591.9	589.1	593.1	603.0	608.7
11°	577.0	573.9	577.5	588.1	593.6
12°	557.6	557.6	558.3	567.8	577.2
13°	537.1	534.7	536.1	546.8	553.4
14°	514.4	512.0	513.4	521.5	531.9
15°	489.8	488.8	490.0	497.8	506.1
17.5°	431.4	429.3	433.5	441.3	445.6
20°	367.8	371.4	373.0	378.0	379.2
22.5°	294.8	298.6	300.9	301.6	302.3
25°	220.1	219.4	220.3	220.3	221.7
27.5°	144.7	144.7	147.3	145.6	144.0
30°	86.8	90.3	92.2	89.1	85.3
32.5°	47.3	50.8	53.9	49.4	46.1
35°	25.5	27.4	31.2	26.7	24.6
37.5°	13.9	15.6	18.0	15.1	13.9
40°	7.3	9.0	10.2	9.0	6.9
42.5°	2.4	4.5	5.9	4.5	2.1
45°	0.5	1.4	3.5	1.4	0.5
47.5°	0.0	0.2	1.7	0.2	0.0
50°	0.0	0.0	0.5	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1316141
CATALOG NUMBER: LDSQA3D02R459740DE010 3LSQCDR1MB

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)