

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1316150

Luminaire Tested: LDSQA3D02R509740DE010 3LSQCDR1MB

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1316150
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-27)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LDSQA3D02R509740DE010 3LSQCDR1MB
Description: 3in Adjustable LED luminaire with, R50 optic, 4000K CCT AND, 97CRI , 3LSQCDR1MB TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 330.0 lumens
Efficiency: N/A
Efficacy: 91.7 lumens/watt
Spacing Criteria (0/90/45): 0.85 / 0.85 / 0.78
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1316150
CATALOG NUMBER: LDSQA3D02R509740DE010 3LSQCDR1MB

Luminous Intensity Polar Plot





TEST NUMBER: P1316150
 CATALOG NUMBER: LDSQA3D02R509740DE010 3LSQCDR1MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	114	112	109	107	112	110	108	106	106	104	102	102	101	99	98	97	97	97	97	97	95
2	109	105	101	98	107	103	100	97	100	98	95	97	95	93	95	93	91	91	91	91	90
3	105	99	95	91	103	98	94	90	95	92	89	93	90	88	91	88	86	86	86	86	85
4	100	94	89	85	99	93	88	85	90	87	84	89	85	83	87	84	82	82	82	82	80
5	96	89	84	80	95	88	83	79	86	82	79	85	81	78	83	80	77	77	77	77	76
6	92	84	79	75	91	83	79	75	82	78	74	81	77	74	79	76	73	73	73	73	72
7	88	80	75	71	87	79	74	71	78	74	70	77	73	70	76	72	70	70	70	70	69
8	85	76	71	67	83	76	71	67	75	70	67	74	70	67	73	69	66	66	66	66	65
9	81	73	67	64	80	72	67	64	71	67	64	70	66	63	70	66	63	63	63	63	62
10	78	69	64	61	77	69	64	61	68	64	60	67	63	60	67	63	60	60	60	60	59

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	88264	88264	88264
5°	86717	86475	86233
10°	83627	82718	82893
15°	76936	75973	76169
20°	68692	68050	68435
25°	53474	55716	52884
30°	28955	32336	28438
35°	9125	10870	8935
40°	2023	2810	1911
45°	49	852	49
50°	0	134	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°
 Vertical Angle: 45°
 Luminance: 852 cd/sqm



TEST NUMBER: P1316150
 CATALOG NUMBER: LDSQA3D02R509740DE010 3LSQCDR1MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	46.9	14.2
10°-20°	119.3	36.1
20°-30°	125.6	38.1
30°-40°	35.9	10.9
40°-50°	2.2	0.7
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	291.9	88.4
0°-40°	327.8	99.3
0°-60°	330.0	100.0
0°-90°	330.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	330.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	512	512	512	512	512	
5°	502	501	500	500	499	47
15°	432	429	426	427	427	120
25°	281	292	293	290	278	123
35°	43	46	52	44	42	34
45°	0	1	4	1	0	1
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P1316150
 CATALOG NUMBER: LDSQA3D02R509740DE010 3LSQCDR1MB

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	512.5	512.5	512.5	512.5	512.5
1°	512.7	512.9	512.5	512.9	511.8
2°	512.0	511.5	511.0	511.3	510.6
3°	509.4	509.2	508.2	508.4	507.5
4°	506.1	505.4	504.7	504.2	503.3
5°	501.6	501.1	500.2	499.7	498.8
6°	497.8	496.9	495.2	494.8	493.8
7°	492.9	492.4	490.3	489.8	489.3
8°	489.1	487.7	485.1	485.3	484.1
9°	484.1	482.2	479.7	479.7	479.9
10°	478.2	475.4	473.0	473.7	474.0
11°	470.4	468.6	465.0	466.7	466.7
12°	461.9	459.6	457.0	458.4	459.4
13°	452.0	450.1	447.8	449.2	448.7
14°	442.4	438.8	437.2	439.1	438.3
15°	431.5	428.7	426.1	426.8	427.2
17.5°	402.5	399.4	397.5	397.7	399.9
20°	374.8	373.7	371.3	372.2	373.4
22.5°	342.3	342.7	339.9	340.6	343.5
25°	281.4	291.8	293.2	289.9	278.3
27.5°	208.4	224.0	228.7	221.2	207.0
30°	145.6	149.9	162.6	148.2	143.0
32.5°	85.4	91.8	98.7	88.8	85.2
35°	43.4	46.5	51.7	43.9	42.5
37.5°	20.1	21.5	23.6	20.1	18.9
40°	9.0	10.6	12.5	10.2	8.5
42.5°	2.8	5.0	6.6	4.5	2.6
45°	0.2	1.2	3.5	1.2	0.2
47.5°	0.0	0.2	1.4	0.2	0.0
50°	0.0	0.0	0.5	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1316150
CATALOG NUMBER: LDSQA3D02R509740DE010 3LSQCDR1MB

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)