

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1316328

Luminaire Tested: LDSQA3D05R559740DE010 3LSQCDR1MMS

Issue Date: 1/29/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1316328  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-28)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LDSQA3D05R559740DE010 3LSQCDR1MMS  
Description: 3in Adjustable LED luminaire with, R55 optic, 4000K CCT AND, 97CRI , 3LSQCDR1MMS TRIM  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 632.0 lumens  
Efficiency: N/A  
Efficacy: 87.8 lumens/watt  
Spacing Criteria (0/90/45): 0.93 / 0.93 / 0.81  
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 7.2  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1316328  
CATALOG NUMBER: LDSQA3D05R559740DE010 3LSQCDR1MMS

### Luminous Intensity Polar Plot





TEST NUMBER: P1316328

CATALOG NUMBER: LDSQA3D05R559740DE010 3LSQCDR1MMS

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	114	112	109	107	112	109	107	106	105	104	102	102	100	99	98	97	96	96	96	96	95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	91	91	91	89
3	104	99	94	91	103	97	93	90	95	91	89	92	90	87	90	88	86	86	86	86	84
4	100	93	88	84	98	92	87	84	90	86	83	88	85	82	86	83	81	81	81	81	80
5	96	88	83	79	94	87	82	79	85	81	78	84	80	77	82	79	77	77	77	77	75
6	91	83	78	74	90	83	78	74	81	77	74	80	76	73	79	75	73	73	73	73	71
7	87	79	74	70	86	79	73	70	77	73	69	76	72	69	75	72	69	69	69	69	67
8	84	75	70	66	83	75	70	66	74	69	66	73	69	65	72	68	65	65	65	65	64
9	80	72	66	63	79	71	66	63	70	66	62	69	65	62	69	65	62	62	62	62	61
10	77	68	63	59	76	68	63	59	67	62	59	66	62	59	66	62	59	59	59	59	58

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	143169	143169	143169
5°	141537	141122	140362
10°	148350	146566	145552
15°	145883	144332	143797
20°	132875	133406	132966
25°	106605	108258	106605
30°	61191	62722	63219
35°	17450	21025	17955
40°	4474	6430	4586
45°	463	2241	365
50°	0	402	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 45°  
 Vertical Angle: 45°  
 Luminance: 2241 cd/sqm



TEST NUMBER: P1316328

CATALOG NUMBER: LDSQA3D05R559740DE010 3LSQCDR1MMS

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	78.9	12.5
10°-20°	225.2	35.6
20°-30°	248.1	39.3
30°-40°	74.1	11.7
40°-50°	5.7	0.9
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	552.2	87.4
0°-40°	626.3	99.1
0°-60°	632.0	100.0
0°-90°	632.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	632.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	831	831	831	831	831	
5°	819	817	816	813	812	79
15°	818	812	810	806	806	227
25°	561	561	570	569	561	246
35°	83	88	100	91	85	69
45°	2	5	9	5	2	4
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P1316328  
 CATALOG NUMBER: LDSQA3D05R559740DE010 3LSQCDR1MMS

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	831.3	831.3	831.3	831.3	831.3
1°	830.8	830.8	829.8	829.4	830.8
2°	828.4	828.4	826.0	825.5	826.9
3°	823.0	822.6	820.6	819.2	820.1
4°	818.7	817.7	816.3	813.8	814.3
5°	818.7	817.2	816.3	812.9	811.9
6°	822.6	821.6	819.7	816.3	815.3
7°	829.4	827.4	825.5	821.1	820.1
8°	836.6	835.2	831.3	826.9	825.0
9°	843.9	840.5	835.7	831.3	830.8
10°	848.3	843.4	838.1	832.8	832.3
11°	847.8	843.4	837.1	832.3	831.8
12°	845.9	839.5	834.2	828.4	828.9
13°	839.1	833.2	827.9	823.5	822.6
14°	829.8	824.5	819.7	815.3	815.8
15°	818.2	812.4	809.5	806.1	806.5
17.5°	776.9	775.5	776.9	773.1	774.5
20°	725.0	723.6	727.9	726.0	725.5
22.5°	652.7	654.7	662.9	660.5	656.1
25°	561.0	561.0	569.7	568.8	561.0
27.5°	441.6	445.0	450.3	452.8	447.0
30°	307.7	315.4	315.4	320.3	317.9
32.5°	171.8	188.3	192.2	194.6	184.9
35°	83.0	88.3	100.0	91.2	85.4
37.5°	39.8	42.2	53.9	43.7	40.8
40°	19.9	22.8	28.6	23.8	20.4
42.5°	8.2	12.1	15.0	12.1	8.2
45°	1.9	4.9	9.2	4.9	1.5
47.5°	0.0	0.5	4.4	1.0	0.0
50°	0.0	0.0	1.5	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1316328  
CATALOG NUMBER: LDSQA3D05R559740DE010 3LSQCDR1MMS

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)