

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1316050

Luminaire Tested: LDSQA3D02R159740DE010 3LSQCDR1MB

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1316050
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-21)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LDSQA3D02R159740DE010 3LSQCDR1MB
Description: 3in Adjustable LED luminaire with, R15 optic, 4000K CCT AND, 97CRI , 3LSQCDR1MB TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 298.0 lumens
Efficiency: N/A
Efficacy: 82.8 lumens/watt
Spacing Criteria (0/90/45): 0.29 / 0.29 / 0.29
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1316050
CATALOG NUMBER: LDSQA3D02R159740DE010 3LSQCDR1MB

Luminous Intensity Polar Plot



— 0°-180° - - 45°-225° - - - 90°-270°



TEST NUMBER: P1316050
 CATALOG NUMBER: LDSQA3D02R159740DE010 3LSQCDR1MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	116	114	112	111	113	112	110	109	108	107	106	104	103	102	101	100	100	100	100	100	98
2	113	109	107	105	111	108	106	104	105	103	101	102	101	99	99	98	97	97	98	97	96
3	110	106	103	100	108	105	102	100	102	100	98	100	98	97	98	96	95	95	98	96	94
4	107	103	99	97	106	102	99	96	100	97	95	98	96	94	96	95	93	95	96	95	92
5	105	100	97	94	104	99	96	94	98	95	93	96	94	92	95	93	91	95	93	91	90
6	103	97	94	92	102	97	94	91	96	93	91	94	92	90	93	91	90	93	91	90	89
7	101	95	92	90	100	95	92	89	94	91	89	93	90	88	92	90	88	92	90	88	87
8	99	93	90	88	98	93	90	88	92	89	87	91	89	87	90	88	87	90	88	87	86
9	97	92	88	86	96	91	88	86	90	88	86	90	87	85	89	87	85	89	87	85	84
10	95	90	87	84	95	90	86	84	89	86	84	88	86	84	88	86	84	88	86	84	83

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	459852	459852	459852
5°	374407	375617	374891
10°	174652	176209	173988
15°	54844	55308	54969
20°	21736	22598	21040
25°	8779	10622	8456
30°	3520	4832	3321
35°	1030	2123	988
40°	315	787	270
45°	49	170	49
50°	0	54	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°
 Vertical Angle: 45°
 Luminance: 170 cd/sqm



TEST NUMBER: P1316050
 CATALOG NUMBER: LDSQA3D02R159740DE010 3LSQCDR1MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	167.2	56.1
10°-20°	100.0	33.6
20°-30°	25.2	8.5
30°-40°	5.1	1.7
40°-50°	0.5	0.2
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	292.4	98.1
0°-40°	297.5	99.8
0°-60°	298.0	100.0
0°-90°	298.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	298.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2670	2670	2670	2670	2670	
5°	2166	2162	2173	2167	2168	167
15°	308	310	310	306	308	100
25°	46	50	56	50	44	24
35°	5	7	10	6	5	4
45°	0	0	1	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P1316050
 CATALOG NUMBER: LDSQA3D02R159740DE010 3LSQCDR1MB

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2670.1	2670.1	2670.1	2670.1	2670.1
1°	2646.0	2655.0	2650.3	2654.0	2649.8
2°	2588.8	2600.8	2597.0	2595.8	2599.1
3°	2487.9	2501.8	2501.3	2497.8	2492.1
4°	2350.2	2344.6	2353.3	2352.3	2342.7
5°	2165.7	2161.7	2172.7	2167.3	2168.5
6°	1939.9	1957.3	1953.5	1954.0	1958.5
7°	1697.3	1706.7	1714.8	1721.4	1712.2
8°	1474.6	1472.2	1472.9	1480.5	1455.0
9°	1225.2	1239.8	1230.4	1215.3	1225.0
10°	998.7	1007.6	1007.6	994.4	994.9
11°	796.2	803.5	798.3	801.6	780.9
12°	641.8	623.7	619.4	622.7	622.5
13°	490.0	491.2	490.0	489.8	487.4
14°	384.2	390.3	387.7	381.4	378.5
15°	307.6	310.2	310.2	305.7	308.3
17.5°	184.8	187.9	188.6	185.5	185.5
20°	118.6	120.0	123.3	118.8	114.8
22.5°	73.1	76.1	81.8	75.2	71.9
25°	46.2	50.4	55.9	49.5	44.5
27.5°	29.0	32.5	37.2	31.1	28.0
30°	17.7	20.0	24.3	19.6	16.7
32.5°	9.9	11.8	15.3	11.3	9.4
35°	4.9	6.6	10.1	6.4	4.7
37.5°	2.8	3.5	6.4	3.1	2.6
40°	1.4	1.9	3.5	1.9	1.2
42.5°	0.5	0.9	1.4	0.9	0.5
45°	0.2	0.5	0.7	0.5	0.2
47.5°	0.0	0.0	0.2	0.0	0.0
50°	0.0	0.0	0.2	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1316050
CATALOG NUMBER: LDSQA3D02R159740DE010 3LSQCDR1MB

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)