

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1316098

Luminaire Tested: LDSQA3D02R309740DE010 3LSQCDR1MB

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1316098
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-24)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LDSQA3D02R309740DE010 3LSQCDR1MB
Description: 3in Adjustable LED luminaire with, R30 optic, 4000K CCT AND, 97CRI , 3LSQCDR1MB TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 303.0 lumens
Efficiency: N/A
Efficacy: 84.2 lumens/watt
Spacing Criteria (0/90/45): 0.51 / 0.51 / 0.46
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1316098
CATALOG NUMBER: LDSQA3D02R309740DE010 3LSQCDR1MB

Luminous Intensity Polar Plot



— 0°-180° - - 45°-225° - - - 90°-270°



TEST NUMBER: P1316098
 CATALOG NUMBER: LDSQA3D02R309740DE010 3LSQCDR1MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	115	113	111	110	113	111	109	108	107	106	105	103	102	101	100	99	99	99	99	99	97
2	112	108	105	103	109	106	104	102	103	101	99	100	99	97	98	96	95	95	94	94	94
3	108	104	100	97	106	102	99	97	100	97	95	98	95	94	95	94	92	95	94	92	91
4	105	100	96	93	103	99	95	92	97	94	91	95	92	90	93	91	89	93	91	89	88
5	102	96	92	89	101	95	92	89	94	91	88	92	90	87	91	89	87	91	89	87	86
6	99	93	89	86	98	92	89	86	91	88	85	90	87	85	89	86	84	89	86	84	83
7	96	90	86	83	95	90	86	83	89	85	83	87	85	82	87	84	82	87	84	82	81
8	94	88	84	81	93	87	83	81	86	83	80	85	82	80	84	82	80	84	82	80	79
9	91	85	81	78	91	85	81	78	84	80	78	83	80	78	82	80	78	82	80	78	77
10	89	83	79	76	88	82	79	76	82	78	76	81	78	76	80	78	76	80	78	76	75

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	202241	202241	202241
5°	197309	197551	198657
10°	168514	167727	166748
15°	103983	102771	103145
20°	39294	39514	39478
25°	12086	13264	12637
30°	4872	6185	5071
35°	1430	2628	1493
40°	585	1057	585
45°	122	341	122
50°	0	54	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°
 Vertical Angle: 45°
 Luminance: 341 cd/sqm



TEST NUMBER: P1316098

CATALOG NUMBER: LDSQA3D02R309740DE010 3LSQCDR1MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	103.6	34.2
10°-20°	153.3	50.6
20°-30°	38.0	12.6
30°-40°	7.1	2.4
40°-50°	0.9	0.3
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	295.0	97.3
0°-40°	302.1	99.7
0°-60°	303.0	100.0
0°-90°	303.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	303.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1174	1174	1174	1174	1174	
5°	1141	1141	1143	1145	1149	104
15°	583	578	576	581	578	154
25°	64	68	70	70	66	37
35°	7	9	12	9	7	6
45°	0	1	1	1	0	1
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P1316098
 CATALOG NUMBER: LDSQA3D02R309740DE010 3LSQCDR1MB

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1174.3	1174.3	1174.3	1174.3	1174.3
1°	1174.7	1173.8	1173.8	1172.4	1175.0
2°	1170.5	1169.6	1171.2	1170.0	1173.3
3°	1164.1	1163.0	1165.3	1166.0	1167.7
4°	1154.7	1153.8	1156.4	1157.8	1162.2
5°	1141.3	1140.8	1142.7	1144.6	1149.1
6°	1122.9	1122.2	1123.4	1125.7	1128.6
7°	1096.3	1094.9	1095.8	1096.3	1097.0
8°	1062.6	1060.4	1059.3	1061.9	1063.3
9°	1019.2	1016.9	1014.3	1013.3	1016.6
10°	963.6	960.1	959.1	956.8	953.5
11°	899.0	896.2	895.5	891.2	889.4
12°	825.0	823.6	825.3	822.7	821.7
13°	754.1	745.1	744.0	739.0	736.4
14°	670.2	662.0	661.7	659.1	662.7
15°	583.2	577.6	576.4	580.9	578.5
17.5°	371.9	375.6	374.7	372.3	368.3
20°	214.4	211.9	215.6	216.6	215.4
22.5°	114.3	115.2	115.9	118.8	120.7
25°	63.6	67.9	69.8	69.5	66.5
27.5°	39.6	42.2	45.7	43.4	40.8
30°	24.5	26.6	31.1	26.9	25.5
32.5°	13.2	16.7	20.0	16.7	13.7
35°	6.8	9.0	12.5	9.2	7.1
37.5°	4.5	5.2	8.0	5.2	4.5
40°	2.6	3.3	4.7	3.3	2.6
42.5°	1.2	1.9	2.6	1.9	1.2
45°	0.5	0.7	1.4	0.9	0.5
47.5°	0.0	0.2	0.7	0.2	0.0
50°	0.0	0.0	0.2	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1316098
CATALOG NUMBER: LDSQA3D02R309740DE010 3LSQCDR1MB

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)