

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1316119

Luminaire Tested: LDSQA3D02R359740DE010 3LSQPHR1MMS

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1316119
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-5)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LDSQA3D02R359740DE010 3LSQPHR1MMS
Description: 3in Adjustable LED luminaire with, R35 optic, 4000K CCT AND, 97CRI , 3LSQPHR1MMS TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 274.0 lumens
Efficiency: N/A
Efficacy: 76.1 lumens/watt
Spacing Criteria (0/90/45): 0.57 / 0.56 / 0.51
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1316119

CATALOG NUMBER: LDSQA3D02R359740DE010 3LSQPHR1MMS

Luminous Intensity Polar Plot



TEST NUMBER: P1316119

CATALOG NUMBER: LDSQA3D02R359740DE010 3LSQPHR1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	113	111	109	113	111	109	108	107	106	104		103	102	101		100
2	111	108	105	102	109	106	103	101	103	101	99		100	98	97		97
3	108	103	100	97	106	102	99	96	99	97	94		97	95	93		95
4	104	99	95	92	103	98	94	92	96	93	91		94	92	90		93
5	101	95	91	88	100	95	91	88	93	90	87		92	89	87		90
6	98	92	88	85	97	91	88	85	90	87	84		89	86	84		88
7	96	89	85	82	94	89	85	82	87	84	81		86	83	81		85
8	93	86	82	79	92	86	82	79	85	81	79		84	81	79		83
9	90	84	80	77	89	83	79	77	82	79	76		82	79	76		81
10	88	81	77	75	87	81	77	74	80	77	74		80	76	74		79

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	155465	155465	155465
5°	152809	152481	152152
10°	140043	135829	132524
15°	100275	97083	95906
20°	46497	48091	49778
25°	11041	15696	16361
30°	3242	3699	4176
35°	736	1198	1093
40°	157	315	202
45°	49	49	49
50°	54	0	54
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 52.5°
Luminance: 57 cd/sqm

TEST NUMBER: P1316119

CATALOG NUMBER: LDSQA3D02R359740DE010 3LSQPHR1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	81.0	29.6
10°-20°	144.9	52.9
20°-30°	43.6	15.9
30°-40°	4.2	1.5
40°-50°	0.3	0.1
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	269.5	98.4
0°-40°	273.7	99.9
0°-60°	274.0	100.0
0°-90°	274.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	274.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	903	903	903	903	903	
5°	884	884	882	881	880	82
15°	562	558	544	542	538	149
25°	58	64	83	86	86	37
35°	4	5	6	6	5	3
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	

TEST NUMBER: P1316119

CATALOG NUMBER: LDSQA3D02R359740DE010 3LSQPHR1MMS

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	902.7	902.7	902.7	902.7	902.7
1°	902.3	902.3	901.8	901.8	900.8
2°	900.1	900.4	899.4	899.2	898.5
3°	896.8	896.1	896.1	895.7	895.2
4°	891.6	890.2	889.8	890.0	889.0
5°	883.9	883.6	882.0	880.8	880.1
6°	875.4	873.7	870.2	867.1	866.4
7°	862.6	859.1	856.0	849.6	848.7
8°	847.0	841.4	834.8	825.8	825.3
9°	827.9	818.7	809.5	797.5	793.2
10°	800.8	792.3	776.7	766.1	757.8
11°	767.0	756.4	738.2	725.5	718.6
12°	728.8	718.9	697.6	686.1	676.4
13°	679.7	671.4	651.6	638.9	631.3
14°	622.8	616.7	597.8	592.1	589.6
15°	562.4	558.2	544.5	542.1	537.9
17.5°	414.0	406.9	399.1	400.5	401.9
20°	253.7	263.6	262.4	267.6	271.6
22.5°	126.5	139.2	154.1	163.1	167.6
25°	58.1	64.0	82.6	86.1	86.1
27.5°	29.3	30.7	38.9	39.6	41.5
30°	16.3	17.5	18.6	20.8	21.0
32.5°	8.3	9.7	10.1	11.3	10.9
35°	3.5	4.7	5.7	6.1	5.2
37.5°	1.7	2.1	3.1	2.8	2.1
40°	0.7	0.9	1.4	1.2	0.9
42.5°	0.5	0.5	0.7	0.5	0.5
45°	0.2	0.2	0.2	0.2	0.2
47.5°	0.2	0.2	0.0	0.2	0.2
50°	0.2	0.0	0.0	0.0	0.2
52.5°	0.2	0.0	0.0	0.0	0.2
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1316119

CATALOG NUMBER: LDSQA3D02R359740DE010 3LSQPHR1MMS

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)