

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1316160

Luminaire Tested: LDSQA3D02R559740DE010 3LSQCDR1MMS

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1316160
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-28)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LDSQA3D02R559740DE010 3LSQCDR1MMS
Description: 3in Adjustable LED luminaire with, R55 optic, 4000K CCT AND, 97CRI , 3LSQCDR1MMS TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 307.0 lumens
Efficiency: N/A
Efficacy: 85.3 lumens/watt
Spacing Criteria (0/90/45): 0.93 / 0.93 / 0.81
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1316160
CATALOG NUMBER: LDSQA3D02R559740DE010 3LSQCDR1MMS

Luminous Intensity Polar Plot





TEST NUMBER: P1316160
 CATALOG NUMBER: LDSQA3D02R559740DE010 3LSQCDR1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	114	112	109	107	112	109	107	106	105	104	102	102	100	99	98	97	96	96	96	96	95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	91	91	91	89
3	104	99	94	91	103	97	93	90	95	91	89	92	90	87	90	88	86	86	86	86	84
4	100	93	88	84	98	92	87	84	90	86	83	88	85	82	86	83	81	81	81	81	80
5	96	88	83	79	94	87	82	79	85	81	78	84	80	77	82	79	77	77	77	77	75
6	91	83	78	74	90	83	78	74	81	77	74	80	76	73	79	75	73	73	73	73	71
7	87	79	74	70	86	79	73	70	77	73	69	76	72	69	75	72	69	69	69	69	67
8	84	75	70	66	83	75	70	66	74	69	66	73	69	65	72	68	65	65	65	65	64
9	80	72	66	63	79	71	66	63	70	66	62	69	65	62	69	65	62	62	62	62	61
10	77	68	63	59	76	68	63	59	67	62	59	66	62	59	66	62	59	59	59	59	58

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	69544	69544	69544
5°	68755	68547	68184
10°	72068	71193	70704
15°	70856	70107	69857
20°	64550	64806	64586
25°	51782	52599	51782
30°	29730	30466	30705
35°	8473	10218	8725
40°	2181	3125	2226
45°	219	1096	170
50°	0	188	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°
 Vertical Angle: 45°
 Luminance: 1096 cd/sqm



TEST NUMBER: P1316160

CATALOG NUMBER: LDSQA3D02R559740DE010 3LSQCDR1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	38.3	12.5
10°-20°	109.4	35.6
20°-30°	120.5	39.3
30°-40°	36.0	11.7
40°-50°	2.8	0.9
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	268.2	87.4
0°-40°	304.2	99.1
0°-60°	307.0	100.0
0°-90°	307.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	307.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	404	404	404	404	404	
5°	398	397	396	395	394	39
15°	397	395	393	392	392	110
25°	272	272	277	276	272	119
35°	40	43	49	44	42	33
45°	1	2	4	2	1	2
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P1316160
 CATALOG NUMBER: LDSQA3D02R559740DE010 3LSQCDR1MMS

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	403.8	403.8	403.8	403.8	403.8
1°	403.6	403.6	403.1	402.9	403.6
2°	402.4	402.4	401.2	401.0	401.7
3°	399.8	399.6	398.6	397.9	398.4
4°	397.7	397.2	396.5	395.3	395.6
5°	397.7	397.0	396.5	394.9	394.4
6°	399.6	399.1	398.2	396.5	396.0
7°	402.9	401.9	401.0	398.9	398.4
8°	406.4	405.7	403.8	401.7	400.7
9°	409.9	408.3	405.9	403.8	403.6
10°	412.1	409.7	407.1	404.5	404.3
11°	411.8	409.7	406.6	404.3	404.0
12°	410.9	407.8	405.2	402.4	402.6
13°	407.6	404.8	402.2	400.0	399.6
14°	403.1	400.5	398.2	396.0	396.3
15°	397.4	394.6	393.2	391.6	391.8
17.5°	377.4	376.7	377.4	375.5	376.2
20°	352.2	351.5	353.6	352.7	352.4
22.5°	317.1	318.0	322.0	320.8	318.7
25°	272.5	272.5	276.8	276.3	272.5
27.5°	214.5	216.2	218.8	219.9	217.1
30°	149.5	153.2	153.2	155.6	154.4
32.5°	83.4	91.5	93.4	94.5	89.8
35°	40.3	42.9	48.6	44.3	41.5
37.5°	19.3	20.5	26.2	21.2	19.8
40°	9.7	11.1	13.9	11.6	9.9
42.5°	4.0	5.9	7.3	5.9	4.0
45°	0.9	2.4	4.5	2.4	0.7
47.5°	0.0	0.2	2.1	0.5	0.0
50°	0.0	0.0	0.7	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1316160
CATALOG NUMBER: LDSQA3D02R559740DE010 3LSQCDR1MMS

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)