

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1316237

Luminaire Tested: LDSQA3D05R209740DE010 3LSQPHR1MW

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1316237
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-2)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LDSQA3D05R209740DE010 3LSQPHR1MW
Description: 3in Adjustable LED luminaire with, R20 optic, 4000K CCT AND, 97CRI , 3LSQPHR1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 545.0 lumens
Efficiency: N/A
Efficacy: 75.7 lumens/watt
Spacing Criteria (0/90/45): 0.35 / 0.36 / 0.33
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1316237
CATALOG NUMBER: LDSQA3D05R209740DE010 3LSQPHR1MW

Luminous Intensity Polar Plot



— 0°-180° - - 45°-225° - - - 90°-270°



TEST NUMBER: P1316237

CATALOG NUMBER: LDSQA3D05R209740DE010 3LSQPHR1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	116	114	112	111	113	112	110	109	108	107	106	104	103	102	101	100	100	100	100	100	98
2	113	109	107	105	111	108	106	104	105	103	101	102	101	99	99	98	97	97	98	97	96
3	110	106	103	100	108	105	102	100	102	100	98	100	98	97	98	96	95	95	98	96	94
4	107	103	99	97	106	102	99	96	100	97	95	98	96	94	96	95	93	93	96	95	92
5	105	100	97	94	104	99	96	94	98	95	93	96	94	92	95	93	92	92	95	93	91
6	103	98	94	92	102	97	94	91	96	93	91	95	92	90	93	91	90	90	93	91	89
7	101	95	92	90	100	95	92	89	94	91	89	93	90	89	92	90	88	88	92	90	87
8	99	93	90	88	98	93	90	88	92	89	87	91	89	87	91	88	87	87	91	88	86
9	97	92	88	86	96	91	88	86	91	88	86	90	87	86	89	87	85	85	89	87	85
10	95	90	87	85	95	90	87	85	89	86	84	88	86	84	88	86	84	84	88	86	83

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	698828	698828	698828
5°	603699	609335	611599
10°	363417	366810	385067
15°	125700	122758	132547
20°	33008	31065	31139
25°	7202	8665	9881
30°	3082	3082	3182
35°	1745	1535	1640
40°	764	877	989
45°	244	365	365
50°	134	134	134
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 22.5°

Vertical Angle: 45°

Luminance: 365 cd/sqm



TEST NUMBER: P1316237

CATALOG NUMBER: LDSQA3D05R209740DE010 3LSQPHR1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	290.2	53.2
10°-20°	221.0	40.5
20°-30°	27.3	5.0
30°-40°	5.2	0.9
40°-50°	1.3	0.2
50°-60°	0.1	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	538.5	98.8
0°-40°	543.7	99.8
0°-60°	545.0	100.0
0°-90°	545.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	545.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4058	4058	4058	4058	4058	
5°	3492	3490	3525	3522	3538	288
15°	705	680	688	730	743	221
25°	38	43	46	48	52	26
35°	8	8	7	8	8	5
45°	1	2	2	2	2	1
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P1316237
 CATALOG NUMBER: LDSQA3D05R209740DE010 3LSQPHR1MW

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4057.7	4057.7	4057.7	4057.7	4057.7
1°	4038.7	4033.9	4037.8	4029.5	4046.5
2°	3974.2	3969.3	3969.3	3964.5	3966.9
3°	3853.8	3861.5	3856.7	3846.5	3859.6
4°	3689.6	3698.4	3706.2	3706.6	3708.6
5°	3492.0	3489.6	3524.6	3522.1	3537.7
6°	3266.7	3263.8	3278.9	3304.1	3335.2
7°	3019.1	2983.7	3024.0	3074.9	3116.7
8°	2698.6	2707.9	2735.6	2795.8	2829.3
9°	2426.7	2372.8	2431.6	2503.5	2539.9
10°	2078.1	2034.4	2097.5	2173.3	2201.9
12.5°	1308.1	1270.2	1290.6	1370.2	1382.8
15°	705.0	679.8	688.5	729.8	743.4
17.5°	359.8	337.0	332.1	358.3	361.2
20°	180.1	174.8	169.5	171.9	169.9
22.5°	83.5	90.8	89.8	85.0	90.8
25°	37.9	43.2	45.6	47.6	52.0
27.5°	23.3	22.3	25.7	27.7	28.2
30°	15.5	15.1	15.5	16.0	16.0
32.5°	11.2	10.7	10.2	10.2	10.7
35°	8.3	8.3	7.3	7.8	7.8
37.5°	5.8	5.8	5.3	5.8	5.8
40°	3.4	3.9	3.9	3.9	4.4
42.5°	1.9	2.4	2.4	2.4	2.4
45°	1.0	1.5	1.5	1.5	1.5
47.5°	0.5	0.5	0.5	1.0	1.0
50°	0.5	0.5	0.5	0.5	0.5
52.5°	0.5	0.0	0.0	0.0	0.5
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)