

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1316723

Luminaire Tested: LDSQA3D17R259740DE010 3LSQPHR1MB

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1316723
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-3)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LDSQA3D17R259740DE010 3LSQPHR1MB
Description: 3in Adjustable LED luminaire with, R25 optic, 4000K CCT AND, 97CRI , 3LSQPHR1MB TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1399.0 lumens
Efficiency: N/A
Efficacy: 66.0 lumens/watt
Spacing Criteria (0/90/45): 0.43 / 0.43 / 0.4
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1316723
CATALOG NUMBER: LDSQA3D17R259740DE010 3LSQPHR1MB

Luminous Intensity Polar Plot



— 0°-180° - - 45°-225° - · - · 90°-270°



TEST NUMBER: P1316723
 CATALOG NUMBER: LDSQA3D17R259740DE010 3LSQPHR1MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	115	113	112	110	113	111	110	108	107	106	105	104	103	102	100	100	99	99	99	99	97
2	112	109	106	104	110	107	105	103	104	102	101	101	100	98	99	97	96	96	96	96	95
3	109	105	102	99	107	104	101	98	101	99	97	99	97	95	97	95	94	94	94	94	93
4	106	101	98	95	105	100	97	95	99	96	94	97	94	93	95	93	92	92	92	92	91
5	104	98	95	92	102	98	94	92	96	93	91	95	92	90	93	91	89	89	89	89	88
6	101	96	92	89	100	95	92	89	94	91	89	93	90	88	91	89	87	87	87	87	86
7	99	93	89	87	98	93	89	87	92	89	86	91	88	86	90	87	86	86	86	86	85
8	97	91	87	85	96	90	87	85	90	86	84	89	86	84	88	86	84	84	84	84	83
9	95	89	85	83	94	88	85	83	88	85	82	87	84	82	86	84	82	82	82	82	81
10	93	87	83	81	92	86	83	81	86	83	81	85	82	80	85	82	80	80	80	80	80

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1305534	1305534	1305534
5°	1183073	1193861	1199670
10°	889384	895715	899860
15°	440378	427255	455712
20°	124371	126423	127798
25°	21568	40780	25597
30°	8432	8690	8929
35°	2628	2880	2880
40°	832	1124	832
45°	609	292	609
50°	322	0	322
55°	360	0	360
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 609 cd/sqm



TEST NUMBER: P1316723

CATALOG NUMBER: LDSQA3D17R259740DE010 3LSQPHR1MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	602.2	43.0
10°-20°	679.1	48.5
20°-30°	105.3	7.5
30°-40°	10.7	0.8
40°-50°	1.4	0.1
50°-60°	0.2	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1386.6	99.1
0°-40°	1397.3	99.9
0°-60°	1399.0	100.0
0°-90°	1399.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1399.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	7580	7580	7580	7580	7580	
5°	6843	6856	6906	6933	6939	596
15°	2470	2452	2396	2504	2556	676
25°	114	168	215	163	135	95
35°	12	14	14	15	14	10
45°	2	1	1	1	2	2
55°	1	0	0	0	1	1
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P1316723
 CATALOG NUMBER: LDSQA3D17R259740DE010 3LSQPHR1MB

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	7580.5	7580.5	7580.5	7580.5	7580.5
1°	7549.3	7559.3	7548.1	7560.6	7559.3
2°	7470.7	7480.7	7467.0	7474.5	7474.5
3°	7309.8	7331.0	7343.5	7352.2	7359.7
4°	7097.8	7121.5	7140.2	7162.6	7162.6
5°	6843.3	6855.8	6905.7	6933.1	6939.3
6°	6540.2	6590.1	6627.5	6682.4	6648.7
7°	6237.0	6278.2	6330.6	6339.3	6363.0
8°	5892.8	5936.4	5985.1	5976.3	5956.4
9°	5473.6	5537.3	5594.6	5575.9	5600.9
10°	5085.7	5124.4	5121.9	5103.2	5145.6
11°	4635.4	4644.1	4595.5	4671.6	4625.4
12°	4101.5	4109.0	4046.6	4121.4	4168.8
13°	3590.0	3572.6	3486.5	3585.1	3644.9
14°	3001.3	3007.5	2897.7	3088.6	3073.6
15°	2469.9	2452.4	2396.3	2503.6	2555.9
17.5°	1316.0	1327.2	1313.5	1367.2	1400.8
20°	678.6	697.3	689.8	712.3	697.3
22.5°	351.8	378.0	385.4	368.0	320.6
25°	113.5	168.4	214.6	163.4	134.7
27.5°	68.6	67.4	104.8	72.3	73.6
30°	42.4	41.2	43.7	43.7	44.9
32.5°	23.7	24.9	23.7	26.2	24.9
35°	12.5	13.7	13.7	15.0	13.7
37.5°	7.5	8.7	8.7	8.7	7.5
40°	3.7	5.0	5.0	3.7	3.7
42.5°	2.5	2.5	2.5	2.5	2.5
45°	2.5	1.2	1.2	1.2	2.5
47.5°	1.2	1.2	0.0	1.2	1.2
50°	1.2	1.2	0.0	1.2	1.2
52.5°	1.2	0.0	0.0	0.0	1.2
55°	1.2	0.0	0.0	0.0	1.2
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1316723
CATALOG NUMBER: LDSQA3D17R259740DE010 3LSQPHR1MB

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)