

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1316280

Luminaire Tested: LDSQA3D05R359740DE010 3LSQCA45R 1MB

Issue Date: 1/29/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1316280  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-77)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LDSQA3D05R359740DE010 3LSQCA45R 1MB  
Description: 3in Adjustable LED luminaire with, R35 optic, 4000K CCT AND, 97CRI , 3LSQCA45R 1MB TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 537.0 lumens  
Efficiency: N/A  
Efficacy: 74.6 lumens/watt  
Spacing Criteria (0/90/45): 4.01 / 0.66 / 1.41  
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 7.2  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1316280  
CATALOG NUMBER: LDSQA3D05R359740DE010 3LSQCA45R 1MB

### Luminous Intensity Polar Plot



— 0°-180°    - - - 45°-225°    ····· 90°-270°



TEST NUMBER: P1316280

CATALOG NUMBER: LDSQA3D05R359740DE010 3LSQCA45R 1MB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	110	106	102	99	107	104	100	97	100	97	94	96	93	91	92	90	89	89	89	89	87
2	100	93	86	81	98	91	85	80	87	83	78	84	80	77	81	78	75	75	75	75	73
3	91	81	73	67	89	79	72	66	76	70	65	74	68	64	71	67	63	63	63	63	61
4	83	71	62	55	80	69	61	55	67	60	54	64	58	53	62	57	52	52	52	52	50
5	75	62	52	46	73	61	52	45	58	51	45	56	50	44	55	49	44	44	44	44	42
6	68	54	45	38	66	53	44	38	51	43	38	50	43	37	48	42	37	37	37	37	35
7	62	48	38	32	60	47	38	32	45	37	32	44	37	31	42	36	31	31	31	31	29
8	57	42	33	27	55	41	33	27	40	32	27	39	32	26	38	31	26	26	26	26	24
9	52	38	29	23	50	37	29	23	36	28	23	35	28	22	34	27	22	22	22	22	20
10	48	34	25	19	46	33	25	19	32	25	19	31	24	19	30	24	19	19	19	19	17

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°	135°	180°
0°	4254	4254	4254	4254	4254
5°	4616	4529	4184	3769	3682
10°	4827	4407	3725	3218	3218
15°	6918	4315	3031	2764	2853
20°	17320	4619	2401	2401	2657
25°	80419	5891	1843	2204	2489
30°	244465	7994	1452	2028	2506
35°	413174	9272	1219	1934	2439
40°	484331	9150	989	1956	2608
45°	510063	6503	828	2119	2825
50°	485491	3885	777	2197	3108
55°	406824	1591	871	2462	3633
60°	227747	344	999	2824	3996
65°	39325	204	978	3179	4523
70°	755	252	1209	3424	5136
75°	665	333	1597	3859	5789
80°	496	496	1884	4364	6744
85°	0	988	3754	4742	7707

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 46°  
 Luminance: 513674 cd/sqm



TEST NUMBER: P1316280

CATALOG NUMBER: LDSQA3D05R359740DE010 3LSQCA45R 1MB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	2.2	0.4
10°-20°	6.3	1.2
20°-30°	32.9	6.1
30°-40°	142.3	26.5
40°-50°	203.0	37.8
50°-60°	125.7	23.4
60°-70°	19.1	3.6
70°-80°	3.6	0.7
80°-90°	1.8	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	41.5	7.7
0°-40°	183.8	34.2
0°-60°	512.5	95.4
0°-90°	537.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	537.0	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	25	25	25	25	25	
5°	27	26	24	22	21	3
15°	39	24	17	16	16	14
25°	423	31	10	12	13	253
35°	1965	44	6	9	12	1180
45°	2094	27	3	9	12	1582
55°	1355	5	3	8	12	1154
65°	96	0	2	8	11	197
75°	1	0	2	6	9	1
85°	0	0	2	2	4	0
90°	0	0	0	0	0	



TEST NUMBER: P1316280

CATALOG NUMBER: LDSQA3D05R359740DE010 3LSQCA45R 1MB

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	45°	67.5°	90°	112.5°
0°	24.7	24.7	24.7	24.7	24.7	24.7	24.7	24.7	24.7	24.7	24.7
2.5°	25.7	25.7	25.7	25.7	25.7	25.7	25.7	25.7	25.7	24.7	24.2
5°	26.7	26.7	26.2	26.2	26.2	26.2	26.2	26.2	25.2	24.2	22.8
7.5°	27.1	27.1	26.7	26.7	26.7	26.7	26.2	25.7	24.7	22.8	21.3
10°	27.6	27.6	27.6	27.6	27.1	26.7	26.2	25.2	23.8	21.3	19.9
12.5°	31.0	31.0	30.5	29.6	28.6	27.6	26.7	24.7	21.8	19.4	17.9
15°	38.8	38.3	37.3	35.9	33.9	31.5	29.6	24.2	19.9	17.0	16.0
17.5°	54.3	53.3	51.9	47.0	42.7	38.3	34.4	24.2	17.9	15.0	14.1
20°	94.5	95.0	84.8	73.2	63.5	52.8	43.1	25.2	16.0	13.1	12.6
22.5°	197.3	189.5	165.3	137.2	104.7	81.0	61.1	27.6	14.1	11.1	11.1
25°	423.2	393.6	335.0	253.0	178.4	126.5	88.7	31.0	12.6	9.7	10.2
27.5°	772.7	746.0	628.2	473.1	314.1	191.0	120.2	35.4	11.1	8.2	9.2
30°	1229.3	1155.7	1002.0	775.6	525.0	292.3	161.4	40.2	9.2	7.3	8.7
31°	1371.9	1337.9	1150.8	897.3	615.2	347.1	178.9	41.7	8.7	7.3	8.2
32°	1541.0	1480.9	1313.2	1030.6	706.8	396.0	199.7	43.1	8.2	6.3	8.2
33°	1692.3	1634.1	1430.0	1147.9	799.4	451.8	222.0	43.6	7.3	6.3	7.8
34°	1851.3	1771.8	1569.6	1270.5	894.4	511.9	242.4	44.1	6.8	5.8	7.8
35°	1965.2	1885.7	1689.9	1367.5	976.3	565.2	265.6	44.1	6.3	5.8	7.3
36°	2053.4	1983.6	1793.6	1467.4	1057.7	613.2	284.1	44.1	5.3	5.3	7.3
37°	2114.0	2047.6	1863.4	1553.2	1119.8	655.9	300.5	44.1	4.8	5.3	7.3
38°	2143.6	2088.3	1930.8	1615.7	1179.9	689.3	313.6	43.1	4.4	4.8	6.8
39°	2156.2	2111.1	1972.0	1668.5	1225.0	718.4	323.3	42.2	3.9	4.8	6.8
40°	2154.3	2115.0	1995.3	1704.9	1261.3	738.3	328.7	40.7	3.4	4.4	6.8
41°	2143.1	2109.2	2007.4	1735.9	1283.2	751.9	330.1	39.3	2.9	4.4	6.3
42°	2130.5	2099.5	2011.3	1752.4	1297.2	756.2	326.2	37.3	2.9	3.9	6.3
43°	2117.4	2088.8	2011.3	1757.7	1300.6	753.3	319.9	33.9	2.4	3.9	6.3
44°	2106.8	2079.6	2005.0	1756.3	1293.3	742.2	308.3	30.1	1.9	3.9	6.3
45°	2094.2	2067.5	1996.7	1747.1	1279.3	723.3	293.8	26.7	1.5	3.4	6.3
46°	2071.9	2051.0	1982.2	1728.2	1257.0	697.1	275.3	24.2	1.0	3.4	5.8
47°	2028.7	2010.8	1954.1	1700.0	1227.4	666.1	256.4	21.8	1.0	3.4	5.8
48°	1941.9	1941.5	1897.8	1647.7	1180.4	627.3	236.6	19.4	1.0	3.4	5.8
49°	1858.1	1849.3	1795.1	1555.6	1113.0	580.7	215.7	17.5	0.5	3.4	5.8
50°	1812.0	1793.1	1703.9	1447.0	1026.7	516.3	193.4	14.5	0.5	2.9	5.8
51°	1764.0	1736.9	1631.7	1349.1	923.9	454.2	169.2	11.6	0.5	2.9	5.3
52°	1677.3	1651.6	1533.8	1255.5	824.1	390.7	145.9	9.7	0.5	2.9	5.8
53°	1583.7	1546.9	1418.9	1152.8	736.3	334.5	122.2	8.2	0.5	2.9	5.3
54°	1465.9	1449.4	1302.5	1026.7	633.6	280.2	100.3	6.8	0.5	2.9	5.3
55°	1354.9	1330.7	1178.0	897.8	540.5	229.8	83.9	5.3	0.5	2.9	5.3
56°	1213.3	1177.0	1034.0	779.5	446.0	185.2	70.8	4.4	0.5	2.9	5.3
57°	1044.7	1005.9	892.9	648.1	350.0	141.1	59.1	3.4	0.5	2.9	5.3
58°	883.7	850.3	729.1	500.3	263.7	97.9	49.0	2.4	0.5	2.4	5.3
59°	763.5	726.7	606.4	384.9	183.2	72.2	36.8	1.9	0.5	2.9	5.3
60°	661.2	613.7	488.2	298.1	130.9	51.9	27.1	1.0	1.0	2.9	5.3
62.5°	381.0	336.4	233.2	121.2	53.8	26.7	13.1	0.5	1.0	2.9	5.3
65°	96.5	85.8	55.7	26.2	15.0	9.2	4.8	0.5	1.0	2.4	4.8



TEST NUMBER: P1316280

CATALOG NUMBER: LDSQA3D05R359740DE010 3LSQCA45R 1MB

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	45°	67.5°	90°	112.5°
67.5°	3.4	3.4	3.4	2.9	2.4	1.9	1.0	0.5	1.0	2.4	4.8
70°	1.5	1.5	1.5	1.0	1.0	0.5	0.5	0.5	1.0	2.4	4.4
72.5°	1.0	1.0	1.0	1.0	0.5	0.5	0.5	0.5	1.5	2.4	3.9
75°	1.0	1.0	1.0	1.0	0.5	0.5	0.5	0.5	1.5	2.4	3.9
77.5°	1.0	1.0	0.5	0.5	0.5	0.5	0.5	0.5	1.5	1.9	3.4
80°	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5	1.5	1.9	2.9
82.5°	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5	1.5	1.9	2.4
85°	0.0	0.0	0.0	0.0	0.0	0.5	0.0	0.5	1.5	1.9	1.9
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.5	1.5	1.9	1.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1316280  
 CATALOG NUMBER: LDSQA3D05R359740DE010 3LSQCA45R 1MB

**CANDELA DISTRIBUTION (continued):**

	135°	157.5°	180°
0°	24.7	24.7	24.7
2.5°	23.3	23.3	23.3
5°	21.8	21.8	21.3
7.5°	20.4	19.9	19.9
10°	18.4	18.4	18.4
12.5°	17.0	17.0	17.0
15°	15.5	16.0	16.0
17.5°	14.1	15.0	15.0
20°	13.1	14.1	14.5
22.5°	12.1	13.1	13.6
25°	11.6	12.6	13.1
27.5°	10.7	12.1	13.1
30°	10.2	11.6	12.6
31°	10.2	11.6	12.1
32°	9.7	11.6	12.1
33°	9.7	11.6	12.1
34°	9.7	11.1	12.1
35°	9.2	11.1	11.6
36°	9.2	11.1	11.6
37°	9.2	11.1	12.1
38°	9.2	11.1	11.6
39°	8.7	11.1	11.6
40°	8.7	11.1	11.6
41°	8.7	11.1	11.6
42°	8.7	11.1	11.6
43°	8.7	11.1	11.6
44°	8.7	10.7	11.6
45°	8.7	10.7	11.6
46°	8.7	11.1	11.6
47°	8.7	11.1	12.1
48°	8.7	10.7	11.6
49°	8.2	10.7	11.6
50°	8.2	10.7	11.6
51°	8.2	11.1	12.1
52°	8.2	11.1	12.1
53°	8.2	11.1	12.1
54°	8.2	11.1	11.6
55°	8.2	11.1	12.1
56°	8.2	11.1	11.6
57°	8.2	11.1	11.6
58°	8.2	10.7	11.6
59°	8.2	10.7	11.6
60°	8.2	10.7	11.6
62.5°	7.8	10.7	11.6
65°	7.8	10.2	11.1



TEST NUMBER: P1316280  
CATALOG NUMBER: LDSQA3D05R359740DE010 3LSQCA45R 1MB

**CANDELA DISTRIBUTION (continued):**

	135°	157.5°	180°
67.5°	7.3	10.2	10.7
70°	6.8	9.7	10.2
72.5°	6.3	9.2	9.7
75°	5.8	8.2	8.7
77.5°	4.8	7.3	8.2
80°	4.4	6.3	6.8
82.5°	3.4	5.3	5.8
85°	2.4	3.9	3.9
87.5°	1.0	1.9	1.9
90°	0.0	0.0	0.0

(END OF REPORT)