

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1317139

Luminaire Tested: LDSQA3D05R159827DE010 3LSQCDR1MMS

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1317139
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-21)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LDSQA3D05R159827DE010 3LSQCDR1MMS
Description: 3in Adjustable LED luminaire with, R15 optic, 2700K CCT AND, 98CRI , 3LSQCDR1MMS TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 436.0 lumens
Efficiency: N/A
Efficacy: 60.6 lumens/watt
Spacing Criteria (0/90/45): 0.29 / 0.29 / 0.29
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1317139
CATALOG NUMBER: LDSQA3D05R159827DE010 3LSQCDR1MMS

Luminous Intensity Polar Plot



— 0°-180° - - - 45°-225° ····· 90°-270°



TEST NUMBER: P1317139

CATALOG NUMBER: LDSQA3D05R159827DE010 3LSQCDR1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	116	114	112	111	113	112	110	109	108	107	106	104	103	102	101	100	100	100	100	100	98
2	113	109	107	105	111	108	106	104	105	103	101	102	101	99	99	98	97	97	98	97	96
3	110	106	103	100	108	105	102	100	102	100	98	100	98	97	98	96	95	98	96	95	94
4	107	103	99	97	106	102	99	96	100	97	95	98	96	94	96	95	93	96	95	93	92
5	105	100	97	94	104	99	96	94	98	95	93	96	94	92	95	93	91	95	93	91	90
6	103	97	94	92	102	97	94	91	96	93	91	94	92	90	93	91	90	93	91	90	89
7	101	95	92	90	100	95	92	89	94	91	89	93	90	88	92	90	88	92	90	88	87
8	99	93	90	88	98	93	90	88	92	89	87	91	89	87	90	88	87	90	88	87	86
9	97	91	88	86	96	91	88	86	90	88	86	90	87	85	89	87	85	89	87	85	84
10	95	90	87	84	95	90	86	84	89	86	84	88	86	84	88	85	84	88	85	84	83

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	672788	672788	672788
5°	547772	549570	548498
10°	255534	257825	254555
15°	80234	80912	80430
20°	31798	33063	30772
25°	12846	15525	12390
30°	5151	7060	4872
35°	1514	3112	1451
40°	472	1169	382
45°	73	244	73
50°	0	80	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°

Vertical Angle: 45°

Luminance: 244 cd/sqm



TEST NUMBER: P1317139

CATALOG NUMBER: LDSQA3D05R159827DE010 3LSQCDR1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	244.6	56.1
10°-20°	146.3	33.6
20°-30°	36.9	8.5
30°-40°	7.5	1.7
40°-50°	0.7	0.2
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	427.8	98.1
0°-40°	435.3	99.8
0°-60°	436.0	100.0
0°-90°	436.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	436.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3906	3906	3906	3906	3906	
5°	3168	3163	3179	3171	3173	244
15°	450	454	454	447	451	146
25°	68	74	82	72	65	35
35°	7	10	15	9	7	6
45°	0	1	1	1	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P1317139

CATALOG NUMBER: LDSQA3D05R159827DE010 3LSQCDR1MMS

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3906.5	3906.5	3906.5	3906.5	3906.5
1°	3871.4	3884.5	3877.6	3883.1	3876.9
2°	3787.6	3805.2	3799.6	3797.9	3802.7
3°	3640.0	3660.3	3659.6	3654.5	3646.2
4°	3438.6	3430.3	3443.1	3441.7	3427.5
5°	3168.5	3162.7	3178.9	3171.0	3172.7
6°	2838.2	2863.7	2858.2	2858.9	2865.4
7°	2483.3	2497.1	2508.8	2518.5	2505.0
8°	2157.4	2154.0	2155.0	2166.0	2128.8
9°	1792.6	1813.9	1800.2	1778.1	1792.2
10°	1461.2	1474.3	1474.3	1455.0	1455.6
11°	1164.9	1175.6	1168.0	1172.9	1142.5
12°	939.0	912.5	906.3	911.1	910.8
13°	717.0	718.7	717.0	716.6	713.2
14°	562.1	571.1	567.3	558.0	553.8
15°	450.0	453.8	453.8	447.3	451.1
17.5°	270.4	274.9	275.9	271.4	271.4
20°	173.5	175.5	180.4	173.8	167.9
22.5°	106.9	111.4	119.7	110.0	105.2
25°	67.6	73.8	81.7	72.4	65.2
27.5°	42.4	47.6	54.5	45.5	41.0
30°	25.9	29.3	35.5	28.6	24.5
32.5°	14.5	17.2	22.4	16.6	13.8
35°	7.2	9.7	14.8	9.3	6.9
37.5°	4.1	5.2	9.3	4.5	3.8
40°	2.1	2.8	5.2	2.8	1.7
42.5°	0.7	1.4	2.1	1.4	0.7
45°	0.3	0.7	1.0	0.7	0.3
47.5°	0.0	0.0	0.3	0.0	0.0
50°	0.0	0.0	0.3	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1317139

CATALOG NUMBER: LDSQA3D05R159827DE010 3LSQCDR1MMS

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)