

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1316921

Luminaire Tested: LDSQA3D20R359740D010 3LSQPHRLP1MW

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1316921
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-15)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LDSQA3D20R359740D010 3LSQPHRLP1MW
Description: 3in Adjustable LED luminaire with, R35 optic, 4000K CCT AND, 97CRI , 3LSQPHRLP1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1075.0 lumens
Efficiency: N/A
Efficacy: 37.3 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.68 / 0.73
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1316921

CATALOG NUMBER: LDSQA3D20R359740D010 3LSQPHRLP1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1316921

CATALOG NUMBER: LDSQA3D20R359740D010 3LSQPHRLP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	111	107	104	101	109	105	102	99	101	99	96		97	95	93		94
2	104	98	92	88	101	96	91	87	92	88	85		89	86	83		86
3	97	89	83	78	95	88	82	77	85	80	76		82	78	75		80
4	92	82	75	70	90	81	75	70	79	73	69		77	72	68		75
5	86	76	69	64	84	75	69	64	73	68	63		72	67	63		70
6	82	71	64	59	80	70	64	59	69	63	58		67	62	58		66
7	77	66	60	55	76	66	59	54	64	58	54		63	58	54		62
8	73	62	56	51	72	62	55	51	61	55	51		60	54	50		59
9	70	59	52	48	68	58	52	48	57	52	47		56	51	47		55
10	66	56	49	45	65	55	49	45	54	49	45		53	48	45		53

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	223769	223769	223769
5°	216412	216706	216412
10°	196599	196320	195463
15°	166887	166299	164854
20°	134359	132563	131354
25°	103869	100752	100752
30°	77458	74853	74197
35°	55736	55042	53676
40°	39006	40108	37523
45°	29105	30689	28302
50°	24998	24998	24542
55°	23570	22610	23090
60°	24249	21976	23112
65°	25999	22006	25347
70°	30464	23062	29659
75°	38128	23955	36997
80°	48697	25985	43837
85°	38730	25886	38730

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 80°

Luminance: 48697 cd/sqm

TEST NUMBER: P1316921

CATALOG NUMBER: LDSQA3D20R359740D010 3LSQPHRLP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	115.4	10.7
10°-20°	257.5	24.0
20°-30°	245.9	22.9
30°-40°	165.2	15.4
40°-50°	97.0	9.0
50°-60°	69.4	6.5
60°-70°	57.7	5.4
70°-80°	47.3	4.4
80°-90°	19.5	1.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	618.9	57.6
0°-40°	784.1	72.9
0°-60°	950.4	88.4
0°-90°	1075.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1075.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1299	1299	1299	1299	1299	
5°	1252	1255	1254	1252	1252	115
15°	936	938	933	926	925	259
25°	547	540	530	530	530	251
35°	265	265	262	257	255	168
45°	120	123	126	120	116	96
55°	78	77	75	75	77	71
65°	64	57	54	57	62	64
75°	57	44	36	44	56	59
85°	20	21	13	21	20	22
90°	0	0	0	0	0	

TEST NUMBER: P1316921

CATALOG NUMBER: LDSQA3D20R359740D010 3LSQPHRLP1MW

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1299.3	1299.3	1299.3	1299.3	1299.3
1°	1297.7	1299.3	1299.3	1297.7	1297.7
2°	1291.1	1294.4	1292.8	1291.1	1292.8
3°	1282.9	1286.2	1284.6	1282.9	1281.3
4°	1269.8	1273.1	1271.5	1268.2	1268.2
5°	1251.8	1255.1	1253.5	1251.8	1251.8
6°	1233.8	1237.1	1233.8	1230.6	1230.6
7°	1209.3	1214.2	1210.9	1207.7	1206.0
8°	1181.5	1186.4	1183.1	1181.5	1178.2
9°	1153.7	1156.9	1152.0	1152.0	1152.0
10°	1124.2	1125.8	1122.6	1117.7	1117.7
11°	1091.5	1089.8	1088.2	1084.9	1081.7
12°	1055.5	1055.5	1050.6	1047.3	1045.7
13°	1017.8	1016.2	1012.9	1009.7	1009.7
14°	978.6	978.6	975.3	968.7	970.4
15°	936.0	937.7	932.7	926.2	924.6
17.5°	839.5	836.2	828.0	823.1	818.2
20°	733.1	731.5	723.3	718.4	716.7
22.5°	634.9	633.3	625.1	620.2	623.5
25°	546.6	540.0	530.2	530.2	530.2
27.5°	464.7	456.6	450.0	446.7	450.0
30°	389.5	382.9	376.4	374.7	373.1
32.5°	322.4	319.1	315.8	310.9	310.9
35°	265.1	265.1	261.8	256.9	255.3
37.5°	216.0	217.6	216.0	211.1	209.5
40°	173.5	176.7	178.4	173.5	166.9
42.5°	142.4	147.3	150.5	142.4	137.5
45°	119.5	122.7	126.0	119.5	116.2
47.5°	104.7	106.4	108.0	103.1	101.5
50°	93.3	93.3	93.3	91.6	91.6
52.5°	85.1	85.1	83.5	81.8	81.8
55°	78.5	76.9	75.3	75.3	76.9
57.5°	73.6	72.0	68.7	70.4	72.0
60°	70.4	67.1	63.8	65.5	67.1
62.5°	65.5	62.2	58.9	60.5	63.8
65°	63.8	57.3	54.0	57.3	62.2
67.5°	62.2	54.0	49.1	54.0	60.5
70°	60.5	50.7	45.8	50.7	58.9
72.5°	58.9	47.5	40.9	47.5	57.3
75°	57.3	44.2	36.0	44.2	55.6
77.5°	54.0	40.9	31.1	40.9	50.7
80°	49.1	37.6	26.2	36.0	44.2
82.5°	36.0	31.1	21.3	31.1	32.7
85°	19.6	21.3	13.1	21.3	19.6
87.5°	1.6	3.3	3.3	9.8	6.5



TEST NUMBER: P1316921
CATALOG NUMBER: LDSQA3D20R359740D010 3LSQPHRLP1MW

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)