

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1317337

Luminaire Tested: LDSQA3D09R309827DE010 3LSQPHR1MW

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1317337
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-4)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LDSQA3D09R309827DE010 3LSQPHR1MW
Description: 3in Adjustable LED luminaire with, R30 optic, 2700K CCT AND, 98CRI , 3LSQPHR1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 591.0 lumens
Efficiency: N/A
Efficacy: 53.7 lumens/watt
Spacing Criteria (0/90/45): 0.5 / 0.49 / 0.46
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1317337
CATALOG NUMBER: LDSQA3D09R309827DE010 3LSQPHR1MW

Luminous Intensity Polar Plot





TEST NUMBER: P1317337

CATALOG NUMBER: LDSQA3D09R309827DE010 3LSQPHR1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	100
1	115	113	111	110	113	111	109	108	107	106	105	103	103	102	100	99	99	99	99	97
2	112	108	105	103	110	107	104	102	104	101	100	101	99	98	98	97	96	96	96	94
3	108	104	101	98	107	103	100	97	100	98	96	98	96	94	96	94	93	96	94	92
4	105	100	97	94	104	99	96	93	97	94	92	95	93	91	94	92	90	94	92	89
5	102	97	93	90	101	96	93	90	95	91	89	93	90	88	92	89	88	92	89	87
6	100	94	90	87	99	93	90	87	92	89	86	91	88	86	90	87	85	90	87	84
7	97	91	87	84	96	91	87	84	90	86	84	88	86	83	88	85	83	88	85	82
8	95	89	85	82	94	88	84	82	87	84	82	86	83	81	86	83	81	86	83	80
9	92	86	82	80	92	86	82	80	85	82	79	84	81	79	84	81	79	84	81	78
10	90	84	80	78	90	84	80	78	83	80	77	82	79	77	82	79	77	82	79	76

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	420068	420068	420068
5°	409243	406425	403088
10°	345369	334772	329333
15°	208127	202315	206041
20°	70598	81521	94039
25°	12979	20333	24019
30°	4455	4972	5568
35°	1282	1598	1724
40°	337	562	450
45°	122	122	122
50°	134	0	134
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 52.5°

Luminance: 141 cd/sqm



TEST NUMBER: P1317337

CATALOG NUMBER: LDSQA3D09R309827DE010 3LSQPHR1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	210.9	35.7
10°-20°	308.2	52.2
20°-30°	65.2	11.0
30°-40°	6.0	1.0
40°-50°	0.6	0.1
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	584.4	98.9
0°-40°	590.4	99.9
0°-60°	591.0	100.0
0°-90°	591.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	591.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2439	2439	2439	2439	2439	
5°	2367	2363	2351	2344	2332	214
15°	1167	1163	1135	1161	1156	308
25°	68	76	107	126	126	50
35°	6	8	8	9	8	5
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P1317337

CATALOG NUMBER: LDSQA3D09R309827DE010 3LSQPHR1MW

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2439.1	2439.1	2439.1	2439.1	2439.1
1°	2439.6	2437.0	2433.5	2438.6	2435.0
2°	2434.5	2428.4	2423.3	2428.4	2426.9
3°	2419.2	2414.1	2410.5	2413.1	2413.1
4°	2396.3	2390.7	2387.6	2388.1	2380.5
5°	2367.2	2362.7	2350.9	2343.8	2331.6
6°	2324.4	2313.2	2299.0	2287.2	2271.4
7°	2266.4	2249.0	2228.6	2208.3	2188.4
8°	2173.1	2165.0	2137.4	2123.7	2103.8
9°	2085.5	2065.6	2036.0	2013.6	2002.9
10°	1974.9	1945.4	1914.3	1896.4	1883.2
11°	1844.0	1813.9	1788.9	1762.9	1742.6
12°	1690.1	1664.6	1636.1	1618.8	1594.8
13°	1507.7	1504.1	1472.0	1466.4	1463.3
14°	1351.3	1337.0	1305.4	1314.1	1316.1
15°	1167.3	1163.2	1134.7	1161.2	1155.6
17.5°	731.2	732.7	750.5	792.3	805.6
20°	385.2	396.9	444.8	495.3	513.1
22.5°	155.9	181.9	230.8	265.0	287.9
25°	68.3	76.4	107.0	125.9	126.4
27.5°	38.7	39.2	51.5	53.5	54.5
30°	22.4	22.9	25.0	26.5	28.0
32.5°	12.2	13.2	13.8	15.8	15.8
35°	6.1	7.6	7.6	9.2	8.2
37.5°	3.6	4.1	4.6	4.6	4.1
40°	1.5	2.0	2.5	2.5	2.0
42.5°	0.5	1.0	1.0	1.0	1.5
45°	0.5	0.5	0.5	0.5	0.5
47.5°	0.5	0.5	0.0	0.5	0.5
50°	0.5	0.0	0.0	0.0	0.5
52.5°	0.5	0.0	0.0	0.0	0.5
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1317337
CATALOG NUMBER: LDSQA3D09R309827DE010 3LSQPHR1MW

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)