

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1317026

Luminaire Tested: LDSQA3D02R259827DE010 3LSQPHR1MB

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1317026
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-3)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LDSQA3D02R259827DE010 3LSQPHR1MB
Description: 3in Adjustable LED luminaire with, R25 optic, 2700K CCT AND, 98CRI , 3LSQPHR1MB TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 187.0 lumens
Efficiency: N/A
Efficacy: 51.9 lumens/watt
Spacing Criteria (0/90/45): 0.43 / 0.43 / 0.4
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1317026
CATALOG NUMBER: LDSQA3D02R259827DE010 3LSQPHR1MB

Luminous Intensity Polar Plot



— 0°-180° - - 45°-225° - · - · 90°-270°



TEST NUMBER: P1317026
 CATALOG NUMBER: LDSQA3D02R259827DE010 3LSQPHR1MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	115	113	112	110	113	111	110	108	107	106	105	104	103	102	100	100	99	99	99	99	97
2	112	109	106	104	110	107	105	103	104	102	101	101	100	98	99	97	96	96	96	96	95
3	109	105	102	99	107	104	101	98	101	99	97	99	97	95	97	95	94	94	94	94	93
4	106	101	98	95	105	100	97	95	99	96	94	97	94	93	95	93	92	92	92	92	91
5	104	98	95	92	102	98	94	92	96	93	91	95	92	90	93	91	89	89	89	89	88
6	101	96	92	89	100	95	92	89	94	91	89	93	90	88	91	89	87	87	87	87	86
7	99	93	89	87	98	93	89	87	92	89	86	91	88	86	90	87	86	86	86	86	85
8	97	91	87	85	96	90	87	85	90	86	84	89	86	84	88	85	84	84	84	84	83
9	95	89	85	83	94	88	85	83	88	85	82	87	84	82	86	84	82	82	82	82	81
10	93	87	83	81	92	86	83	81	86	83	81	85	82	80	85	82	80	80	80	80	80

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	174513	174513	174513
5°	158134	159586	160364
10°	118883	119722	120282
15°	58856	57109	60907
20°	16623	16898	17081
25°	2888	5454	3420
30°	1134	1153	1193
35°	357	378	378
40°	112	157	112
45°	73	49	73
50°	54	0	54
55°	60	0	60
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 73 cd/sqm



TEST NUMBER: P1317026

CATALOG NUMBER: LDSQA3D02R259827DE010 3LSQPHR1MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	80.5	43.0
10°-20°	90.8	48.5
20°-30°	14.1	7.5
30°-40°	1.4	0.8
40°-50°	0.2	0.1
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	185.3	99.1
0°-40°	186.8	99.9
0°-60°	187.0	100.0
0°-90°	187.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	187.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1013	1013	1013	1013	1013	
5°	915	916	923	927	928	80
15°	330	328	320	335	342	90
25°	15	22	29	22	18	13
35°	2	2	2	2	2	1
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P1317026
 CATALOG NUMBER: LDSQA3D02R259827DE010 3LSQPHR1MB

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1013.3	1013.3	1013.3	1013.3	1013.3
1°	1009.1	1010.4	1008.9	1010.6	1010.4
2°	998.6	999.9	998.1	999.1	999.1
3°	977.1	979.9	981.6	982.8	983.8
4°	948.7	951.9	954.4	957.4	957.4
5°	914.7	916.4	923.1	926.7	927.6
6°	874.2	880.9	885.9	893.2	888.7
7°	833.7	839.2	846.2	847.4	850.5
8°	787.7	793.5	800.0	798.8	796.2
9°	731.6	740.1	747.8	745.3	748.7
10°	679.8	685.0	684.6	682.1	687.8
11°	619.6	620.8	614.3	624.4	618.3
12°	548.2	549.2	540.9	550.9	557.2
13°	479.9	477.5	466.0	479.2	487.2
14°	401.2	402.0	387.3	412.8	410.8
15°	330.1	327.8	320.3	334.6	341.6
17.5°	175.9	177.4	175.6	182.7	187.2
20°	90.7	93.2	92.2	95.2	93.2
22.5°	47.0	50.5	51.5	49.2	42.9
25°	15.2	22.5	28.7	21.8	18.0
27.5°	9.2	9.0	14.0	9.7	9.8
30°	5.7	5.5	5.8	5.8	6.0
32.5°	3.2	3.3	3.2	3.5	3.3
35°	1.7	1.8	1.8	2.0	1.8
37.5°	1.0	1.2	1.2	1.2	1.0
40°	0.5	0.7	0.7	0.5	0.5
42.5°	0.3	0.3	0.3	0.3	0.3
45°	0.3	0.2	0.2	0.2	0.3
47.5°	0.2	0.2	0.0	0.2	0.2
50°	0.2	0.2	0.0	0.2	0.2
52.5°	0.2	0.0	0.0	0.0	0.2
55°	0.2	0.0	0.0	0.0	0.2
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1317026
CATALOG NUMBER: LDSQA3D02R259827DE010 3LSQPHR1MB

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)