

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1317082

Luminaire Tested: LDSQA3D02R459827DE010 3LSQCA45R 1MW

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1317082
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-84)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LDSQA3D02R459827DE010 3LSQCA45R 1MW
Description: 3in Adjustable LED luminaire with, R45 optic, 2700K CCT AND, 98CRI , 3LSQCA45R 1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 201.0 lumens
Efficiency: N/A
Efficacy: 55.8 lumens/watt
Spacing Criteria (0/90/45): 3.81 / 0.82 / 1.83
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1317082
CATALOG NUMBER: LDSQA3D02R459827DE010 3LSQCA45R 1MW

Luminous Intensity Polar Plot



— 0°-180° - - - 45°-225° ····· 90°-270°



TEST NUMBER: P1317082

CATALOG NUMBER: LDSQA3D02R459827DE010 3LSQCA45R 1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	110	106	102	99	107	104	100	97	99	97	94	96	93	91	92	90	88	88	88	88	86
2	100	93	86	81	98	91	85	80	87	83	78	84	80	77	81	78	75	75	75	75	73
3	91	81	73	67	89	80	72	66	77	70	65	74	69	64	71	67	63	63	63	63	61
4	83	71	62	56	81	70	62	55	67	60	55	65	59	54	63	58	53	53	53	53	51
5	76	63	53	47	73	61	53	46	59	52	46	57	51	45	55	50	45	45	45	45	43
6	69	55	46	39	67	54	46	39	52	45	39	51	44	39	49	43	38	38	38	38	36
7	63	49	40	34	61	48	40	33	47	39	33	45	38	33	44	37	33	33	33	33	31
8	58	44	35	29	56	43	35	29	42	34	29	40	33	28	39	33	28	28	28	28	26
9	53	39	31	25	52	39	30	25	38	30	25	36	29	25	35	29	24	24	24	24	22
10	49	36	27	22	48	35	27	22	34	27	21	33	26	21	32	26	21	21	21	21	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°	135°	180°
0°	1998	1998	1998	1998	1998
5°	2386	2213	1988	1833	1833
10°	3812	2588	1854	1749	1749
15°	9468	3459	1694	1623	1694
20°	24962	5168	1466	1558	1649
25°	50110	7677	1254	1444	1615
30°	73879	10281	1014	1412	1651
35°	93202	12047	883	1388	1703
40°	99438	12163	787	1461	1821
45°	103318	10156	731	1583	1973
50°	103153	7073	723	1688	2224
55°	87676	3153	751	1892	2432
60°	58935	620	758	2101	2790
65°	15649	285	734	2282	3179
70°	403	352	755	2518	3575
75°	333	333	799	2662	4059
80°	298	496	793	2777	4661
85°	395	593	1383	2964	4545

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 10°
 Vertical Angle: 47.5°
 Luminance: 105971 cd/sqm



TEST NUMBER: P1317082

CATALOG NUMBER: LDSQA3D02R459827DE010 3LSQCA45R 1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1.2	0.6
10°-20°	5.7	2.8
20°-30°	23.4	11.6
30°-40°	49.3	24.5
40°-50°	60.8	30.2
50°-60°	45.6	22.7
60°-70°	11.7	5.8
70°-80°	2.4	1.2
80°-90°	1.0	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	30.2	15.0
0°-40°	79.5	39.5
0°-60°	185.8	92.5
0°-90°	201.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	201.0	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	12	12	12	12	12	
5°	14	13	12	11	11	2
15°	53	19	10	9	10	19
25°	264	40	7	8	8	123
35°	443	57	4	7	8	270
45°	424	42	3	6	8	325
55°	292	10	2	6	8	252
65°	38	1	2	6	8	55
75°	0	0	1	4	6	1
85°	0	0	1	2	2	0
90°	0	0	0	0	0	



TEST NUMBER: P1317082

CATALOG NUMBER: LDSQA3D02R459827DE010 3LSQCA45R 1MW

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	45°	67.5°	90°	112.5°
0°	11.6	11.6	11.6	11.6	11.6	11.6	11.6	11.6	11.6	11.6	11.6
2.5°	12.3	12.3	12.3	12.3	12.3	12.3	12.3	12.1	12.0	11.6	11.3
5°	13.8	13.6	13.6	13.6	13.5	13.3	13.3	12.8	12.1	11.5	11.0
7.5°	16.3	16.3	16.1	15.8	15.6	15.3	14.9	13.6	12.1	11.1	10.5
10°	21.8	21.4	20.9	20.6	19.8	18.6	17.8	14.8	12.0	10.6	10.1
12.5°	32.6	33.2	31.6	29.9	27.6	25.4	22.8	16.8	12.0	10.1	9.6
15°	53.1	54.3	51.2	47.8	42.2	36.9	31.9	19.4	11.6	9.5	9.0
17.5°	86.9	88.4	83.0	75.2	66.4	55.8	46.7	23.1	11.3	8.8	8.5
20°	136.2	136.0	125.7	115.9	99.0	83.4	66.3	28.2	10.8	8.0	8.0
22.5°	196.8	197.5	184.8	167.2	143.2	118.1	90.8	34.2	10.1	7.3	7.5
25°	263.7	258.1	243.1	221.7	191.0	156.3	120.4	40.4	9.5	6.6	7.0
27.5°	319.5	314.1	297.0	271.5	238.5	197.3	150.5	46.5	8.6	6.0	6.5
30°	371.5	364.5	344.0	315.2	275.9	231.4	178.7	51.7	7.6	5.1	6.0
32.5°	414.4	408.1	384.6	351.3	308.4	260.6	202.6	55.6	6.6	4.7	5.6
35°	443.3	436.8	415.2	378.5	331.8	281.8	222.1	57.3	5.8	4.2	5.5
37.5°	449.9	446.4	431.0	396.6	347.9	295.5	234.5	56.8	4.8	3.8	5.1
40°	442.3	443.1	435.8	407.2	356.6	301.3	239.7	54.1	4.0	3.5	5.0
42.5°	432.5	434.6	434.1	411.5	360.2	301.6	237.5	48.8	3.2	3.2	4.8
45°	424.2	426.3	429.3	409.7	357.7	297.3	230.7	41.7	2.3	3.0	4.8
47.5°	409.1	411.4	415.7	395.1	345.1	286.2	218.4	33.9	1.7	2.8	4.7
50°	385.0	386.1	385.0	361.9	320.9	268.2	198.5	26.4	1.2	2.7	4.7
52.5°	360.2	357.9	348.3	319.0	282.3	239.8	173.4	18.8	0.8	2.5	4.5
55°	292.0	288.3	281.2	263.2	242.3	204.9	140.2	10.5	0.8	2.5	4.3
57.5°	203.4	205.4	207.9	204.3	194.6	161.4	106.5	4.7	0.8	2.3	4.3
60°	171.1	169.4	169.6	167.2	151.3	117.8	73.2	1.8	0.8	2.2	4.2
62.5°	102.1	103.3	105.5	106.0	90.2	65.8	38.4	0.8	0.8	2.0	4.0
65°	38.4	40.2	35.2	30.6	24.2	17.8	9.0	0.7	1.0	1.8	3.7
67.5°	1.2	1.3	1.7	1.5	1.5	1.3	1.0	0.7	1.0	1.7	3.5
70°	0.8	0.8	0.8	0.8	0.8	0.7	0.7	0.7	0.8	1.5	3.2
72.5°	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.8	1.3	2.8
75°	0.5	0.7	0.5	0.5	0.5	0.5	0.5	0.5	0.8	1.2	2.3
77.5°	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.7	1.0	2.0
80°	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.5	0.7	0.8	1.7
82.5°	0.3	0.3	0.3	0.2	0.3	0.3	0.3	0.3	0.7	0.7	1.3
85°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.3	0.5	0.7	0.8
87.5°	0.0	0.0	0.0	0.0	0.2	0.2	0.2	0.3	0.5	0.5	0.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1317082

CATALOG NUMBER: LDSQA3D02R459827DE010 3LSQCA45R 1MW

CANDELA DISTRIBUTION (continued):

	135°	157.5°	180°
0°	11.6	11.6	11.6
2.5°	11.0	11.0	11.0
5°	10.6	10.6	10.6
7.5°	10.3	10.3	10.3
10°	10.0	10.0	10.0
12.5°	9.6	9.6	9.8
15°	9.1	9.5	9.5
17.5°	8.8	9.1	9.3
20°	8.5	8.8	9.0
22.5°	8.0	8.5	8.8
25°	7.6	8.3	8.5
27.5°	7.3	8.1	8.5
30°	7.1	8.0	8.3
32.5°	6.8	7.8	8.1
35°	6.6	7.8	8.1
37.5°	6.6	7.6	8.1
40°	6.5	7.6	8.1
42.5°	6.5	7.6	8.1
45°	6.5	7.6	8.1
47.5°	6.3	7.6	8.3
50°	6.3	7.8	8.3
52.5°	6.3	7.8	8.3
55°	6.3	7.8	8.1
57.5°	6.1	7.6	8.1
60°	6.1	7.6	8.1
62.5°	5.8	7.5	8.0
65°	5.6	7.3	7.8
67.5°	5.3	7.1	7.5
70°	5.0	6.6	7.1
72.5°	4.5	6.3	6.8
75°	4.0	5.8	6.1
77.5°	3.5	5.1	5.5
80°	2.8	4.3	4.7
82.5°	2.2	3.3	3.5
85°	1.5	2.2	2.3
87.5°	0.7	1.0	1.2
90°	0.0	0.0	0.0

(END OF REPORT)