

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1317221

Luminaire Tested: LDSQA3D05R409827DE010 3LSQCDR1MMS

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1317221
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-26)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LDSQA3D05R409827DE010 3LSQCDR1MMS
Description: 3in Adjustable LED luminaire with, R40 optic, 2700K CCT AND, 98CRI , 3LSQCDR1MMS TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 490.0 lumens
Efficiency: N/A
Efficacy: 68.1 lumens/watt
Spacing Criteria (0/90/45): 0.68 / 0.69 / 0.6
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1317221
CATALOG NUMBER: LDSQA3D05R409827DE010 3LSQCDR1MMS

Luminous Intensity Polar Plot





TEST NUMBER: P1317221
 CATALOG NUMBER: LDSQA3D05R409827DE010 3LSQCDR1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	98	98	98	96
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	94	94	94	92
3	107	102	98	95	105	101	97	94	98	95	93	96	93	91	94	92	90	92	92	92	89
4	103	97	93	90	102	96	92	89	94	91	88	92	90	87	91	88	87	91	88	87	85
5	100	93	89	86	98	93	88	85	91	87	85	89	86	84	88	85	83	88	85	83	82
6	96	90	85	82	95	89	85	82	88	84	81	86	83	81	85	82	80	85	82	80	79
7	93	86	82	79	92	86	81	78	85	81	78	83	80	78	82	80	77	82	80	77	76
8	90	83	79	76	89	83	78	75	82	78	75	81	77	75	80	77	75	80	77	75	73
9	87	80	76	73	86	80	75	73	79	75	72	78	75	72	77	74	72	77	74	72	71
10	85	77	73	70	84	77	73	70	76	72	70	76	72	70	75	72	70	75	72	70	69

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	200674	200674	200674
5°	198934	200196	201146
10°	193277	192910	195935
15°	168135	170845	172931
20°	110350	112495	113961
25°	39336	41635	39145
30°	8571	11594	8651
35°	2754	4794	2691
40°	854	1484	787
45°	73	511	73
50°	0	80	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°
 Vertical Angle: 45°
 Luminance: 511 cd/sqm



TEST NUMBER: P1317221

CATALOG NUMBER: LDSQA3D05R409827DE010 3LSQCDR1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	109.0	22.2
10°-20°	253.8	51.8
20°-30°	113.8	23.2
30°-40°	12.3	2.5
40°-50°	1.1	0.2
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	476.5	97.3
0°-40°	488.8	99.8
0°-60°	490.0	100.0
0°-90°	490.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	490.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1165	1165	1165	1165	1165	
5°	1151	1154	1158	1160	1164	109
15°	943	950	958	964	970	251
25°	207	213	219	223	206	110
35°	13	15	23	15	13	10
45°	0	1	2	1	0	1
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P1317221

CATALOG NUMBER: LDSQA3D05R409827DE010 3LSQCDR1MMS

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1165.2	1165.2	1165.2	1165.2	1165.2
1°	1162.8	1165.2	1167.3	1165.6	1168.0
2°	1161.8	1164.5	1167.6	1165.9	1168.0
3°	1159.0	1162.5	1165.9	1164.9	1167.0
4°	1155.2	1158.0	1163.2	1163.2	1166.3
5°	1150.7	1153.8	1158.0	1159.7	1163.5
6°	1145.9	1147.6	1150.7	1154.2	1159.4
7°	1139.7	1139.7	1143.5	1146.9	1153.8
8°	1131.1	1130.4	1133.1	1137.6	1143.8
9°	1120.4	1118.0	1120.0	1126.6	1135.9
10°	1105.2	1103.1	1103.1	1111.4	1120.4
11°	1085.5	1084.8	1085.2	1093.1	1105.2
12°	1059.0	1059.6	1059.6	1068.6	1083.5
13°	1028.9	1028.6	1031.7	1041.7	1051.7
14°	992.4	994.4	997.5	1006.5	1016.9
15°	943.0	949.9	958.2	963.7	969.9
17.5°	792.9	799.8	811.2	815.7	817.1
20°	602.1	612.1	613.8	622.8	621.8
22.5°	403.7	403.0	404.4	405.4	405.8
25°	207.0	213.2	219.1	222.9	206.0
27.5°	90.1	100.8	108.3	98.3	91.1
30°	43.1	49.0	58.3	49.3	43.5
32.5°	23.5	27.3	36.9	26.9	23.1
35°	13.1	15.2	22.8	14.8	12.8
37.5°	7.6	8.3	12.4	8.3	7.2
40°	3.8	4.8	6.6	4.8	3.5
42.5°	1.4	2.4	3.5	2.4	1.4
45°	0.3	0.7	2.1	0.7	0.3
47.5°	0.0	0.0	1.0	0.0	0.0
50°	0.0	0.0	0.3	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1317221
CATALOG NUMBER: LDSQA3D05R409827DE010 3LSQCDR1MMS

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)