

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1317775

Luminaire Tested: LDSQA3D20R309827D010 3LSQPHR1MW

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1317775
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-4)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LDSQA3D20R309827D010 3LSQPHR1MW
Description: 3in Adjustable LED luminaire with, R30 optic, 2700K CCT AND, 98CRI , 3LSQPHR1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1650.0 lumens
Efficiency: N/A
Efficacy: 60.2 lumens/watt
Spacing Criteria (0/90/45): 0.5 / 0.49 / 0.46
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 27.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1317775
CATALOG NUMBER: LDSQA3D20R309827D010 3LSQPHR1MW

Luminous Intensity Polar Plot





TEST NUMBER: P1317775
 CATALOG NUMBER: LDSQA3D20R309827D010 3LSQPHR1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	115	113	111	110	113	111	109	108	107	106	105	103	103	102	100	99	99	99	99	99	97
2	112	108	105	103	110	107	104	102	104	101	100	101	99	98	98	97	96	96	96	96	94
3	108	104	101	98	107	103	100	97	100	98	96	98	96	94	96	94	93	96	94	93	92
4	105	100	97	94	104	99	96	93	97	94	92	95	93	91	94	92	90	94	92	90	89
5	102	97	93	90	101	96	93	90	95	91	89	93	90	88	92	89	88	92	89	88	87
6	100	94	90	87	99	93	90	87	92	89	86	91	88	86	90	87	85	90	87	85	84
7	97	91	87	84	96	91	87	84	90	86	84	88	86	83	88	85	83	88	85	83	82
8	95	89	85	82	94	88	84	82	87	84	82	86	83	81	86	83	81	86	83	81	80
9	92	86	82	80	92	86	82	80	85	82	79	84	81	79	84	81	79	84	81	79	78
10	90	84	80	78	90	84	80	78	83	80	77	82	79	77	82	79	77	82	79	77	76

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1172767	1172767	1172767
5°	1142567	1134701	1125366
10°	964233	934626	919446
15°	581073	564848	575243
20°	197094	227610	262542
25°	36219	56761	67041
30°	12449	13861	15551
35°	3595	4478	4794
40°	967	1596	1281
45°	341	341	341
50°	375	0	375
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 52.5°
 Luminance: 396 cd/sqm



TEST NUMBER: P1317775

CATALOG NUMBER: LDSQA3D20R309827D010 3LSQPHR1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	588.8	35.7
10°-20°	860.6	52.2
20°-30°	182.1	11.0
30°-40°	16.8	1.0
40°-50°	1.6	0.1
50°-60°	0.1	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1631.5	98.9
0°-40°	1648.3	99.9
0°-60°	1650.0	100.0
0°-90°	1650.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1650.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	6810	6810	6810	6810	6810	
5°	6609	6596	6564	6544	6510	597
15°	3259	3248	3168	3242	3226	860
25°	191	213	299	351	353	139
35°	17	21	21	26	23	14
45°	1	1	1	1	1	1
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P1317775

CATALOG NUMBER: LDSQA3D20R309827D010 3LSQPHR1MW

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	6809.6	6809.6	6809.6	6809.6	6809.6
1°	6811.0	6803.9	6794.0	6808.2	6798.2
2°	6796.8	6779.7	6765.5	6779.7	6775.5
3°	6754.1	6739.9	6730.0	6737.1	6737.1
4°	6690.1	6674.5	6665.9	6667.4	6646.0
5°	6609.0	6596.2	6563.5	6543.6	6509.5
6°	6489.5	6458.3	6418.4	6385.7	6341.6
7°	6327.4	6279.0	6222.1	6165.2	6109.7
8°	6067.1	6044.3	5967.5	5929.1	5873.6
9°	5822.4	5766.9	5684.4	5621.8	5591.9
10°	5513.7	5431.2	5344.4	5294.6	5257.6
11°	5148.1	5064.2	4994.5	4921.9	4865.0
12°	4718.5	4647.4	4567.7	4519.4	4452.5
13°	4209.2	4199.3	4109.7	4094.0	4085.5
14°	3772.5	3732.7	3644.5	3668.7	3674.4
15°	3259.0	3247.6	3168.0	3241.9	3226.3
17.5°	2041.3	2045.6	2095.4	2212.0	2249.0
20°	1075.4	1108.1	1241.9	1382.7	1432.5
22.5°	435.3	507.8	644.4	739.7	803.7
25°	190.6	213.4	298.7	351.4	352.8
27.5°	108.1	109.5	143.7	149.4	152.2
30°	62.6	64.0	69.7	74.0	78.2
32.5°	34.1	37.0	38.4	44.1	44.1
35°	17.1	21.3	21.3	25.6	22.8
37.5°	10.0	11.4	12.8	12.8	11.4
40°	4.3	5.7	7.1	7.1	5.7
42.5°	1.4	2.8	2.8	2.8	4.3
45°	1.4	1.4	1.4	1.4	1.4
47.5°	1.4	1.4	0.0	1.4	1.4
50°	1.4	0.0	0.0	0.0	1.4
52.5°	1.4	0.0	0.0	0.0	1.4
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1317775
CATALOG NUMBER: LDSQA3D20R309827D010 3LSQPHR1MW

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)