

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1317916

Luminaire Tested: LDSQA3D02R309830DE010 3LSQCDR1MB

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1317916
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-24)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LDSQA3D02R309830DE010 3LSQCDR1MB
Description: 3in Adjustable LED luminaire with, R30 optic, 3000K CCT AND, 98CRI , 3LSQCDR1MB TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 230.0 lumens
Efficiency: N/A
Efficacy: 63.9 lumens/watt
Spacing Criteria (0/90/45): 0.51 / 0.51 / 0.46
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1317916
CATALOG NUMBER: LDSQA3D02R309830DE010 3LSQCDR1MB

Luminous Intensity Polar Plot



— 0°-180° - - 45°-225° ···· 90°-270°



TEST NUMBER: P1317916
 CATALOG NUMBER: LDSQA3D02R309830DE010 3LSQCDR1MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	100	97
1	115	113	111	110	113	111	109	108	107	106	105	103	102	101	100	99	99	99	97	97
2	112	108	105	103	109	106	104	102	103	101	99	100	99	97	98	96	95	95	94	94
3	108	104	100	97	106	102	99	97	100	97	95	98	95	94	95	94	92	92	91	91
4	105	100	96	93	103	99	95	92	97	94	91	95	92	90	93	91	89	89	88	88
5	102	96	92	89	101	95	92	89	94	91	88	92	90	87	91	89	87	87	86	86
6	99	93	89	86	98	92	89	86	91	88	85	90	87	85	89	86	84	84	83	83
7	96	90	86	83	95	90	86	83	89	85	83	87	85	82	87	84	82	82	81	81
8	94	88	84	81	93	87	83	81	86	83	80	85	82	80	84	82	80	80	79	79
9	91	85	81	78	91	85	81	78	84	80	78	83	80	78	82	80	78	78	77	77
10	89	83	79	76	88	82	79	76	82	78	76	81	78	76	80	78	76	76	75	75

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	153519	153519	153519
5°	149766	149957	150786
10°	127907	127312	126560
15°	78933	78005	78291
20°	29837	30002	29966
25°	9178	10052	9577
30°	3699	4693	3838
35°	1093	1997	1135
40°	450	809	450
45°	97	268	97
50°	0	54	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°
 Vertical Angle: 45°
 Luminance: 268 cd/sqm



TEST NUMBER: P1317916

CATALOG NUMBER: LDSQA3D02R309830DE010 3LSQCDR1MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	78.6	34.2
10°-20°	116.4	50.6
20°-30°	28.9	12.6
30°-40°	5.4	2.4
40°-50°	0.7	0.3
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	223.9	97.3
0°-40°	229.3	99.7
0°-60°	230.0	100.0
0°-90°	230.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	230.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	891	891	891	891	891	
5°	866	866	867	869	872	79
15°	443	438	438	441	439	117
25°	48	52	53	53	50	28
35°	5	7	10	7	5	4
45°	0	0	1	1	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P1317916

CATALOG NUMBER: LDSQA3D02R309830DE010 3LSQCDR1MB

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	891.4	891.4	891.4	891.4	891.4
1°	891.7	891.0	891.0	889.9	891.9
2°	888.5	887.8	889.0	888.1	890.6
3°	883.7	882.8	884.6	885.1	886.3
4°	876.5	875.8	877.8	878.8	882.2
5°	866.3	866.0	867.4	868.8	872.2
6°	852.4	851.8	852.7	854.5	856.7
7°	832.1	831.1	831.8	832.1	832.7
8°	806.6	805.0	804.1	806.0	807.1
9°	773.7	771.9	769.9	769.2	771.7
10°	731.4	728.8	728.0	726.3	723.7
11°	682.4	680.3	679.7	676.5	675.1
12°	626.3	625.2	626.4	624.5	623.8
13°	572.4	565.6	564.7	561.0	559.0
14°	508.7	502.5	502.3	500.3	503.0
15°	442.7	438.4	437.5	440.9	439.1
17.5°	282.3	285.1	284.4	282.6	279.6
20°	162.8	160.8	163.7	164.4	163.5
22.5°	86.8	87.5	88.0	90.2	91.6
25°	48.3	51.5	52.9	52.8	50.4
27.5°	30.1	32.0	34.7	32.9	30.9
30°	18.6	20.2	23.6	20.4	19.3
32.5°	10.0	12.7	15.2	12.7	10.4
35°	5.2	6.8	9.5	7.0	5.4
37.5°	3.4	3.9	6.1	3.9	3.4
40°	2.0	2.5	3.6	2.5	2.0
42.5°	0.9	1.4	2.0	1.4	0.9
45°	0.4	0.5	1.1	0.7	0.4
47.5°	0.0	0.2	0.5	0.2	0.0
50°	0.0	0.0	0.2	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1317916
CATALOG NUMBER: LDSQA3D02R309830DE010 3LSQCDR1MB

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)