

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1317933

Luminaire Tested: LDSQA3D02R359830DE010 3LSQCDR1MB

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1317933
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-25)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LDSQA3D02R359830DE010 3LSQCDR1MB
Description: 3in Adjustable LED luminaire with, R35 optic, 3000K CCT AND, 98CRI , 3LSQCDR1MB TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 226.0 lumens
Efficiency: N/A
Efficacy: 62.8 lumens/watt
Spacing Criteria (0/90/45): 0.57 / 0.58 / 0.52
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1317933
CATALOG NUMBER: LDSQA3D02R359830DE010 3LSQCDR1MB

Luminous Intensity Polar Plot





TEST NUMBER: P1317933
 CATALOG NUMBER: LDSQA3D02R359830DE010 3LSQCDR1MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	115	113	111	109	113	111	109	107	107	105	104	103	102	101	100	99	98	98	98	98	96
2	111	107	104	102	109	106	103	100	102	100	98	100	98	96	97	96	94	94	94	94	93
3	107	102	99	96	105	101	98	95	99	96	94	96	94	92	94	92	91	91	91	91	89
4	104	98	94	91	102	97	93	90	95	92	89	93	91	88	92	89	87	87	87	87	86
5	100	94	90	87	99	93	90	87	92	88	86	90	87	85	89	86	84	84	84	84	83
6	97	91	86	83	96	90	86	83	89	85	83	88	84	82	86	84	82	82	82	82	80
7	94	88	83	80	93	87	83	80	86	82	80	85	82	79	84	81	79	79	79	79	78
8	91	85	80	77	91	84	80	77	83	80	77	82	79	77	81	79	76	76	76	76	75
9	89	82	78	75	88	81	77	75	81	77	74	80	77	74	79	76	74	74	74	74	73
10	86	79	75	72	85	79	75	72	78	75	72	78	74	72	77	74	72	72	72	72	71

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	116905	116905	116905
5°	113358	114153	114775
10°	103581	105767	107586
15°	74493	77738	78380
20°	37920	39826	39917
25°	14385	14689	14290
30°	5588	6483	5449
35°	1913	3007	1808
40°	652	1169	607
45°	49	390	49
50°	0	54	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°
 Vertical Angle: 45°
 Luminance: 390 cd/sqm



TEST NUMBER: P1317933

CATALOG NUMBER: LDSQA3D02R359830DE010 3LSQCDR1MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	61.4	27.2
10°-20°	114.5	50.7
20°-30°	41.1	18.2
30°-40°	8.0	3.6
40°-50°	0.9	0.4
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	217.1	96.0
0°-40°	225.1	99.6
0°-60°	226.0	100.0
0°-90°	226.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	226.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	679	679	679	679	679	
5°	656	658	660	663	664	61
15°	418	425	436	439	440	111
25°	76	76	77	77	75	40
35°	9	10	14	11	9	7
45°	0	0	2	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P1317933

CATALOG NUMBER: LDSQA3D02R359830DE010 3LSQCDR1MB

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	678.8	678.8	678.8	678.8	678.8
1°	676.8	677.7	677.9	679.1	677.7
2°	673.9	674.5	675.2	676.3	675.6
3°	668.4	669.5	671.1	672.5	672.5
4°	662.5	663.9	665.9	668.4	668.2
5°	655.7	657.5	660.3	663.4	663.9
6°	647.1	649.2	653.9	658.2	658.9
7°	638.0	641.2	645.7	651.9	653.5
8°	627.2	629.7	636.2	643.5	645.3
9°	611.5	615.2	623.5	630.3	631.3
10°	592.3	595.0	604.8	612.0	615.2
11°	567.6	571.6	581.2	588.6	590.7
12°	536.1	541.8	553.1	558.5	560.3
13°	502.1	506.9	515.7	522.3	523.8
14°	463.8	468.4	477.6	482.9	481.7
15°	417.8	424.8	436.0	439.1	439.6
17.5°	308.6	313.1	323.1	327.9	331.3
20°	206.9	211.2	217.3	220.5	217.8
22.5°	125.8	129.4	132.6	132.5	131.6
25°	75.7	76.4	77.3	76.8	75.2
27.5°	44.2	46.2	48.9	47.1	44.4
30°	28.1	29.7	32.6	29.5	27.4
32.5°	14.9	18.8	21.8	17.7	15.6
35°	9.1	10.4	14.3	10.6	8.6
37.5°	5.5	6.4	9.0	6.3	5.0
40°	2.9	4.1	5.2	3.8	2.7
42.5°	0.9	2.0	2.9	1.8	0.9
45°	0.2	0.5	1.6	0.5	0.2
47.5°	0.0	0.0	0.7	0.2	0.0
50°	0.0	0.0	0.2	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1317933
CATALOG NUMBER: LDSQA3D02R359830DE010 3LSQCDR1MB

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)