

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1318097

Luminaire Tested: LDSQA3D05R409830DE010 3LSQCDR1MMS

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1318097
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-26)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LDSQA3D05R409830DE010 3LSQCDR1MMS
Description: 3in Adjustable LED luminaire with, R40 optic, 3000K CCT AND, 98CRI , 3LSQCDR1MMS TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 526.0 lumens
Efficiency: N/A
Efficacy: 73.1 lumens/watt
Spacing Criteria (0/90/45): 0.68 / 0.69 / 0.6
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1318097
CATALOG NUMBER: LDSQA3D05R409830DE010 3LSQCDR1MMS

Luminous Intensity Polar Plot





TEST NUMBER: P1318097

CATALOG NUMBER: LDSQA3D05R409830DE010 3LSQCDR1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	98	98	98	96
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	94	94	94	92
3	107	102	98	95	105	101	97	94	98	95	93	96	93	91	94	92	90	92	92	92	89
4	103	97	93	90	102	96	92	89	94	91	88	92	90	87	91	88	87	88	88	87	85
5	100	93	89	86	98	93	88	85	91	87	85	89	86	84	88	85	83	88	85	83	82
6	96	90	85	82	95	89	85	82	88	84	81	86	83	81	85	82	80	85	82	80	79
7	93	86	82	79	92	86	81	78	85	81	78	83	80	78	82	80	77	82	80	77	76
8	90	83	79	76	89	83	78	75	82	78	75	81	77	75	80	77	75	80	77	75	73
9	87	80	76	73	86	80	75	73	79	75	72	78	75	72	77	74	72	77	74	72	71
10	85	77	73	70	84	77	73	70	76	72	70	76	72	70	75	72	70	75	72	70	69

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	215416	215416	215416
5°	213559	214908	215928
10°	207477	207092	210328
15°	180491	183397	185644
20°	118451	120760	122336
25°	42224	44694	42015
30°	9207	12449	9287
35°	2964	5130	2880
40°	922	1574	832
45°	97	536	97
50°	0	107	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°

Vertical Angle: 45°

Luminance: 536 cd/sqm



TEST NUMBER: P1318097

CATALOG NUMBER: LDSQA3D05R409830DE010 3LSQCDR1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	117.0	22.2
10°-20°	272.4	51.8
20°-30°	122.2	23.2
30°-40°	13.2	2.5
40°-50°	1.2	0.2
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	511.6	97.3
0°-40°	524.8	99.8
0°-60°	526.0	100.0
0°-90°	526.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	526.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1251	1251	1251	1251	1251	
5°	1235	1239	1243	1245	1249	117
15°	1012	1020	1029	1034	1041	269
25°	222	229	235	239	221	119
35°	14	16	24	16	14	11
45°	0	1	2	1	0	1
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P1318097

CATALOG NUMBER: LDSQA3D05R409830DE010 3LSQCDR1MMS

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1250.8	1250.8	1250.8	1250.8	1250.8
1°	1248.2	1250.8	1253.1	1251.2	1253.8
2°	1247.1	1250.1	1253.4	1251.6	1253.8
3°	1244.2	1247.9	1251.6	1250.5	1252.7
4°	1240.1	1243.1	1248.6	1248.6	1252.0
5°	1235.3	1238.6	1243.1	1244.9	1249.0
6°	1230.1	1232.0	1235.3	1239.0	1244.5
7°	1223.4	1223.4	1227.5	1231.2	1238.6
8°	1214.2	1213.4	1216.4	1221.2	1227.9
9°	1202.7	1200.1	1202.3	1209.4	1219.4
10°	1186.4	1184.2	1184.2	1193.1	1202.7
11°	1165.3	1164.5	1164.9	1173.4	1186.4
12°	1136.8	1137.5	1137.5	1147.1	1163.1
13°	1104.5	1104.2	1107.5	1118.2	1129.0
14°	1065.3	1067.5	1070.8	1080.5	1091.6
15°	1012.3	1019.7	1028.6	1034.5	1041.2
17.5°	851.2	858.6	870.8	875.6	877.1
20°	646.3	657.1	658.9	668.6	667.5
22.5°	433.4	432.6	434.1	435.2	435.6
25°	222.2	228.9	235.2	239.3	221.1
27.5°	96.7	108.2	116.3	105.6	97.8
30°	46.3	52.6	62.6	53.0	46.7
32.5°	25.2	29.3	39.6	28.9	24.8
35°	14.1	16.3	24.4	15.9	13.7
37.5°	8.1	8.9	13.3	8.9	7.8
40°	4.1	5.2	7.0	5.2	3.7
42.5°	1.5	2.6	3.7	2.6	1.5
45°	0.4	0.7	2.2	0.7	0.4
47.5°	0.0	0.0	1.1	0.0	0.0
50°	0.0	0.0	0.4	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1318097
CATALOG NUMBER: LDSQA3D05R409830DE010 3LSQCDR1MMS

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)