

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1318115

Luminaire Tested: LDSQA3D05R509830DE010 3LSQCDR1MMS

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1318115
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-27)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LDSQA3D05R509830DE010 3LSQCDR1MMS
Description: 3in Adjustable LED luminaire with, R50 optic, 3000K CCT AND, 98CRI , 3LSQCDR1MMS TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 518.0 lumens
Efficiency: N/A
Efficacy: 71.9 lumens/watt
Spacing Criteria (0/90/45): 0.85 / 0.85 / 0.78
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1318115
CATALOG NUMBER: LDSQA3D05R509830DE010 3LSQCDR1MMS

Luminous Intensity Polar Plot





TEST NUMBER: P1318115
 CATALOG NUMBER: LDSQA3D05R509830DE010 3LSQCDR1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	114	112	109	107	112	110	108	106	106	104	102	102	101	99	98	97	97	97	97	97	95
2	109	105	101	98	107	103	100	97	100	98	95	97	95	93	95	93	91	91	91	91	90
3	105	99	95	91	103	98	94	90	95	92	89	93	90	88	91	88	86	86	86	86	85
4	100	94	89	85	99	93	88	85	90	87	84	89	85	83	87	84	82	82	82	82	80
5	96	89	84	80	95	88	83	79	86	82	79	85	81	78	83	80	77	77	77	77	76
6	92	84	79	75	91	83	79	75	82	78	74	81	77	74	79	76	73	73	73	73	72
7	88	80	75	71	87	79	74	71	78	74	70	77	73	70	76	72	70	70	70	70	69
8	85	76	71	67	83	76	71	67	75	70	67	74	70	67	73	69	66	66	66	66	65
9	81	73	67	64	80	72	67	64	71	67	64	70	66	63	70	66	63	63	63	63	62
10	78	69	64	61	77	69	64	61	68	64	60	67	63	60	67	63	60	60	60	60	59

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	138536	138536	138536
5°	136126	135728	135348
10°	131282	129848	130110
15°	120761	119246	119567
20°	107839	106813	107436
25°	83935	87450	83004
30°	45461	50770	44645
35°	14339	17051	14023
40°	3170	4406	2990
45°	97	1364	97
50°	0	188	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°
 Vertical Angle: 45°
 Luminance: 1364 cd/sqm



TEST NUMBER: P1318115

CATALOG NUMBER: LDSQA3D05R509830DE010 3LSQCDR1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	73.7	14.2
10°-20°	187.2	36.1
20°-30°	197.2	38.1
30°-40°	56.3	10.9
40°-50°	3.5	0.7
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	458.2	88.4
0°-40°	514.5	99.3
0°-60°	518.0	100.0
0°-90°	518.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	518.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	804	804	804	804	804	
5°	787	787	785	784	783	74
15°	677	673	669	670	671	189
25°	442	458	460	455	437	193
35°	68	73	81	69	67	53
45°	0	2	6	2	0	2
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P1318115
 CATALOG NUMBER: LDSQA3D05R509830DE010 3LSQCDR1MMS

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	804.4	804.4	804.4	804.4	804.4
1°	804.8	805.1	804.4	805.1	803.3
2°	803.7	802.9	802.2	802.6	801.4
3°	799.6	799.2	797.7	798.1	796.6
4°	794.4	793.3	792.2	791.4	790.0
5°	787.4	786.6	785.1	784.4	782.9
6°	781.4	780.0	777.4	776.6	775.1
7°	773.7	772.9	769.6	768.8	768.1
8°	767.7	765.5	761.4	761.8	759.9
9°	759.9	757.0	752.9	752.9	753.3
10°	750.7	746.2	742.5	743.6	744.0
11°	738.5	735.5	729.9	732.5	732.5
12°	725.1	721.4	717.3	719.6	721.0
13°	709.6	706.6	702.9	705.1	704.4
14°	694.4	688.8	686.2	689.2	688.1
15°	677.3	672.9	668.8	669.9	670.6
17.5°	631.7	626.9	624.0	624.3	627.7
20°	588.4	586.5	582.8	584.3	586.2
22.5°	537.3	538.0	533.6	534.7	539.1
25°	441.7	458.0	460.2	455.0	436.8
27.5°	327.2	351.6	359.0	347.2	324.9
30°	228.6	235.3	255.3	232.7	224.5
32.5°	134.1	144.1	154.9	139.3	133.8
35°	68.2	73.0	81.1	68.9	66.7
37.5°	31.5	33.7	37.1	31.5	29.6
40°	14.1	16.7	19.6	15.9	13.3
42.5°	4.4	7.8	10.4	7.0	4.1
45°	0.4	1.9	5.6	1.9	0.4
47.5°	0.0	0.4	2.2	0.4	0.0
50°	0.0	0.0	0.7	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1318115
CATALOG NUMBER: LDSQA3D05R509830DE010 3LSQCDR1MMS

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)