

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1317987

Luminaire Tested: LDSQA3D02R609830DE010 3LSQCDR1MMS

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1317987
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-29)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LDSQA3D02R609830DE010 3LSQCDR1MMS
Description: 3in Adjustable LED luminaire with, R60 optic, 3000K CCT AND, 98CRI , 3LSQCDR1MMS TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 224.0 lumens
Efficiency: N/A
Efficacy: 62.2 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.93 / 0.9
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1317987
CATALOG NUMBER: LDSQA3D02R609830DE010 3LSQCDR1MMS

Luminous Intensity Polar Plot





TEST NUMBER: P1317987

CATALOG NUMBER: LDSQA3D02R609830DE010 3LSQCDR1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	96	96	96	94
2	108	104	100	97	106	102	98	95	99	96	93	96	93	91	93	91	89	93	91	89	88
3	103	97	92	88	101	96	91	88	93	89	86	91	88	85	88	86	84	88	86	84	82
4	98	91	86	81	96	90	85	81	88	83	80	86	82	79	84	81	78	84	81	78	77
5	93	85	80	76	92	84	79	75	83	78	75	81	77	74	79	76	73	79	76	73	72
6	89	80	74	70	87	79	74	70	78	73	70	77	72	69	75	72	69	75	72	69	67
7	85	76	70	66	83	75	69	65	74	69	65	72	68	65	71	67	64	71	67	64	63
8	81	71	66	62	79	71	65	61	70	65	61	69	64	61	68	64	61	68	64	61	59
9	77	67	62	58	76	67	61	58	66	61	57	65	61	57	64	60	57	64	60	57	56
10	73	64	58	54	72	63	58	54	63	58	54	62	57	54	61	57	54	61	57	54	53

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	43538	43538	43538
5°	41232	41439	41509
10°	42793	42741	42985
15°	43505	43451	43754
20°	38506	38506	38561
25°	32989	32019	32286
30°	26389	25435	25833
35°	16378	16714	16336
40°	7194	7914	7397
45°	97	2557	219
50°	0	295	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°
 Vertical Angle: 45°
 Luminance: 2557 cd/sqm



TEST NUMBER: P1317987

CATALOG NUMBER: LDSQA3D02R609830DE010 3LSQCDR1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	23.1	10.3
10°-20°	66.9	29.9
20°-30°	77.7	34.7
30°-40°	48.9	21.8
40°-50°	7.4	3.3
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	167.7	74.9
0°-40°	216.6	96.7
0°-60°	224.0	100.0
0°-90°	224.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	224.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	253	253	253	253	253	
5°	238	239	240	240	240	23
15°	244	243	244	245	245	67
25°	174	172	168	169	170	79
35°	78	78	80	78	78	49
45°	0	3	10	4	1	5
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P1317987

CATALOG NUMBER: LDSQA3D02R609830DE010 3LSQCDR1MMS

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	252.8	252.8	252.8	252.8	252.8
1°	250.8	251.5	251.5	251.7	251.5
2°	247.4	248.5	248.5	249.0	248.7
3°	244.0	244.9	245.1	245.8	245.6
4°	240.3	241.7	242.2	242.6	242.4
5°	238.5	239.4	239.7	240.3	240.1
6°	237.8	238.5	238.8	239.4	239.4
7°	238.3	238.8	239.4	239.7	239.4
8°	239.9	240.4	240.4	241.2	240.6
9°	242.2	242.4	242.4	243.3	242.8
10°	244.7	244.4	244.4	245.6	245.8
11°	246.9	246.5	246.3	247.6	247.9
12°	248.1	247.4	247.4	249.0	249.2
13°	248.3	247.4	247.4	249.0	249.6
14°	246.9	245.8	246.0	247.8	248.3
15°	244.0	243.1	243.7	245.3	245.4
17.5°	230.4	229.9	230.3	231.3	231.5
20°	210.1	209.7	210.1	210.1	210.4
22.5°	189.9	189.0	187.2	188.3	188.5
25°	173.6	171.7	168.5	169.2	169.9
27.5°	155.8	153.3	149.9	150.8	150.9
30°	132.7	131.5	127.9	128.8	129.9
32.5°	102.5	105.9	103.8	103.6	103.8
35°	77.9	78.1	79.5	77.9	77.7
37.5°	54.5	54.7	55.7	53.9	54.1
40°	32.0	34.3	35.2	34.5	32.9
42.5°	10.0	17.7	20.0	17.3	11.1
45°	0.4	3.4	10.5	4.5	0.9
47.5°	0.0	0.2	5.0	0.4	0.0
50°	0.0	0.0	1.1	0.0	0.0
52.5°	0.0	0.0	0.2	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1317987
CATALOG NUMBER: LDSQA3D02R609830DE010 3LSQCDR1MMS

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)