

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1318037

Luminaire Tested: LDSQA3D05R209830DE010 3LSQPHRLD1MW

Issue Date: 1/29/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1318037  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-17)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LDSQA3D05R209830DE010 3LSQPHRLD1MW  
Description: 3in Adjustable LED luminaire with, R20 optic, 3000K CCT AND, 98CRI , 3LSQPHRLD1MW TRIM  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 248.0 lumens  
Efficiency: N/A  
Efficacy: 34.5 lumens/watt  
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.86  
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 7.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1318037  
CATALOG NUMBER: LDSQA3D05R209830DE010 3LSQPHRLD1MW

### Luminous Intensity Polar Plot



— 0°-180°    - - 45°-225°    - - - 90°-270°



TEST NUMBER: P1318037

CATALOG NUMBER: LDSQA3D05R209830DE010 3LSQPHRLD1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	111	107	104	100	108	105	102	99	101	98	96	97	95	93	93	92	90	90	90	90	88
2	103	96	91	86	100	94	89	85	91	87	83	88	84	81	85	82	79	79	79	79	77
3	96	87	80	75	93	85	79	74	82	77	73	80	75	71	77	74	70	70	70	70	68
4	89	79	71	66	87	78	71	65	75	69	65	73	68	64	71	67	63	63	63	63	61
5	83	72	64	59	81	71	64	58	69	63	58	67	62	57	65	61	57	57	57	57	55
6	78	66	59	53	76	65	58	53	64	57	52	62	56	52	61	56	52	52	52	52	50
7	73	61	54	48	71	60	53	48	59	53	48	58	52	48	56	51	47	47	47	47	45
8	69	57	49	44	67	56	49	44	55	49	44	54	48	44	53	47	43	43	43	43	42
9	65	53	46	41	63	52	45	41	51	45	41	50	45	40	49	44	40	40	40	40	39
10	61	50	43	38	60	49	42	38	48	42	38	47	42	38	46	41	37	37	37	37	36

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	35702	35702	35702
5°	34628	34628	34697
10°	31793	31863	31916
15°	27993	28118	28189
20°	24229	24229	24284
25°	20618	20618	20751
30°	17600	17520	17679
35°	15033	15033	15096
40°	12905	12905	12995
45°	11277	11277	11374
50°	9913	9913	9913
55°	8768	8768	8888
60°	7922	7922	7922
65°	7091	7091	7091
70°	6345	6345	6345
75°	5656	5390	5656
80°	4761	4761	4761
85°	2964	2964	3754

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 90°  
 Vertical Angle: 45°  
 Luminance: 11374 cd/sqm



TEST NUMBER: P1318037

CATALOG NUMBER: LDSQA3D05R209830DE010 3LSQPHRLD1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	18.5	7.5
10°-20°	43.9	17.7
20°-30°	50.0	20.2
30°-40°	44.9	18.1
40°-50°	36.0	14.5
50°-60°	26.4	10.7
60°-70°	17.3	7.0
70°-80°	9.0	3.6
80°-90°	2.1	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	112.4	45.3
0°-40°	157.3	63.4
0°-60°	219.7	88.6
0°-90°	248.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	248.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	207	207	207	207	207	
5°	200	200	200	200	201	19
15°	157	157	158	158	158	44
25°	108	108	108	109	109	50
35°	72	72	72	72	72	45
45°	46	46	46	46	47	36
55°	29	29	29	29	30	26
65°	17	17	17	17	17	17
75°	8	8	8	8	8	9
85°	2	2	2	2	2	2
90°	0	0	0	0	0	



TEST NUMBER: P1318037

CATALOG NUMBER: LDSQA3D05R209830DE010 3LSQPHRLD1MW

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	207.3	207.3	207.3	207.3	207.3
1°	207.0	206.6	207.0	207.0	207.3
2°	206.2	206.2	206.2	205.9	206.6
3°	204.7	204.7	205.1	204.7	205.1
4°	202.9	202.9	202.9	202.5	203.3
5°	200.3	200.3	200.3	200.3	200.7
6°	197.7	197.3	197.7	197.3	197.7
7°	194.0	194.0	194.4	194.0	194.4
8°	190.3	189.9	190.7	190.3	191.0
9°	186.6	186.2	186.6	186.2	187.3
10°	181.8	182.2	182.2	182.2	182.5
12.5°	170.7	169.9	169.9	169.9	170.7
15°	157.0	157.0	157.7	157.7	158.1
17.5°	144.8	144.4	145.1	145.1	145.1
20°	132.2	131.8	132.2	132.2	132.5
22.5°	119.6	120.0	120.0	120.0	120.3
25°	108.5	108.5	108.5	108.9	109.2
27.5°	98.1	97.7	98.1	98.5	98.9
30°	88.5	88.1	88.1	88.5	88.9
32.5°	79.6	79.2	79.6	79.6	80.0
35°	71.5	71.5	71.5	71.5	71.8
37.5°	64.1	64.1	64.1	64.4	64.4
40°	57.4	57.4	57.4	57.8	57.8
42.5°	51.5	51.5	51.5	51.8	52.2
45°	46.3	46.3	46.3	46.3	46.7
47.5°	41.5	41.5	41.5	41.8	41.8
50°	37.0	36.7	37.0	37.4	37.0
52.5°	33.0	33.0	33.0	33.0	33.3
55°	29.2	29.2	29.2	29.2	29.6
57.5°	25.9	25.9	25.9	26.3	26.3
60°	23.0	23.0	23.0	23.0	23.0
62.5°	20.0	20.0	20.0	20.0	20.0
65°	17.4	17.0	17.4	17.4	17.4
67.5°	14.8	14.8	14.8	14.8	14.8
70°	12.6	12.6	12.6	12.6	12.6
72.5°	10.4	10.4	10.4	10.4	10.4
75°	8.5	8.1	8.1	8.5	8.5
77.5°	6.7	6.3	6.7	6.7	6.7
80°	4.8	4.8	4.8	4.8	4.8
82.5°	3.0	3.0	3.0	3.3	3.3
85°	1.5	1.5	1.5	1.9	1.9
87.5°	0.4	0.4	0.4	0.7	0.7
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)