

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1318060

Luminaire Tested: LDSQA3D05R309830DE010 3LSQCA45R 1MMS

Issue Date: 1/29/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1318060  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-76)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LDSQA3D05R309830DE010 3LSQCA45R 1MMS  
Description: 3in Adjustable LED luminaire with, R30 optic, 3000K CCT AND, 98CRI , 3LSQCA45R 1MMS TRII  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 439.0 lumens  
Efficiency: N/A  
Efficacy: 61.0 lumens/watt  
Spacing Criteria (0/90/45): 4.07 / 0.66 / 1.44  
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 7.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1318060  
CATALOG NUMBER: LDSQA3D05R309830DE010 3LSQCA45R 1MMS

### Luminous Intensity Polar Plot



— 0°-180°    - - - 45°-225°    ····· 90°-270°



TEST NUMBER: P1318060  
 CATALOG NUMBER: LDSQA3D05R309830DE010 3LSQCA45R 1MMS

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	110	106	102	99	108	104	100	97	100	97	94	96	93	91	92	90	89	89	89	89	87
2	100	93	86	81	98	91	85	80	87	83	78	84	80	77	81	78	75	75	75	75	73
3	91	81	73	67	89	79	72	66	76	70	65	74	68	64	71	67	63	63	63	63	61
4	83	71	62	55	80	69	61	55	67	60	54	64	58	53	62	57	52	52	52	52	50
5	75	62	52	46	73	60	52	45	58	51	45	56	50	44	54	49	44	44	44	44	42
6	68	54	45	38	66	53	44	38	51	43	37	49	42	37	48	42	37	37	37	37	35
7	62	48	38	32	60	47	38	32	45	37	31	44	36	31	42	36	31	31	31	31	29
8	56	42	33	27	55	41	33	27	40	32	26	39	32	26	37	31	26	26	26	26	24
9	52	37	29	23	50	37	28	23	36	28	22	34	27	22	33	27	22	22	22	22	20
10	48	33	25	19	46	33	25	19	32	24	19	31	24	19	30	24	19	19	19	19	17

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°	135°	180°
0°	2928	2928	2928	2928	2928
5°	3129	3077	2870	2628	2559
10°	3428	3043	2518	2256	2203
15°	5010	3031	2104	1908	1979
20°	12609	3317	1631	1631	1833
25°	58528	4143	1273	1482	1691
30°	186357	5727	955	1392	1690
35°	323357	7001	778	1325	1703
40°	377114	6992	585	1326	1754
45°	386748	4944	633	1437	1900
50°	359670	2786	482	1474	2170
55°	305666	1441	540	1651	2432
60°	176528	379	620	1791	2687
65°	36024	0	734	2119	3016
70°	554	201	906	2417	3525
75°	466	266	998	2462	4192
80°	397	397	1488	2975	4761
85°	0	790	2964	2964	5928

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 386748 cd/sqm



TEST NUMBER: P1318060

CATALOG NUMBER: LDSQA3D05R309830DE010 3LSQCA45R 1MMS

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	1.5	0.4
10°-20°	4.4	1.0
20°-30°	25.3	5.8
30°-40°	118.2	26.9
40°-50°	167.2	38.1
50°-60°	102.9	23.4
60°-70°	15.7	3.6
70°-80°	2.5	0.6
80°-90°	1.2	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	31.3	7.1
0°-40°	149.5	34.1
0°-60°	419.6	95.6
0°-90°	439.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	439.0	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	17	17	17	17	17	
5°	18	18	17	15	15	2
15°	28	17	12	11	11	10
25°	308	22	7	8	9	190
35°	1538	33	4	6	8	923
45°	1588	20	3	6	8	1204
55°	1018	5	2	6	8	866
65°	88	0	2	5	7	160
75°	1	0	2	4	6	1
85°	0	0	2	2	3	0
90°	0	0	0	0	0	



TEST NUMBER: P1318060  
 CATALOG NUMBER: LDSQA3D05R309830DE010 3LSQCA45R 1MMS

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	22.5°	45°	67.5°	90°	112.5°	135°
0°	17.0	17.0	17.0	17.0	17.0	17.0	17.0	17.0	17.0	17.0	17.0
2.5°	17.4	17.4	17.8	17.8	17.4	17.8	17.8	17.8	17.0	16.6	15.9
5°	18.1	18.1	18.1	18.5	18.1	18.1	17.8	17.4	16.6	15.5	15.2
7.5°	18.9	18.9	18.5	18.9	18.5	18.5	17.8	17.0	15.9	14.8	14.1
10°	19.6	19.6	19.2	19.2	18.9	18.9	17.4	16.3	14.4	13.3	12.9
12.5°	21.8	21.8	21.4	21.1	20.3	20.0	17.0	15.2	12.9	11.8	11.5
15°	28.1	27.7	27.0	25.9	24.0	23.7	17.0	14.1	11.8	10.7	10.7
17.5°	38.5	38.1	37.0	34.0	30.7	29.6	17.0	12.6	10.4	9.6	9.6
20°	68.8	65.8	60.3	52.9	45.1	41.0	18.1	11.1	8.9	8.5	8.9
21°	89.9	86.9	79.9	67.7	54.0	49.6	18.9	10.7	8.5	8.1	8.9
22°	122.4	119.1	104.7	88.0	68.4	60.6	19.2	10.0	7.8	7.8	8.5
23°	170.8	165.3	140.9	114.3	85.4	74.3	20.0	9.6	7.4	7.8	8.1
24°	223.7	218.9	191.2	151.2	109.1	93.2	20.7	9.2	7.0	7.0	7.8
25°	308.0	302.5	253.3	190.8	138.3	112.0	21.8	8.5	6.7	6.7	7.8
26°	417.1	391.6	326.2	245.9	170.5	140.5	22.9	8.1	6.3	6.7	7.4
27°	520.7	499.6	426.0	315.4	210.8	172.7	24.4	7.8	5.9	6.3	7.4
28°	656.8	627.2	534.4	399.0	265.5	208.9	25.9	7.4	5.5	6.3	7.0
29°	809.1	767.7	655.6	492.9	327.3	249.6	27.4	7.0	5.2	5.9	7.0
30°	937.1	898.2	786.2	604.2	398.3	303.2	28.8	6.7	4.8	5.9	7.0
31°	1087.2	1028.4	892.7	698.5	459.3	356.9	30.3	5.9	4.4	5.5	6.7
32°	1208.9	1167.8	1023.6	805.0	539.5	416.0	31.4	5.5	4.4	5.5	6.7
33°	1326.5	1271.4	1131.9	907.1	612.0	476.7	32.5	5.2	4.1	5.2	6.7
34°	1438.9	1388.2	1234.4	989.6	680.4	534.4	33.3	4.4	4.1	5.2	6.3
35°	1538.0	1479.2	1324.6	1070.2	750.7	586.9	33.3	4.1	3.7	4.8	6.3
36°	1602.3	1560.2	1403.0	1149.7	814.3	636.8	33.3	3.7	3.3	4.8	5.9
37°	1657.4	1608.2	1465.9	1210.7	861.3	676.7	33.3	3.3	3.3	4.8	5.9
38°	1680.0	1637.8	1509.1	1264.7	905.3	717.4	32.9	3.0	3.0	4.4	5.9
39°	1688.9	1651.1	1541.7	1303.5	937.8	744.8	32.2	2.6	3.0	4.4	5.9
40°	1677.4	1648.9	1558.3	1328.7	963.7	764.7	31.1	2.2	2.6	4.4	5.9
42.5°	1630.1	1611.2	1554.6	1353.8	985.9	779.5	27.0	1.5	2.6	4.1	5.9
45°	1587.9	1567.2	1517.3	1327.6	957.0	750.3	20.3	0.7	2.6	4.1	5.9
47.5°	1506.2	1493.2	1454.0	1260.6	893.8	684.5	14.4	0.4	2.2	3.7	5.5
50°	1342.4	1330.2	1278.4	1094.6	768.8	578.7	10.4	0.4	1.8	3.7	5.5
52.5°	1195.5	1182.6	1108.3	910.1	590.6	424.2	6.7	0.4	1.8	3.7	5.5
55°	1018.0	995.5	897.9	690.8	418.6	284.4	4.8	0.4	1.8	3.3	5.5
57.5°	753.6	720.7	633.5	471.1	241.1	154.2	2.6	0.4	1.8	3.3	5.5
60°	512.5	492.9	396.4	248.5	102.8	65.1	1.1	0.4	1.8	3.3	5.2
62.5°	310.6	285.9	199.3	105.8	44.4	29.6	0.0	0.7	1.8	3.3	5.2
65°	88.4	78.4	52.1	24.0	12.6	9.6	0.0	0.7	1.8	3.3	5.2
67.5°	3.0	3.0	3.0	2.6	1.8	1.8	0.4	0.7	1.8	3.3	4.8
70°	1.1	1.1	1.1	0.7	0.7	0.4	0.4	0.7	1.8	3.0	4.8
72.5°	0.7	0.7	0.7	0.7	0.4	0.4	0.4	0.7	1.5	2.6	4.4
75°	0.7	0.7	0.7	0.4	0.4	0.4	0.4	1.1	1.5	2.6	3.7
77.5°	0.7	0.7	0.7	0.4	0.4	0.4	0.4	1.1	1.5	2.2	3.7
80°	0.4	0.4	0.4	0.4	0.4	0.4	0.4	1.1	1.5	2.2	3.0



TEST NUMBER: P1318060  
CATALOG NUMBER: LDSQA3D05R309830DE010 3LSQCA45R 1MMS

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	22.5°	45°	67.5°	90°	112.5°	135°
82.5°	0.4	0.4	0.4	0.0	0.0	0.0	0.4	1.1	1.5	1.5	2.2
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.4	1.1	1.5	1.1	1.5
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.4	1.1	1.1	1.1	0.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1318060  
CATALOG NUMBER: LDSQA3D05R309830DE010 3LSQCA45R 1MMS

**CANDELA DISTRIBUTION (continued):**

	157.5°	180°
0°	17.0	17.0
2.5°	15.9	15.9
5°	14.8	14.8
7.5°	13.7	13.7
10°	12.6	12.6
12.5°	11.8	11.8
15°	10.7	11.1
17.5°	10.0	10.4
20°	9.6	10.0
21°	9.6	10.0
22°	9.2	9.6
23°	9.2	9.6
24°	8.9	9.2
25°	8.5	8.9
26°	8.5	8.9
27°	8.5	8.9
28°	8.1	8.9
29°	8.1	8.5
30°	8.1	8.5
31°	7.8	8.5
32°	7.8	8.5
33°	7.8	8.1
34°	7.4	8.1
35°	7.4	8.1
36°	7.4	8.1
37°	7.4	7.8
38°	7.4	8.1
39°	7.4	7.8
40°	7.4	7.8
42.5°	7.4	7.8
45°	7.4	7.8
47.5°	7.4	8.1
50°	7.4	8.1
52.5°	7.4	8.1
55°	7.4	8.1
57.5°	7.4	7.8
60°	7.4	7.8
62.5°	7.0	7.8
65°	7.0	7.4
67.5°	7.0	7.4
70°	6.7	7.0
72.5°	6.3	6.7
75°	5.5	6.3
77.5°	5.2	5.5
80°	4.4	4.8



TEST NUMBER: P1318060  
CATALOG NUMBER: LDSQA3D05R309830DE010 3LSQCA45R 1MMS

**CANDELA DISTRIBUTION (continued):**

	157.5°	180°
82.5°	3.7	3.7
85°	2.6	3.0
87.5°	1.5	1.5
90°	0.0	0.0

(END OF REPORT)