

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1318178

Luminaire Tested: LDSQA3D09R209830DE010 3LSQPHR1MMS

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1318178
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-2)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LDSQA3D09R209830DE010 3LSQPHR1MMS
Description: 3in Adjustable LED luminaire with, R20 optic, 3000K CCT AND, 98CRI , 3LSQPHR1MMS TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 614.0 lumens
Efficiency: N/A
Efficacy: 55.8 lumens/watt
Spacing Criteria (0/90/45): 0.35 / 0.36 / 0.33
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1318178
CATALOG NUMBER: LDSQA3D09R209830DE010 3LSQPHR1MMS

Luminous Intensity Polar Plot





TEST NUMBER: P1318178
 CATALOG NUMBER: LDSQA3D09R209830DE010 3LSQPHR1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	116	114	112	111	113	112	110	109	108	107	106	104	103	102	101	100	100	100	100	100	98
2	113	109	107	105	111	108	106	104	105	103	101	102	101	99	99	98	97	97	97	97	96
3	110	106	103	100	108	105	102	100	102	100	98	100	98	97	98	96	95	95	95	95	94
4	107	103	99	97	106	102	99	96	100	97	95	98	96	94	96	95	93	93	93	93	92
5	105	100	97	94	104	99	96	94	98	95	93	96	94	92	95	93	92	92	92	92	91
6	103	98	94	92	102	97	94	91	96	93	91	95	92	90	93	91	90	90	90	90	89
7	101	95	92	90	100	95	92	89	94	91	89	93	90	89	92	90	88	88	88	88	87
8	99	93	90	88	98	93	90	88	92	89	87	91	89	87	91	88	87	87	87	87	86
9	97	92	88	86	96	91	88	86	91	88	86	90	87	86	89	87	85	85	85	85	85
10	95	90	87	85	95	90	87	85	89	86	84	88	86	84	88	86	84	84	84	84	83

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	787299	787299	787299
5°	680129	686474	689033
10°	409428	413258	433823
15°	141622	138306	149325
20°	37187	34987	35097
25°	8114	9767	11117
30°	3480	3480	3599
35°	1955	1724	1850
40°	854	989	1102
45°	268	390	390
50°	134	134	134
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 22.5°
 Vertical Angle: 45°
 Luminance: 390 cd/sqm



TEST NUMBER: P1318178

CATALOG NUMBER: LDSQA3D09R209830DE010 3LSQPHR1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	327.0	53.3
10°-20°	248.9	40.5
20°-30°	30.8	5.0
30°-40°	5.8	1.0
40°-50°	1.4	0.2
50°-60°	0.1	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	606.7	98.8
0°-40°	612.5	99.8
0°-60°	614.0	100.0
0°-90°	614.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	614.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4571	4571	4571	4571	4571	
5°	3934	3931	3971	3968	3986	324
15°	794	766	776	822	838	249
25°	43	49	51	54	58	29
35°	9	9	8	9	9	6
45°	1	2	2	2	2	1
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P1318178
 CATALOG NUMBER: LDSQA3D09R209830DE010 3LSQPHR1MMS

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4571.4	4571.4	4571.4	4571.4	4571.4
1°	4550.1	4544.6	4549.0	4539.7	4558.8
2°	4477.3	4471.9	4471.9	4466.4	4469.1
3°	4341.7	4350.4	4344.9	4333.5	4348.2
4°	4156.8	4166.6	4175.4	4175.9	4178.1
5°	3934.1	3931.4	3970.8	3968.1	3985.6
6°	3680.3	3677.0	3694.0	3722.4	3757.5
7°	3401.3	3361.4	3406.8	3464.3	3511.3
8°	3040.3	3050.7	3081.9	3149.7	3187.5
9°	2734.0	2673.3	2739.5	2820.4	2861.4
10°	2341.2	2292.0	2363.1	2448.4	2480.7
12.5°	1473.7	1431.0	1454.0	1543.7	1557.9
15°	794.3	765.8	775.7	822.2	837.5
17.5°	405.3	379.6	374.2	403.7	407.0
20°	202.9	196.9	190.9	193.6	191.5
22.5°	94.1	102.3	101.2	95.7	102.3
25°	42.7	48.7	51.4	53.6	58.5
27.5°	26.3	25.2	29.0	31.2	31.7
30°	17.5	17.0	17.5	18.1	18.1
32.5°	12.6	12.0	11.5	11.5	12.0
35°	9.3	9.3	8.2	8.8	8.8
37.5°	6.6	6.6	6.0	6.6	6.6
40°	3.8	4.4	4.4	4.4	4.9
42.5°	2.2	2.7	2.7	2.7	2.7
45°	1.1	1.6	1.6	1.6	1.6
47.5°	0.5	0.5	0.5	1.1	1.1
50°	0.5	0.5	0.5	0.5	0.5
52.5°	0.5	0.0	0.0	0.0	0.5
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)