

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1318333

Luminaire Tested: LDSQA3D13R259830DE010 3LSQCA30R 1MW

Issue Date: 1/29/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1318333  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-61)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LDSQA3D13R259830DE010 3LSQCA30R 1MW  
Description: 3in Adjustable LED luminaire with, R25 optic, 3000K CCT AND, 98CRI , 3LSQCA30R 1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 778.0 lumens  
Efficiency: N/A  
Efficacy: 53.7 lumens/watt  
Spacing Criteria (0/90/45): 2.36 / 0.51 / 1.27  
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 14.5  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1318333  
CATALOG NUMBER: LDSQA3D13R259830DE010 3LSQCA30R 1MW

### Luminous Intensity Polar Plot



— 0°-180°    - - 45°-225°    - - - 90°-270°



TEST NUMBER: P1318333

CATALOG NUMBER: LDSQA3D13R259830DE010 3LSQCA30R 1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	113	109	107	104	110	107	105	102	103	101	99	99	98	96	96	95	93	96	95	93	92
2	106	100	95	92	103	98	94	90	95	92	88	92	89	87	89	87	85	89	87	85	83
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	79	77	83	79	77	75
4	93	84	77	72	91	83	77	72	80	75	71	78	74	70	76	73	69	76	73	69	68
5	87	77	70	65	85	76	69	65	74	68	64	72	67	63	71	66	63	71	66	63	61
6	81	71	63	58	79	70	63	58	68	62	58	67	61	57	65	60	57	65	60	57	55
7	76	65	58	53	74	64	57	52	63	57	52	61	56	52	60	55	52	60	55	52	50
8	71	60	52	48	70	59	52	47	58	52	47	57	51	47	56	51	47	56	51	47	45
9	66	55	48	43	65	54	48	43	53	47	43	52	47	43	51	46	42	51	46	42	41
10	62	51	44	39	61	50	44	39	49	43	39	48	43	39	48	42	39	48	42	39	37

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°	135°	180°
0°	5752	5752	5752	5752	5752
5°	14436	10667	5394	2766	2126
10°	63097	18152	4442	1277	892
15°	300004	48925	3102	517	392
20°	577519	78350	1998	128	128
25°	703346	79032	1102	0	0
30°	773309	60475	438	0	0
35°	745213	38454	147	0	0
40°	556813	16637	0	0	157
45°	206149	4408	170	170	536
50°	24301	589	402	402	777
55°	2402	0	450	661	1081
60°	241	0	758	999	1240
65°	285	285	1182	1467	1793
70°	352	352	1460	1460	2216
75°	466	466	1464	1464	1930
80°	0	694	2182	1488	2182
85°	0	1383	4347	1383	1383

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 206149 cd/sqm



TEST NUMBER: P1318333

CATALOG NUMBER: LDSQA3D13R259830DE010 3LSQCA30R 1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	4.9	0.6
10°-20°	90.7	11.7
20°-30°	284.7	36.6
30°-40°	299.7	38.5
40°-50°	88.0	11.3
50°-60°	4.7	0.6
60°-70°	2.3	0.3
70°-80°	2.0	0.3
80°-90°	1.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	380.3	48.9
0°-40°	680.0	87.4
0°-60°	772.7	99.3
0°-90°	778.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	778.0	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	33	33	33	33	33	
5°	84	62	31	16	12	15
15°	1683	274	17	3	2	530
25°	3701	416	6	0	0	1698
35°	3544	183	1	0	0	2139
45°	846	18	1	1	2	769
55°	8	0	2	2	4	20
65°	1	1	3	4	4	1
75°	1	1	2	2	3	0
85°	0	1	2	1	1	0
90°	0	0	0	0	0	



TEST NUMBER: P1318333

CATALOG NUMBER: LDSQA3D13R259830DE010 3LSQCA30R 1MW

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	45°	67.5°	90°	112.5°
0°	33.4	33.4	33.4	33.4	33.4	33.4	33.4	33.4	33.4	33.4	33.4
2.5°	51.5	52.3	50.1	51.5	50.1	49.4	48.6	45.0	39.2	33.4	27.6
5°	83.5	83.5	79.8	79.1	77.7	74.8	71.9	61.7	44.3	31.2	21.8
7.5°	130.7	129.9	128.5	124.9	117.6	110.3	103.1	80.6	48.6	29.0	16.7
10°	360.8	355.7	349.2	310.0	265.7	226.5	192.4	103.8	52.3	25.4	12.3
12.5°	896.5	867.4	798.5	720.1	619.9	514.7	411.6	169.1	53.7	21.1	8.7
15°	1682.6	1622.4	1514.9	1358.1	1153.4	923.3	727.3	274.4	52.3	17.4	6.5
17.5°	2540.6	2482.5	2333.7	2095.6	1794.4	1440.9	1093.9	363.7	48.6	14.5	4.4
20°	3151.1	3089.4	2950.0	2697.4	2371.5	1900.4	1440.2	427.5	45.7	10.9	2.2
21°	3329.6	3267.9	3120.6	2876.7	2534.1	2061.5	1551.2	438.4	43.6	9.4	1.5
22°	3442.9	3406.6	3248.3	3011.7	2662.5	2190.7	1646.3	443.5	42.1	8.7	1.5
23°	3556.8	3502.4	3354.3	3104.6	2760.5	2286.5	1716.7	439.9	40.6	7.3	0.7
24°	3641.0	3595.3	3423.3	3176.5	2828.8	2345.3	1758.1	430.4	38.5	6.5	0.7
25°	3701.3	3659.2	3479.9	3225.1	2874.5	2377.3	1771.2	415.9	36.3	5.8	0.7
26°	3758.6	3712.9	3527.1	3253.4	2898.5	2387.4	1758.8	400.0	34.1	5.1	0.0
27°	3800.0	3753.5	3559.7	3270.1	2899.9	2375.1	1725.4	378.2	31.9	4.4	0.0
28°	3844.3	3790.6	3582.2	3279.5	2891.2	2346.1	1677.5	355.0	30.5	3.6	0.0
29°	3871.1	3820.3	3605.5	3289.7	2873.0	2297.4	1607.8	327.4	26.9	2.2	0.0
30°	3888.6	3828.3	3603.3	3278.8	2849.1	2245.2	1524.4	304.1	23.2	2.2	0.0
31°	3874.0	3810.9	3580.1	3248.3	2810.6	2176.9	1438.7	275.1	18.9	1.5	0.0
32°	3842.8	3768.1	3539.4	3195.3	2741.7	2089.1	1350.1	251.2	13.8	1.5	0.0
33°	3766.6	3703.5	3466.1	3124.2	2651.7	1970.0	1234.7	227.9	9.4	0.7	0.0
34°	3670.8	3607.6	3365.9	3029.1	2531.2	1816.2	1094.6	204.0	8.0	0.7	0.0
35°	3544.5	3482.1	3252.7	2896.3	2371.5	1631.1	950.2	182.9	6.5	0.7	0.0
36°	3411.7	3328.9	3109.7	2754.7	2157.3	1420.6	795.6	159.0	5.1	0.7	0.0
37°	3216.4	3160.5	2917.3	2539.1	1925.8	1218.8	683.1	137.2	3.6	0.7	0.0
38°	3013.9	2962.3	2725.0	2322.1	1667.4	1019.1	572.0	116.1	2.9	0.0	0.0
39°	2804.8	2719.2	2484.7	2044.1	1396.6	853.6	481.3	97.3	1.5	0.0	0.0
40°	2476.7	2411.4	2161.0	1710.2	1155.6	691.8	410.1	74.0	1.5	0.0	0.0
42.5°	1641.9	1581.0	1318.2	927.7	614.1	404.3	270.8	29.0	0.0	0.7	0.0
45°	846.4	807.9	656.2	485.6	348.4	248.3	174.2	18.1	0.0	0.7	0.7
47.5°	336.1	329.6	297.6	257.0	198.2	147.4	95.1	8.0	0.0	0.7	0.7
50°	90.7	91.5	85.7	79.1	71.9	67.5	39.9	2.2	0.0	1.5	0.7
52.5°	38.5	39.2	37.7	35.6	31.9	24.0	16.0	0.7	0.7	1.5	1.5
55°	8.0	8.7	9.4	10.2	11.6	10.2	6.5	0.0	0.7	1.5	1.5
57.5°	1.5	1.5	1.5	1.5	2.2	2.2	1.5	0.0	0.7	1.5	2.2
60°	0.7	0.7	0.7	0.7	0.7	0.0	0.0	0.0	1.5	2.2	2.2
62.5°	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	1.5	2.2	2.9
65°	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	1.5	2.9	2.9
67.5°	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	2.2	2.9	2.9
70°	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	2.2	2.9	2.9
72.5°	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	2.2	2.9	2.2
75°	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	2.2	2.2	2.2
77.5°	0.0	0.0	0.0	0.0	0.0	0.7	0.7	0.7	1.5	2.2	2.2
80°	0.0	0.0	0.0	0.0	0.0	0.7	0.7	0.7	1.5	2.2	1.5



TEST NUMBER: P1318333

CATALOG NUMBER: LDSQA3D13R259830DE010 3LSQCA30R 1MW

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	45°	67.5°	90°	112.5°
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.7	0.7	1.5	2.2	1.5
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.7	1.5	2.2	1.5
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.7	1.5	2.2	1.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1318333

CATALOG NUMBER: LDSQA3D13R259830DE010 3LSQCA30R 1MW

**CANDELA DISTRIBUTION (continued):**

	135°	157.5°	180°
0°	33.4	33.4	33.4
2.5°	23.2	21.1	20.3
5°	16.0	13.8	12.3
7.5°	10.9	8.7	8.0
10°	7.3	5.8	5.1
12.5°	5.1	2.9	2.9
15°	2.9	2.2	2.2
17.5°	1.5	0.7	0.7
20°	0.7	0.7	0.7
21°	0.0	0.0	0.0
22°	0.0	0.0	0.0
23°	0.0	0.0	0.0
24°	0.0	0.0	0.0
25°	0.0	0.0	0.0
26°	0.0	0.0	0.0
27°	0.0	0.0	0.0
28°	0.0	0.0	0.0
29°	0.0	0.0	0.0
30°	0.0	0.0	0.0
31°	0.0	0.0	0.0
32°	0.0	0.0	0.0
33°	0.0	0.0	0.0
34°	0.0	0.0	0.0
35°	0.0	0.0	0.0
36°	0.0	0.0	0.0
37°	0.0	0.0	0.0
38°	0.0	0.0	0.7
39°	0.0	0.7	0.7
40°	0.0	0.7	0.7
42.5°	0.0	0.7	1.5
45°	0.7	1.5	2.2
47.5°	1.5	2.2	2.9
50°	1.5	2.9	2.9
52.5°	2.2	2.9	3.6
55°	2.2	3.6	3.6
57.5°	2.9	3.6	4.4
60°	2.9	3.6	3.6
62.5°	2.9	4.4	4.4
65°	3.6	4.4	4.4
67.5°	3.6	4.4	4.4
70°	2.9	3.6	4.4
72.5°	2.9	3.6	3.6
75°	2.2	2.9	2.9
77.5°	2.2	2.2	2.9
80°	1.5	2.2	2.2



TEST NUMBER: P1318333

CATALOG NUMBER: LDSQA3D13R259830DE010 3LSQCA30R 1MW

**CANDELA DISTRIBUTION (continued):**

	135°	157.5°	180°
82.5°	1.5	1.5	1.5
85°	0.7	0.7	0.7
87.5°	0.7	0.7	0.7
90°	0.0	0.0	0.0

(END OF REPORT)