

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1318833

Luminaire Tested: LDSQA3D02R459835DE010 3LSQCA45R 1MMS

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1318833
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-84)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LDSQA3D02R459835DE010 3LSQCA45R 1MMS
Description: 3in Adjustable LED luminaire with, R45 optic, 3500K CCT AND, 98CRI , 3LSQCA45R 1MMS TRII
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 226.0 lumens
Efficiency: N/A
Efficacy: 62.8 lumens/watt
Spacing Criteria (0/90/45): 3.81 / 0.82 / 1.83
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1318833
CATALOG NUMBER: LDSQA3D02R459835DE010 3LSQCA45R 1MMS

Luminous Intensity Polar Plot



— 0°-180° - - - 45°-225° ····· 90°-270°



TEST NUMBER: P1318833

CATALOG NUMBER: LDSQA3D02R459835DE010 3LSQCA45R 1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100	
1	110	106	102	99	107	104	100	97	99	97	94	96	93	91	92	90	88	88	88	88	86	
2	100	93	86	81	98	91	85	80	87	83	78	84	80	77	81	78	75	75	75	75	73	
3	91	81	73	67	89	80	72	66	77	70	65	74	69	64	71	67	63	63	63	63	61	
4	83	71	62	56	81	70	62	55	67	60	55	65	59	54	63	58	53	53	53	53	51	
5	76	63	53	47	73	61	53	46	59	52	46	57	51	45	55	50	45	45	45	45	43	
6	69	55	46	39	67	54	46	39	52	45	39	51	44	39	49	43	38	38	38	38	36	
7	63	49	40	34	61	48	40	33	47	39	33	45	38	33	44	37	33	33	33	33	31	
8	58	44	35	29	56	43	35	29	42	34	29	40	33	28	39	33	28	28	28	28	26	
9	53	39	31	25	52	39	30	25	38	30	25	36	29	25	35	29	24	24	24	24	22	
10	49	36	27	22	48	35	27	22	34	27	21	33	26	21	32	26	21	21	21	21	19	

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°	135°	180°
0°	2256	2256	2256	2256	2256
5°	2680	2489	2230	2075	2075
10°	4285	2903	2099	1959	1959
15°	10662	3887	1890	1836	1890
20°	28059	5810	1649	1741	1851
25°	56343	8627	1425	1634	1805
30°	83066	11554	1153	1591	1849
35°	104786	13540	988	1577	1934
40°	111803	13692	877	1641	2068
45°	116154	11423	828	1778	2241
50°	115987	7958	804	1902	2492
55°	98576	3543	841	2132	2762
60°	66237	723	827	2377	3169
65°	17564	285	856	2567	3586
70°	453	352	856	2820	4028
75°	399	399	865	2994	4591
80°	397	595	893	3174	5157
85°	395	790	1383	3359	5138

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 10°
 Vertical Angle: 47.5°
 Luminance: 119150 cd/sqm



TEST NUMBER: P1318833

CATALOG NUMBER: LDSQA3D02R459835DE010 3LSQCA45R 1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1.3	0.6
10°-20°	6.4	2.8
20°-30°	26.3	11.6
30°-40°	55.4	24.5
40°-50°	68.4	30.2
50°-60°	51.2	22.7
60°-70°	13.2	5.8
70°-80°	2.7	1.2
80°-90°	1.1	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	34.0	15.0
0°-40°	89.4	39.5
0°-60°	209.0	92.5
0°-90°	226.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	226.0	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	13	13	13	13	13	
5°	16	14	13	12	12	2
15°	60	22	11	10	11	22
25°	296	45	8	9	10	138
35°	498	64	5	8	9	304
45°	477	47	3	7	9	365
55°	328	12	3	7	9	283
65°	43	1	2	6	9	62
75°	1	1	1	4	7	1
85°	0	0	1	2	3	0
90°	0	0	0	0	0	



TEST NUMBER: P1318833

CATALOG NUMBER: LDSQA3D02R459835DE010 3LSQCA45R 1MMS

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	45°	67.5°	90°	112.5°
0°	13.1	13.1	13.1	13.1	13.1	13.1	13.1	13.1	13.1	13.1	13.1
2.5°	13.8	13.8	13.8	13.8	13.8	13.8	13.8	13.6	13.4	13.1	12.7
5°	15.5	15.3	15.3	15.3	15.1	14.9	14.9	14.4	13.6	12.9	12.3
7.5°	18.3	18.3	18.1	17.7	17.6	17.2	16.8	15.3	13.6	12.5	11.8
10°	24.5	24.1	23.5	23.2	22.2	20.9	20.0	16.6	13.4	12.0	11.4
12.5°	36.6	37.3	35.5	33.6	31.0	28.6	25.6	18.9	13.4	11.4	10.8
15°	59.8	61.1	57.5	53.8	47.4	41.5	35.9	21.8	13.1	10.6	10.1
17.5°	97.7	99.3	93.4	84.6	74.7	62.7	52.5	26.0	12.7	9.9	9.5
20°	153.1	152.9	141.4	130.3	111.3	93.7	74.5	31.7	12.1	9.0	9.0
22.5°	221.3	222.0	207.8	188.0	161.0	132.8	102.1	38.5	11.4	8.2	8.4
25°	296.5	290.2	273.4	249.3	214.7	175.7	135.4	45.4	10.6	7.5	7.8
27.5°	359.3	353.1	333.9	305.3	268.2	221.8	169.2	52.3	9.7	6.7	7.3
30°	417.7	409.9	386.7	354.4	310.2	260.1	200.9	58.1	8.6	5.8	6.7
32.5°	465.9	458.8	432.5	395.0	346.8	293.0	227.8	62.6	7.5	5.2	6.3
35°	498.4	491.1	466.8	425.6	373.1	316.9	249.7	64.4	6.5	4.7	6.2
37.5°	505.9	502.0	484.6	445.9	391.2	332.2	263.7	63.9	5.4	4.3	5.8
40°	497.3	498.2	490.0	457.9	400.9	338.7	269.5	60.9	4.5	3.9	5.6
42.5°	486.3	488.7	488.1	462.7	405.0	339.1	267.0	54.9	3.5	3.5	5.4
45°	476.9	479.4	482.7	460.7	402.2	334.3	259.4	46.9	2.6	3.4	5.4
47.5°	459.9	462.6	467.4	444.3	388.0	321.8	245.6	38.1	1.9	3.2	5.2
50°	432.9	434.2	432.9	406.9	360.8	301.6	223.2	29.7	1.3	3.0	5.2
52.5°	405.0	402.4	391.6	358.7	317.5	269.7	195.0	21.1	0.9	2.8	5.0
55°	328.3	324.2	316.1	296.0	272.5	230.4	157.6	11.8	0.9	2.8	4.9
57.5°	228.8	231.0	233.8	229.7	218.9	181.5	119.7	5.2	0.9	2.6	4.9
60°	192.3	190.5	190.7	188.0	170.1	132.4	82.4	2.1	0.9	2.4	4.7
62.5°	114.8	116.2	118.6	119.1	101.4	73.9	43.1	0.9	0.9	2.2	4.5
65°	43.1	45.2	39.6	34.4	27.3	20.0	10.1	0.7	1.1	2.1	4.1
67.5°	1.3	1.5	1.9	1.7	1.7	1.5	1.1	0.7	1.1	1.9	3.9
70°	0.9	0.9	0.9	0.9	0.9	0.7	0.7	0.7	0.9	1.7	3.5
72.5°	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.9	1.5	3.2
75°	0.6	0.7	0.6	0.6	0.6	0.6	0.6	0.6	0.9	1.3	2.6
77.5°	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.7	1.1	2.2
80°	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.6	0.7	0.9	1.9
82.5°	0.4	0.4	0.4	0.2	0.4	0.4	0.4	0.4	0.7	0.7	1.5
85°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.4	0.6	0.7	0.9
87.5°	0.0	0.0	0.0	0.0	0.2	0.2	0.2	0.4	0.6	0.6	0.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1318833
CATALOG NUMBER: LDSQA3D02R459835DE010 3LSQCA45R 1MMS

CANDELA DISTRIBUTION (continued):

	135°	157.5°	180°
0°	13.1	13.1	13.1
2.5°	12.3	12.3	12.3
5°	12.0	12.0	12.0
7.5°	11.6	11.6	11.6
10°	11.2	11.2	11.2
12.5°	10.8	10.8	11.0
15°	10.3	10.6	10.6
17.5°	9.9	10.3	10.5
20°	9.5	9.9	10.1
22.5°	9.0	9.5	9.9
25°	8.6	9.3	9.5
27.5°	8.2	9.2	9.5
30°	8.0	9.0	9.3
32.5°	7.7	8.8	9.2
35°	7.5	8.8	9.2
37.5°	7.5	8.6	9.2
40°	7.3	8.6	9.2
42.5°	7.3	8.6	9.2
45°	7.3	8.6	9.2
47.5°	7.1	8.6	9.3
50°	7.1	8.8	9.3
52.5°	7.1	8.8	9.3
55°	7.1	8.8	9.2
57.5°	6.9	8.6	9.2
60°	6.9	8.6	9.2
62.5°	6.5	8.4	9.0
65°	6.3	8.2	8.8
67.5°	6.0	8.0	8.4
70°	5.6	7.5	8.0
72.5°	5.0	7.1	7.7
75°	4.5	6.5	6.9
77.5°	3.9	5.8	6.2
80°	3.2	4.9	5.2
82.5°	2.4	3.7	3.9
85°	1.7	2.4	2.6
87.5°	0.7	1.1	1.3
90°	0.0	0.0	0.0

(END OF REPORT)