

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1318908

Luminaire Tested: LDSQA3D05R209835DE010 3LSQPHR1MMS

Issue Date: 1/29/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1318908  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-2)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LDSQA3D05R209835DE010 3LSQPHR1MMS  
Description: 3in Adjustable LED luminaire with, R20 optic, 3500K CCT AND, 98CRI , 3LSQPHR1MMS TRIM  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 434.0 lumens  
Efficiency: N/A  
Efficacy: 60.3 lumens/watt  
Spacing Criteria (0/90/45): 0.35 / 0.36 / 0.33  
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 7.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1318908  
CATALOG NUMBER: LDSQA3D05R209835DE010 3LSQPHR1MMS

### Luminous Intensity Polar Plot



— 0°-180°    - - 45°-225°    - - - 90°-270°



TEST NUMBER: P1318908

CATALOG NUMBER: LDSQA3D05R209835DE010 3LSQPHR1MMS

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	116	114	112	111	113	112	110	109	108	107	106	104	103	102	101	100	100	100	100	100	98
2	113	109	107	105	111	108	106	104	105	103	101	102	101	99	99	98	97	97	98	97	96
3	110	106	103	100	108	105	102	100	102	100	98	100	98	97	98	96	95	98	96	95	94
4	107	103	99	97	106	102	99	96	100	97	95	98	96	94	96	95	93	96	95	93	92
5	105	100	97	94	104	99	96	94	98	95	93	96	94	92	95	93	92	95	93	92	91
6	103	98	94	92	102	97	94	91	96	93	91	95	92	90	93	91	90	93	91	90	89
7	101	95	92	90	100	95	92	89	94	91	89	93	90	89	92	90	88	92	90	88	87
8	99	93	90	88	98	93	90	88	92	89	87	91	89	87	91	88	87	91	88	87	86
9	97	92	88	86	96	91	88	86	91	88	86	90	87	86	89	87	85	89	87	85	85
10	95	90	87	85	95	90	87	85	89	86	84	88	86	84	88	86	84	88	86	84	83

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	556503	556503	556503
5°	480746	485224	487039
10°	289408	292101	306651
15°	100096	97761	105552
20°	26282	24724	24797
25°	5739	6898	7867
30°	2466	2466	2545
35°	1388	1219	1304
40°	607	697	787
45°	195	292	292
50°	107	107	107
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 22.5°

Vertical Angle: 45°

Luminance: 292 cd/sqm



TEST NUMBER: P1318908

CATALOG NUMBER: LDSQA3D05R209835DE010 3LSQPHR1MMS

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	231.1	53.3
10°-20°	176.0	40.5
20°-30°	21.8	5.0
30°-40°	4.1	0.9
40°-50°	1.0	0.2
50°-60°	0.1	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	428.8	98.8
0°-40°	432.9	99.8
0°-60°	434.0	100.0
0°-90°	434.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	434.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	3231	3231	3231	3231	3231	
5°	2781	2779	2807	2805	2817	229
15°	561	541	548	581	592	176
25°	30	34	36	38	41	21
35°	7	7	6	6	6	4
45°	1	1	1	1	1	1
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P1318908  
 CATALOG NUMBER: LDSQA3D05R209835DE010 3LSQPHR1MMS

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	3231.3	3231.3	3231.3	3231.3	3231.3
1°	3216.2	3212.3	3215.4	3208.8	3222.4
2°	3164.8	3160.9	3160.9	3157.0	3159.0
3°	3068.9	3075.0	3071.2	3063.1	3073.5
4°	2938.2	2945.1	2951.3	2951.7	2953.3
5°	2780.8	2778.9	2806.7	2804.8	2817.2
6°	2601.4	2599.1	2611.1	2631.2	2655.9
7°	2404.2	2376.0	2408.1	2448.7	2481.9
8°	2149.0	2156.4	2178.4	2226.3	2253.0
9°	1932.5	1889.6	1936.4	1993.6	2022.6
10°	1654.9	1620.1	1670.3	1730.7	1753.5
12.5°	1041.6	1011.5	1027.7	1091.1	1101.2
15°	561.4	541.3	548.3	581.1	592.0
17.5°	286.5	268.3	264.5	285.3	287.7
20°	143.4	139.2	134.9	136.9	135.3
22.5°	66.5	72.3	71.5	67.7	72.3
25°	30.2	34.4	36.3	37.9	41.4
27.5°	18.6	17.8	20.5	22.0	22.4
30°	12.4	12.0	12.4	12.8	12.8
32.5°	8.9	8.5	8.1	8.1	8.5
35°	6.6	6.6	5.8	6.2	6.2
37.5°	4.6	4.6	4.3	4.6	4.6
40°	2.7	3.1	3.1	3.1	3.5
42.5°	1.5	1.9	1.9	1.9	1.9
45°	0.8	1.2	1.2	1.2	1.2
47.5°	0.4	0.4	0.4	0.8	0.8
50°	0.4	0.4	0.4	0.4	0.4
52.5°	0.4	0.0	0.0	0.0	0.4
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)