

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1318925

Luminaire Tested: LDSQA3D05R259835DE010 3LSQPHR1MMS

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1318925
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-3)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LDSQA3D05R259835DE010 3LSQPHR1MMS
Description: 3in Adjustable LED luminaire with, R25 optic, 3500K CCT AND, 98CRI , 3LSQPHR1MMS TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 434.0 lumens
Efficiency: N/A
Efficacy: 60.3 lumens/watt
Spacing Criteria (0/90/45): 0.43 / 0.43 / 0.4
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1318925
CATALOG NUMBER: LDSQA3D05R259835DE010 3LSQPHR1MMS

Luminous Intensity Polar Plot



0% Up
100% Dn

— 0°-180° - - 45°-225° - - - 90°-270°



TEST NUMBER: P1318925
 CATALOG NUMBER: LDSQA3D05R259835DE010 3LSQPHR1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	115	113	112	110	113	111	110	108	107	106	105	104	103	102	100	100	99	99	99	99	97
2	112	109	106	104	110	107	105	103	104	102	101	101	100	98	99	97	96	96	96	96	95
3	109	105	102	99	107	104	101	98	101	99	97	99	97	95	97	95	94	94	94	94	93
4	106	101	98	95	105	100	97	95	99	96	94	97	94	93	95	93	92	92	92	92	91
5	104	98	95	92	102	98	94	92	96	93	91	95	92	90	93	91	89	89	89	89	88
6	101	96	92	89	100	95	92	89	94	91	89	93	90	88	91	89	87	87	87	87	86
7	99	93	89	87	98	93	89	87	92	89	86	91	88	86	90	87	86	86	86	86	85
8	97	91	87	85	96	90	87	85	90	86	84	89	86	84	88	85	84	84	84	84	83
9	95	89	85	83	94	88	85	83	88	85	82	87	84	82	86	84	82	82	82	82	81
10	93	87	83	81	92	86	83	81	86	83	81	85	82	80	85	82	80	80	80	80	80

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	404999	404999	404999
5°	367008	370362	372160
10°	275907	277866	279160
15°	136612	132547	141372
20°	38579	39221	39642
25°	6689	12656	7943
30°	2625	2685	2764
35°	820	904	904
40°	270	337	270
45°	195	97	195
50°	107	0	107
55°	120	0	120
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 195 cd/sqm



TEST NUMBER: P1318925

CATALOG NUMBER: LDSQA3D05R259835DE010 3LSQPHR1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	186.8	43.0
10°-20°	210.7	48.5
20°-30°	32.7	7.5
30°-40°	3.3	0.8
40°-50°	0.5	0.1
50°-60°	0.1	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	430.2	99.1
0°-40°	433.5	99.9
0°-60°	434.0	100.0
0°-90°	434.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	434.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2352	2352	2352	2352	2352	
5°	2123	2127	2142	2151	2153	185
15°	766	761	743	777	793	210
25°	35	52	67	51	42	30
35°	4	4	4	5	4	3
45°	1	0	0	0	1	1
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P1318925
 CATALOG NUMBER: LDSQA3D05R259835DE010 3LSQPHR1MMS

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2351.6	2351.6	2351.6	2351.6	2351.6
1°	2342.0	2345.1	2341.6	2345.4	2345.1
2°	2317.6	2320.7	2316.4	2318.7	2318.7
3°	2267.7	2274.2	2278.1	2280.8	2283.1
4°	2201.9	2209.2	2215.0	2222.0	2222.0
5°	2122.9	2126.8	2142.3	2150.8	2152.7
6°	2028.9	2044.4	2056.0	2073.0	2062.6
7°	1934.9	1947.6	1963.9	1966.6	1974.0
8°	1828.1	1841.6	1856.7	1854.0	1847.8
9°	1698.0	1717.8	1735.6	1729.8	1737.5
10°	1577.7	1589.7	1588.9	1583.1	1596.3
11°	1438.0	1440.7	1425.6	1449.2	1434.9
12°	1272.4	1274.7	1255.3	1278.6	1293.3
13°	1113.7	1108.3	1081.6	1112.2	1130.7
14°	931.1	933.0	898.9	958.1	953.5
15°	766.2	760.8	743.4	776.7	792.9
17.5°	408.3	411.7	407.5	424.1	434.6
20°	210.5	216.3	214.0	221.0	216.3
22.5°	109.1	117.3	119.6	114.2	99.5
25°	35.2	52.2	66.6	50.7	41.8
27.5°	21.3	20.9	32.5	22.4	22.8
30°	13.2	12.8	13.5	13.5	13.9
32.5°	7.4	7.7	7.4	8.1	7.7
35°	3.9	4.3	4.3	4.6	4.3
37.5°	2.3	2.7	2.7	2.7	2.3
40°	1.2	1.5	1.5	1.2	1.2
42.5°	0.8	0.8	0.8	0.8	0.8
45°	0.8	0.4	0.4	0.4	0.8
47.5°	0.4	0.4	0.0	0.4	0.4
50°	0.4	0.4	0.0	0.4	0.4
52.5°	0.4	0.0	0.0	0.0	0.4
55°	0.4	0.0	0.0	0.0	0.4
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1318925
CATALOG NUMBER: LDSQA3D05R259835DE010 3LSQPHR1MMS

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)