

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1319068

Luminaire Tested: LDSQA3D09R259835DE010 3LSQCDR1MMS

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1319068
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-23)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LDSQA3D09R259835DE010 3LSQCDR1MMS
Description: 3in Adjustable LED luminaire with, R25 optic, 3500K CCT AND, 98CRI , 3LSQCDR1MMS TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 744.0 lumens
Efficiency: N/A
Efficacy: 67.6 lumens/watt
Spacing Criteria (0/90/45): 0.44 / 0.45 / 0.41
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1319068
CATALOG NUMBER: LDSQA3D09R259835DE010 3LSQCDR1MMS

Luminous Intensity Polar Plot



— 0°-180° - - 45°-225° - - - 90°-270°



TEST NUMBER: P1319068

CATALOG NUMBER: LDSQA3D09R259835DE010 3LSQCDR1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									20
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	99	99	97	97	97	97	97	97	97	97	97	97	100															
1	115	113	111	110	113	111	110	108	107	106	105	103	103	102	100	99	99	97	97	97	97	97	97	97	97	97	97	97	97	97	97															
2	112	108	105	103	110	107	104	102	104	102	100	101	99	98	98	97	96	94	94	94	94	94	94	94	94	94	94	94	94	94	94															
3	108	104	101	98	107	103	100	97	100	98	96	98	96	94	96	94	93	92	92	92	92	92	92	92	92	92	92	92	92	92	92															
4	105	100	97	94	104	99	96	93	97	95	92	96	93	91	94	92	90	89	89	89	89	89	89	89	89	89	89	89	89	89	89															
5	103	97	93	90	101	96	93	90	95	92	89	93	91	89	92	90	88	87	87	87	87	87	87	87	87	87	87	87	87	87	87															
6	100	94	90	87	99	93	90	87	92	89	87	91	88	86	90	87	85	84	84	84	84	84	84	84	84	84	84	84	84	84	84															
7	97	91	87	85	96	91	87	84	90	86	84	89	86	84	88	85	83	82	82	82	82	82	82	82	82	82	82	82	82	82	82															
8	95	89	85	82	94	88	85	82	87	84	82	87	84	82	86	83	81	80	80	80	80	80	80	80	80	80	80	80	80	80	80															
9	93	86	83	80	92	86	82	80	85	82	80	85	82	80	84	81	79	78	78	78	78	78	78	78	78	78	78	78	78	78	78															
10	91	84	81	78	90	84	80	78	83	80	78	83	80	78	82	79	77	76	76	76	76	76	76	76	76	76	76	76	76	76	76															

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	615575	615575	615575
5°	567601	568881	570073
10°	440696	442305	444701
15°	217791	226956	227045
20°	73329	78259	74795
25°	30366	33730	31240
30°	11912	14975	12031
35°	3112	6118	3238
40°	1147	2428	1147
45°	146	706	146
50°	0	161	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°
 Vertical Angle: 45°
 Luminance: 706 cd/sqm



TEST NUMBER: P1319068

CATALOG NUMBER: LDSQA3D09R259835DE010 3LSQCDR1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	289.6	38.9
10°-20°	350.3	47.1
20°-30°	85.5	11.5
30°-40°	16.6	2.2
40°-50°	1.9	0.3
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	725.5	97.5
0°-40°	742.1	99.7
0°-60°	744.0	100.0
0°-90°	744.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	744.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3574	3574	3574	3574	3574	
5°	3283	3288	3291	3305	3298	289
15°	1222	1251	1273	1285	1273	344
25°	160	168	178	170	164	81
35°	15	21	29	21	15	13
45°	1	2	3	2	1	1
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P1319068

CATALOG NUMBER: LDSQA3D09R259835DE010 3LSQCDR1MMS

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3574.3	3574.3	3574.3	3574.3	3574.3
1°	3560.6	3562.9	3563.5	3566.9	3560.0
2°	3528.1	3528.6	3530.3	3537.2	3530.9
3°	3468.1	3472.1	3472.7	3481.8	3483.5
4°	3386.5	3388.8	3393.4	3408.8	3395.1
5°	3283.2	3287.8	3290.6	3304.9	3297.5
6°	3155.3	3156.5	3162.8	3179.3	3169.0
7°	3025.2	3024.6	3025.2	3038.3	3035.5
8°	2868.2	2865.4	2874.5	2890.5	2901.3
9°	2704.4	2708.4	2714.1	2729.5	2717.0
10°	2520.0	2530.9	2529.2	2530.3	2542.9
11°	2307.7	2311.1	2311.7	2323.7	2322.0
12°	2058.3	2058.3	2077.1	2096.5	2090.2
13°	1806.6	1824.3	1811.7	1815.7	1840.8
14°	1513.2	1526.9	1544.0	1560.0	1547.4
15°	1221.5	1250.6	1272.9	1285.4	1273.4
17.5°	699.8	709.5	728.3	730.6	723.2
20°	400.1	412.1	427.0	422.4	408.1
22.5°	251.7	255.1	270.0	262.6	259.1
25°	159.8	168.4	177.5	170.1	164.4
27.5°	99.3	105.0	114.7	106.7	100.5
30°	59.9	65.1	75.3	64.5	60.5
32.5°	31.4	38.8	47.4	39.4	31.4
35°	14.8	21.1	29.1	21.1	15.4
37.5°	9.1	11.4	17.7	11.4	9.1
40°	5.1	7.4	10.8	7.4	5.1
42.5°	2.3	4.0	5.1	4.0	2.9
45°	0.6	1.7	2.9	1.7	0.6
47.5°	0.0	0.0	1.7	0.6	0.0
50°	0.0	0.0	0.6	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1319068
CATALOG NUMBER: LDSQA3D09R259835DE010 3LSQCDR1MMS

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)