

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1319182

Luminaire Tested: LDSQA3D13R159835DE010 3LSQCDR1MB

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1319182
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-21)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LDSQA3D13R159835DE010 3LSQCDR1MB
Description: 3in Adjustable LED luminaire with, R15 optic, 3500K CCT AND, 98CRI , 3LSQCDR1MB TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 957.0 lumens
Efficiency: N/A
Efficacy: 66.0 lumens/watt
Spacing Criteria (0/90/45): 0.29 / 0.29 / 0.29
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1319182
CATALOG NUMBER: LDSQA3D13R159835DE010 3LSQCDR1MB

Luminous Intensity Polar Plot





TEST NUMBER: P1319182
 CATALOG NUMBER: LDSQA3D13R159835DE010 3LSQCDR1MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	116	114	112	111	113	112	110	109	108	107	106	104	103	102	101	100	100	100	100	100	98
2	113	109	107	105	111	108	106	104	105	103	101	102	101	99	99	98	97	97	98	97	96
3	110	106	103	100	108	105	102	100	102	100	98	100	98	97	98	96	95	95	98	96	94
4	107	103	99	97	106	102	99	96	100	97	95	98	96	94	96	95	93	93	96	95	92
5	105	100	97	94	104	99	96	94	98	95	93	96	94	92	95	93	91	91	95	93	90
6	103	97	94	92	102	97	94	91	96	93	91	94	92	90	93	91	90	90	93	91	89
7	101	95	92	90	100	95	92	89	94	91	89	93	90	88	92	90	88	88	92	90	87
8	99	93	90	88	98	93	90	88	92	89	87	91	89	87	90	88	87	87	90	88	86
9	97	91	88	86	96	91	88	86	90	88	86	90	87	85	89	87	85	85	89	87	84
10	95	90	87	84	95	90	86	84	89	86	84	88	86	84	88	85	84	84	88	85	83

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1476757	1476757	1476757
5°	1202349	1206274	1203923
10°	560873	565892	558757
15°	176123	177603	176533
20°	69773	72559	67555
25°	28200	34091	27193
30°	11296	15512	10679
35°	3343	6833	3175
40°	1012	2563	854
45°	195	560	195
50°	0	214	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°
 Vertical Angle: 45°
 Luminance: 560 cd/sqm



TEST NUMBER: P1319182

CATALOG NUMBER: LDSQA3D13R159835DE010 3LSQCDR1MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	536.9	56.1
10°-20°	321.1	33.6
20°-30°	81.0	8.5
30°-40°	16.5	1.7
40°-50°	1.5	0.2
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	938.9	98.1
0°-40°	955.4	99.8
0°-60°	957.0	100.0
0°-90°	957.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	957.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	8575	8575	8575	8575	8575	
5°	6955	6942	6978	6960	6964	535
15°	988	996	996	982	990	321
25°	148	162	179	159	143	76
35°	16	21	32	20	15	13
45°	1	2	2	2	1	1
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P1319182
 CATALOG NUMBER: LDSQA3D13R159835DE010 3LSQCDR1MB

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	8574.7	8574.7	8574.7	8574.7	8574.7
1°	8497.5	8526.2	8511.1	8523.2	8509.6
2°	8313.5	8352.1	8340.0	8336.2	8346.8
3°	7989.6	8034.2	8032.7	8021.4	8003.2
4°	7547.5	7529.3	7557.4	7554.3	7523.3
5°	6954.8	6942.0	6977.5	6960.1	6963.9
6°	6229.7	6285.7	6273.6	6275.1	6289.5
7°	5450.8	5481.0	5506.8	5528.0	5498.5
8°	4735.5	4727.9	4730.2	4754.4	4672.6
9°	3934.6	3981.5	3951.3	3902.8	3933.8
10°	3207.2	3235.9	3235.9	3193.6	3195.1
11°	2557.0	2580.4	2563.8	2574.4	2507.8
12°	2061.2	2002.9	1989.3	1999.9	1999.1
13°	1573.7	1577.5	1573.7	1572.9	1565.4
14°	1233.8	1253.5	1245.2	1224.7	1215.7
15°	987.8	996.1	996.1	981.8	990.1
17.5°	593.4	603.3	605.6	595.7	595.7
20°	380.7	385.3	395.9	381.5	368.6
22.5°	234.7	244.5	262.7	241.5	230.9
25°	148.4	162.0	179.4	159.0	143.1
27.5°	93.1	104.5	119.6	99.9	90.1
30°	56.8	64.3	78.0	62.8	53.7
32.5°	31.8	37.8	49.2	36.3	30.3
35°	15.9	21.2	32.5	20.4	15.1
37.5°	9.1	11.4	20.4	9.8	8.3
40°	4.5	6.1	11.4	6.1	3.8
42.5°	1.5	3.0	4.5	3.0	1.5
45°	0.8	1.5	2.3	1.5	0.8
47.5°	0.0	0.0	0.8	0.0	0.0
50°	0.0	0.0	0.8	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1319182
CATALOG NUMBER: LDSQA3D13R159835DE010 3LSQCDR1MB

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)