

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1318982

Luminaire Tested: LDSQA3D05R459835DE010 3LSQCDR1MMS

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1318982
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-32)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LDSQA3D05R459835DE010 3LSQCDR1MMS
Description: 3in Adjustable LED luminaire with, R45 optic, 3500K CCT AND, 98CRI , 3LSQCDR1MMS TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 520.0 lumens
Efficiency: N/A
Efficacy: 72.2 lumens/watt
Spacing Criteria (0/90/45): 0.72 / 0.74 / 0.67
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1318982
CATALOG NUMBER: LDSQA3D05R459835DE010 3LSQCDR1MMS

Luminous Intensity Polar Plot



— 0°-180° - - 45°-225° - - - 90°-270°



TEST NUMBER: P1318982

CATALOG NUMBER: LDSQA3D05R459835DE010 3LSQCDR1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	97	97	97	95
2	110	106	103	100	108	104	101	99	101	99	96	98	96	94	95	94	92	92	92	92	91
3	106	100	96	93	104	99	95	92	97	93	91	94	92	89	92	90	88	88	88	88	87
4	102	95	91	87	100	94	90	87	92	89	86	90	87	85	89	86	84	84	84	84	83
5	98	91	86	83	96	90	86	82	88	85	82	87	83	81	85	82	80	80	80	80	79
6	94	87	82	78	93	86	81	78	85	81	78	83	80	77	82	79	77	77	77	77	75
7	91	83	78	75	89	82	78	74	81	77	74	80	76	74	79	76	73	73	73	73	72
8	87	79	75	71	86	79	74	71	78	74	71	77	73	70	76	73	70	70	70	70	69
9	84	76	71	68	83	76	71	68	75	71	68	74	70	68	73	70	67	67	67	67	66
10	81	73	68	65	80	73	68	65	72	68	65	71	67	65	71	67	65	65	65	65	64

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	173222	173222	173222
5°	173607	174609	176355
10°	169266	169598	174058
15°	142799	142870	147559
20°	110240	111798	113631
25°	68391	68467	68904
30°	28219	29969	27742
35°	8767	10722	8452
40°	2698	3732	2518
45°	195	1413	195
50°	0	214	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°
 Vertical Angle: 45°
 Luminance: 1413 cd/sqm



TEST NUMBER: P1318982

CATALOG NUMBER: LDSQA3D05R459835DE010 3LSQCDR1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	95.7	18.4
10°-20°	222.6	42.8
20°-30°	163.3	31.4
30°-40°	35.1	6.7
40°-50°	3.3	0.6
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	481.6	92.6
0°-40°	516.6	99.4
0°-60°	520.0	100.0
0°-90°	520.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	520.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1006	1006	1006	1006	1006	
5°	1004	1007	1010	1017	1020	95
15°	801	799	801	814	828	221
25°	360	359	360	360	363	161
35°	42	45	51	44	40	33
45°	1	2	6	2	1	2
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P1318982

CATALOG NUMBER: LDSQA3D05R459835DE010 3LSQCDR1MMS

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1005.8	1005.8	1005.8	1005.8	1005.8
1°	1003.8	1006.2	1006.2	1007.7	1008.5
2°	1004.6	1006.2	1005.8	1008.5	1009.6
3°	1003.5	1006.2	1006.9	1010.0	1012.0
4°	1003.8	1006.2	1008.5	1013.1	1015.8
5°	1004.2	1006.9	1010.0	1017.0	1020.1
6°	1004.6	1006.5	1010.0	1018.9	1024.7
7°	1000.7	1003.5	1007.3	1018.5	1024.7
8°	994.6	996.1	999.2	1013.9	1021.2
9°	983.0	982.6	987.2	1003.5	1012.0
10°	967.9	963.3	969.8	986.1	995.3
11°	943.5	938.5	944.3	961.7	970.6
12°	911.8	911.8	913.0	928.5	943.9
13°	878.2	874.3	876.7	894.1	904.9
14°	841.1	837.2	839.6	852.7	869.7
15°	800.9	799.4	801.3	814.0	827.6
17.5°	705.4	702.0	708.9	721.7	728.6
20°	601.5	607.3	610.0	618.1	620.0
22.5°	482.0	488.2	492.1	493.2	494.4
25°	359.9	358.7	360.3	360.3	362.6
27.5°	236.6	236.6	240.8	238.1	235.4
30°	141.9	147.7	150.7	145.7	139.5
32.5°	77.3	83.1	88.1	80.8	75.4
35°	41.7	44.8	51.0	43.7	40.2
37.5°	22.8	25.5	29.4	24.7	22.8
40°	12.0	14.7	16.6	14.7	11.2
42.5°	3.9	7.3	9.7	7.3	3.5
45°	0.8	2.3	5.8	2.3	0.8
47.5°	0.0	0.4	2.7	0.4	0.0
50°	0.0	0.0	0.8	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1318982
CATALOG NUMBER: LDSQA3D05R459835DE010 3LSQCDR1MMS

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)