

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1319087

Luminaire Tested: LDSQA3D09R309835DE010 3LSQPHR1MB

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1319087
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-4)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LDSQA3D09R309835DE010 3LSQPHR1MB
Description: 3in Adjustable LED luminaire with, R30 optic, 3500K CCT AND, 98CRI , 3LSQPHR1MB TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 662.0 lumens
Efficiency: N/A
Efficacy: 60.2 lumens/watt
Spacing Criteria (0/90/45): 0.5 / 0.49 / 0.46
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1319087
CATALOG NUMBER: LDSQA3D09R309835DE010 3LSQPHR1MB

Luminous Intensity Polar Plot



— 0°-180° - - 45°-225° - - - 90°-270°



TEST NUMBER: P1319087

CATALOG NUMBER: LDSQA3D09R309835DE010 3LSQPHR1MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	99	99	100
1	115	113	111	110	113	111	109	108	107	106	105	103	103	102	100	99	99	97	97	97	97
2	112	108	105	103	110	107	104	102	104	101	100	101	99	98	98	97	96	94	94	94	94
3	108	104	101	98	107	103	100	97	100	98	96	98	96	94	96	94	93	92	92	92	92
4	105	100	97	94	104	99	96	93	97	94	92	95	93	91	94	92	90	89	89	89	89
5	102	97	93	90	101	96	93	90	95	91	89	93	90	88	92	89	88	87	87	87	87
6	100	94	90	87	99	93	90	87	92	89	86	91	88	86	90	87	85	84	84	84	84
7	97	91	87	84	96	91	87	84	90	86	84	88	86	83	88	85	83	82	82	82	82
8	95	89	85	82	94	88	84	82	87	84	82	86	83	81	86	83	81	80	80	80	80
9	92	86	82	80	92	86	82	80	85	82	79	84	81	79	84	81	79	78	78	78	78
10	90	84	80	78	90	84	80	78	83	80	77	82	79	77	82	79	77	76	76	76	76

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	470529	470529	470529
5°	458410	455264	451512
10°	386868	374977	368891
15°	233142	226617	230789
20°	79083	91326	105328
25°	14537	22784	26889
30°	4992	5568	6244
35°	1430	1808	1913
40°	382	652	517
45°	146	146	146
50°	161	0	161
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 52.5°

Luminance: 170 cd/sqm



TEST NUMBER: P1319087

CATALOG NUMBER: LDSQA3D09R309835DE010 3LSQPHR1MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	236.2	35.7
10°-20°	345.3	52.2
20°-30°	73.1	11.0
30°-40°	6.7	1.0
40°-50°	0.7	0.1
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	654.6	98.9
0°-40°	661.3	99.9
0°-60°	662.0	100.0
0°-90°	662.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	662.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2732	2732	2732	2732	2732	
5°	2652	2646	2633	2625	2612	239
15°	1308	1303	1271	1301	1294	345
25°	76	86	120	141	142	56
35°	7	9	9	10	9	6
45°	1	1	1	1	1	1
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P1319087
 CATALOG NUMBER: LDSQA3D09R309835DE010 3LSQPHR1MB

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2732.1	2732.1	2732.1	2732.1	2732.1
1°	2732.7	2729.8	2725.8	2731.5	2727.5
2°	2727.0	2720.1	2714.4	2720.1	2718.4
3°	2709.8	2704.1	2700.1	2703.0	2703.0
4°	2684.2	2677.9	2674.5	2675.0	2666.5
5°	2651.6	2646.5	2633.4	2625.4	2611.7
6°	2603.7	2591.1	2575.1	2562.0	2544.3
7°	2538.6	2519.2	2496.4	2473.6	2451.3
8°	2434.2	2425.0	2394.2	2378.8	2356.6
9°	2336.0	2313.8	2280.7	2255.5	2243.6
10°	2212.2	2179.1	2144.2	2124.3	2109.4
11°	2065.5	2031.8	2003.8	1974.7	1951.9
12°	1893.1	1864.6	1832.6	1813.2	1786.4
13°	1688.8	1684.8	1648.8	1642.6	1639.1
14°	1513.6	1497.6	1462.2	1471.9	1474.2
15°	1307.6	1303.0	1271.0	1300.7	1294.4
17.5°	819.0	820.7	840.7	887.5	902.3
20°	431.5	444.6	498.3	554.8	574.7
22.5°	174.6	203.8	258.5	296.8	322.5
25°	76.5	85.6	119.9	141.0	141.5
27.5°	43.4	43.9	57.6	59.9	61.1
30°	25.1	25.7	28.0	29.7	31.4
32.5°	13.7	14.8	15.4	17.7	17.7
35°	6.8	8.6	8.6	10.3	9.1
37.5°	4.0	4.6	5.1	5.1	4.6
40°	1.7	2.3	2.9	2.9	2.3
42.5°	0.6	1.1	1.1	1.1	1.7
45°	0.6	0.6	0.6	0.6	0.6
47.5°	0.6	0.6	0.0	0.6	0.6
50°	0.6	0.0	0.0	0.0	0.6
52.5°	0.6	0.0	0.0	0.0	0.6
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1319087
CATALOG NUMBER: LDSQA3D09R309835DE010 3LSQPHR1MB

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)