

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1319543

Luminaire Tested: LDSQA3D20R359835D010 3LSQPHR1MMS

Issue Date: 1/29/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1319543  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-5)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LDSQA3D20R359835D010 3LSQPHR1MMS  
Description: 3in Adjustable LED luminaire with, R35 optic, 3500K CCT AND, 98CRI , 3LSQPHR1MMS TRIM  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1850.0 lumens  
Efficiency: N/A  
Efficacy: 67.5 lumens/watt  
Spacing Criteria (0/90/45): 0.57 / 0.56 / 0.51  
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 27.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1319543  
CATALOG NUMBER: LDSQA3D20R359835D010 3LSQPHR1MMS

### Luminous Intensity Polar Plot



0% Up  
100% Dn

— 0°-180°    - - 45°-225°    - - - 90°-270°



TEST NUMBER: P1319543

CATALOG NUMBER: LDSQA3D20R359835D010 3LSQPHR1MMS

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	97
2	111	108	105	102	109	106	103	101	103	101	99	100	98	97	97	96	95	93
3	108	103	100	97	106	102	99	96	99	97	94	97	95	93	95	93	92	90
4	104	99	95	92	103	98	94	92	96	93	91	94	92	90	93	90	89	87
5	101	95	91	88	100	95	91	88	93	90	87	92	89	87	90	88	86	85
6	98	92	88	85	97	91	88	85	90	87	84	89	86	84	88	85	83	82
7	96	89	85	82	94	89	85	82	87	84	81	86	83	81	85	83	81	80
8	93	86	82	79	92	86	82	79	85	81	79	84	81	79	83	80	78	77
9	90	84	80	77	89	83	79	77	82	79	76	82	79	76	81	78	76	75
10	88	81	77	75	87	81	77	74	80	77	74	80	76	74	79	76	74	73

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	1049714	1049714	1049714
5°	1031682	1029486	1027273
10°	945521	917103	894806
15°	677051	655459	647507
20°	313951	324764	336146
25°	74490	105978	110520
30°	21875	25037	28199
35°	5025	8031	7380
40°	1079	2158	1439
45°	390	390	390
50°	429	0	429
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 52.5°

Luminance: 453 cd/sqm



TEST NUMBER: P1319543

CATALOG NUMBER: LDSQA3D20R359835D010 3LSQPHR1MMS

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	547.2	29.6
10°-20°	978.3	52.9
20°-30°	294.3	15.9
30°-40°	28.1	1.5
40°-50°	1.9	0.1
50°-60°	0.1	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1819.8	98.4
0°-40°	1847.9	99.9
0°-60°	1850.0	100.0
0°-90°	1850.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1850.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	6095	6095	6095	6095	6095	
5°	5968	5966	5955	5947	5942	553
15°	3797	3769	3676	3660	3632	1003
25°	392	432	558	582	582	252
35°	24	32	38	41	35	22
45°	2	2	2	2	2	2
55°	0	0	0	0	0	1
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P1319543

CATALOG NUMBER: LDSQA3D20R359835D010 3LSQPHR1MMS

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	6095.1	6095.1	6095.1	6095.1	6095.1
1°	6091.9	6091.9	6088.7	6088.7	6082.4
2°	6077.6	6079.2	6072.8	6071.2	6066.4
3°	6055.3	6050.5	6050.5	6047.3	6044.1
4°	6020.2	6010.7	6007.5	6009.1	6002.7
5°	5967.6	5966.0	5954.9	5946.9	5942.1
6°	5910.3	5899.1	5875.2	5854.5	5849.7
7°	5824.2	5800.3	5779.6	5736.6	5730.2
8°	5719.0	5680.8	5636.2	5575.6	5572.4
9°	5590.0	5527.8	5465.7	5384.4	5355.7
10°	5406.7	5349.4	5244.2	5172.5	5116.7
11°	5178.9	5107.1	4984.4	4898.4	4852.2
12°	4920.7	4853.8	4710.4	4632.3	4567.0
13°	4589.3	4533.5	4399.6	4313.6	4262.6
14°	4205.2	4163.8	4036.3	3998.1	3980.5
15°	3797.3	3768.6	3676.2	3660.3	3631.6
17.5°	2795.0	2747.2	2694.6	2704.2	2713.7
20°	1713.0	1779.9	1772.0	1807.0	1834.1
22.5°	854.1	940.2	1040.6	1101.1	1131.4
25°	392.0	431.8	557.7	581.6	581.6
27.5°	197.6	207.2	262.9	267.7	280.5
30°	110.0	117.9	125.9	140.2	141.8
32.5°	55.8	65.3	68.5	76.5	73.3
35°	23.9	31.9	38.2	41.4	35.1
37.5°	11.2	14.3	20.7	19.1	14.3
40°	4.8	6.4	9.6	8.0	6.4
42.5°	3.2	3.2	4.8	3.2	3.2
45°	1.6	1.6	1.6	1.6	1.6
47.5°	1.6	1.6	0.0	1.6	1.6
50°	1.6	0.0	0.0	0.0	1.6
52.5°	1.6	0.0	0.0	0.0	1.6
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1319543  
CATALOG NUMBER: LDSQA3D20R359835D010 3LSQPHR1MMS

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)