

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1319669

Luminaire Tested: LDSQA3D02R309840DE010 3LSQCDR1MMS

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1319669
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-24)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LDSQA3D02R309840DE010 3LSQCDR1MMS
Description: 3in Adjustable LED luminaire with, R30 optic, 4000K CCT AND, 98CRI , 3LSQCDR1MMS TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 244.0 lumens
Efficiency: N/A
Efficacy: 67.8 lumens/watt
Spacing Criteria (0/90/45): 0.51 / 0.51 / 0.46
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1319669
CATALOG NUMBER: LDSQA3D02R309840DE010 3LSQCDR1MMS

Luminous Intensity Polar Plot





TEST NUMBER: P1319669

CATALOG NUMBER: LDSQA3D02R309840DE010 3LSQCDR1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	115	113	111	110	113	111	109	108	107	106	105	103	102	101	100	99	99	99	99	99	97
2	112	108	105	103	109	106	104	102	103	101	99	100	99	97	98	96	95	95	95	95	94
3	108	104	100	97	106	102	99	97	100	97	95	98	95	94	95	94	92	92	92	92	91
4	105	100	96	93	103	99	95	92	97	94	91	95	92	90	93	91	89	89	89	89	88
5	102	96	92	89	101	95	92	89	94	91	88	92	90	87	91	89	87	87	87	87	86
6	99	93	89	86	98	92	89	86	91	88	85	90	87	85	89	86	84	84	84	84	83
7	96	90	86	83	95	90	86	83	89	85	83	87	85	82	87	84	82	82	82	82	81
8	94	88	83	81	93	87	83	81	86	83	80	85	82	80	84	82	80	80	80	80	79
9	91	85	81	78	91	85	81	78	84	80	78	83	80	78	82	80	78	78	78	78	77
10	89	83	79	76	88	82	79	76	82	78	76	81	78	76	80	78	76	76	76	76	75

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	162854	162854	162854
5°	158877	159085	159966
10°	135706	135077	134272
15°	83747	82766	83069
20°	31652	31817	31780
25°	9729	10679	10166
30°	3918	4972	4077
35°	1156	2123	1198
40°	472	854	472
45°	97	268	97
50°	0	54	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°
 Vertical Angle: 45°
 Luminance: 268 cd/sqm



TEST NUMBER: P1319669

CATALOG NUMBER: LDSQA3D02R309840DE010 3LSQCDR1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	83.4	34.2
10°-20°	123.5	50.6
20°-30°	30.6	12.6
30°-40°	5.8	2.4
40°-50°	0.7	0.3
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	237.5	97.3
0°-40°	243.3	99.7
0°-60°	244.0	100.0
0°-90°	244.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	244.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	946	946	946	946	946	
5°	919	919	920	922	925	83
15°	470	465	464	468	466	124
25°	51	55	56	56	54	29
35°	6	7	10	7	6	5
45°	0	1	1	1	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P1319669
 CATALOG NUMBER: LDSQA3D02R309840DE010 3LSQCDR1MMS

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	945.6	945.6	945.6	945.6	945.6
1°	946.0	945.2	945.2	944.1	946.2
2°	942.6	941.8	943.1	942.2	944.9
3°	937.5	936.5	938.4	939.0	940.3
4°	929.9	929.1	931.2	932.3	935.9
5°	919.0	918.7	920.2	921.7	925.3
6°	904.2	903.7	904.6	906.5	908.8
7°	882.8	881.7	882.4	882.8	883.4
8°	855.7	854.0	853.0	855.1	856.2
9°	820.7	818.8	816.8	816.0	818.7
10°	776.0	773.1	772.4	770.5	767.8
11°	724.0	721.7	721.1	717.7	716.2
12°	664.4	663.2	664.6	662.5	661.7
13°	607.3	600.0	599.1	595.1	593.0
14°	539.7	533.1	532.9	530.8	533.6
15°	469.7	465.1	464.2	467.8	465.9
17.5°	299.5	302.5	301.7	299.8	296.6
20°	172.7	170.6	173.6	174.4	173.4
22.5°	92.0	92.8	93.4	95.6	97.2
25°	51.2	54.7	56.2	56.0	53.5
27.5°	31.9	34.0	36.8	34.9	32.8
30°	19.7	21.4	25.0	21.6	20.5
32.5°	10.6	13.5	16.1	13.5	11.0
35°	5.5	7.2	10.1	7.4	5.7
37.5°	3.6	4.2	6.5	4.2	3.6
40°	2.1	2.7	3.8	2.7	2.1
42.5°	0.9	1.5	2.1	1.5	0.9
45°	0.4	0.6	1.1	0.8	0.4
47.5°	0.0	0.2	0.6	0.2	0.0
50°	0.0	0.0	0.2	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1319669
CATALOG NUMBER: LDSQA3D02R309840DE010 3LSQCDR1MMS

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)