

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1319721

Luminaire Tested: LDSQA3D02R509840DE010 3LSQCDR1MMS

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1319721
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-27)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LDSQA3D02R509840DE010 3LSQCDR1MMS
Description: 3in Adjustable LED luminaire with, R50 optic, 4000K CCT AND, 98CRI , 3LSQCDR1MMS TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 265.0 lumens
Efficiency: N/A
Efficacy: 73.6 lumens/watt
Spacing Criteria (0/90/45): 0.85 / 0.85 / 0.78
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1319721
CATALOG NUMBER: LDSQA3D02R509840DE010 3LSQCDR1MMS

Luminous Intensity Polar Plot





TEST NUMBER: P1319721

CATALOG NUMBER: LDSQA3D02R509840DE010 3LSQCDR1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	114	112	109	107	112	110	108	106	106	104	102	102	101	99	98	97	97	97	97	97	95
2	109	105	101	98	107	103	100	97	100	98	95	97	95	93	95	93	91	91	91	91	90
3	105	99	95	91	103	98	94	90	95	92	89	93	90	88	91	88	86	86	86	86	85
4	100	94	89	85	99	93	88	85	90	87	84	89	85	83	87	84	82	82	82	82	80
5	96	89	84	80	95	88	83	79	86	82	79	85	81	78	83	80	77	77	77	77	76
6	92	84	79	75	91	83	79	75	82	78	74	81	77	74	79	76	73	73	73	73	72
7	88	80	75	71	87	79	74	71	78	74	70	77	73	70	76	72	70	70	70	70	69
8	85	76	71	67	83	76	71	67	75	70	67	74	70	67	73	69	66	66	66	66	65
9	81	73	67	64	80	72	67	64	71	67	64	70	66	63	70	66	63	63	63	63	62
10	78	69	64	61	77	69	64	61	68	64	60	67	63	60	67	63	60	60	60	60	59

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	70870	70870	70870
5°	69636	69446	69239
10°	67154	66437	66559
15°	61780	60996	61174
20°	55166	54653	54964
25°	42927	44732	42471
30°	23267	25972	22850
35°	7338	8725	7169
40°	1619	2248	1529
45°	49	682	49
50°	0	107	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°

Vertical Angle: 45°

Luminance: 682 cd/sqm



TEST NUMBER: P1319721

CATALOG NUMBER: LDSQA3D02R509840DE010 3LSQCDR1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	37.7	14.2
10°-20°	95.8	36.1
20°-30°	100.9	38.1
30°-40°	28.8	10.9
40°-50°	1.8	0.7
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	234.4	88.5
0°-40°	263.2	99.3
0°-60°	265.0	100.0
0°-90°	265.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	265.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	412	412	412	412	412	
5°	403	402	402	401	400	38
15°	346	344	342	343	343	97
25°	226	234	235	233	224	99
35°	35	37	42	35	34	27
45°	0	1	3	1	0	1
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P1319721

CATALOG NUMBER: LDSQA3D02R509840DE010 3LSQCDR1MMS

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	411.5	411.5	411.5	411.5	411.5
1°	411.7	411.9	411.5	411.9	411.0
2°	411.1	410.8	410.4	410.6	410.0
3°	409.1	408.9	408.1	408.3	407.5
4°	406.4	405.8	405.3	404.9	404.1
5°	402.8	402.4	401.7	401.3	400.5
6°	399.8	399.0	397.7	397.3	396.5
7°	395.8	395.4	393.7	393.3	392.9
8°	392.8	391.6	389.5	389.7	388.8
9°	388.8	387.3	385.2	385.2	385.4
10°	384.0	381.8	379.9	380.4	380.6
11°	377.8	376.3	373.4	374.7	374.7
12°	371.0	369.1	367.0	368.1	368.9
13°	363.0	361.5	359.6	360.7	360.3
14°	355.2	352.4	351.1	352.6	352.0
15°	346.5	344.2	342.1	342.7	343.1
17.5°	323.2	320.7	319.2	319.4	321.1
20°	301.0	300.1	298.2	298.9	299.9
22.5°	274.9	275.2	273.0	273.5	275.8
25°	225.9	234.3	235.4	232.8	223.5
27.5°	167.4	179.9	183.7	177.6	166.2
30°	117.0	120.4	130.6	119.0	114.9
32.5°	68.6	73.7	79.2	71.3	68.4
35°	34.9	37.3	41.5	35.3	34.1
37.5°	16.1	17.2	19.0	16.1	15.2
40°	7.2	8.5	10.0	8.2	6.8
42.5°	2.3	4.0	5.3	3.6	2.1
45°	0.2	0.9	2.8	0.9	0.2
47.5°	0.0	0.2	1.1	0.2	0.0
50°	0.0	0.0	0.4	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1319721
CATALOG NUMBER: LDSQA3D02R509840DE010 3LSQCDR1MMS

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)