

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1319973

Luminaire Tested: LDSQA3D09R359840DE010 3LSQCA30R 1MW

Issue Date: 1/29/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1319973  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-63)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LDSQA3D09R359840DE010 3LSQCA30R 1MW  
Description: 3in Adjustable LED luminaire with, R35 optic, 4000K CCT AND, 98CRI , 3LSQCA30R 1MW TRIM  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 646.0 lumens  
Efficiency: N/A  
Efficacy: 58.7 lumens/watt  
Spacing Criteria (0/90/45): 2.45 / 0.5 / 1.25  
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 11  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1319973  
CATALOG NUMBER: LDSQA3D09R359840DE010 3LSQCA30R 1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P1319973

CATALOG NUMBER: LDSQA3D09R359840DE010 3LSQCA30R 1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	109	106	104	110	107	104	102	103	101	99	99	98	96	96	94	93	91			91
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	84	83			83
3	99	91	85	81	97	90	84	80	87	83	79	85	81	77	82	79	76	74			74
4	92	83	77	72	91	82	76	71	80	75	71	78	73	70	76	72	69	67			67
5	86	76	69	64	85	75	69	64	74	68	63	72	67	63	70	66	62	61			61
6	81	70	63	58	79	69	62	58	68	62	57	66	61	57	65	60	56	55			55
7	75	64	57	52	74	64	57	52	62	56	52	61	55	51	60	55	51	49			49
8	71	59	52	47	69	59	52	47	57	51	47	56	51	47	55	50	46	45			45
9	66	55	48	43	65	54	47	43	53	47	43	52	46	42	51	46	42	41			41
10	62	50	44	39	61	50	43	39	49	43	39	48	43	39	47	42	39	37			37

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°	135°	180°
0°	11677	11677	11677	11677	11677
5°	39797	25863	10926	4616	3406
10°	128082	52429	8622	1731	1119
15°	260957	88917	6098	624	410
20°	345089	110735	3940	220	220
25°	374448	107669	2204	114	228
30°	408470	85791	915	119	239
35°	425620	53402	252	126	252
40°	403890	23336	135	270	382
45°	269620	9328	146	414	706
50°	90427	1554	322	616	938
55°	5044	180	360	871	1231
60°	413	207	586	999	1412
65°	489	245	693	1182	1671
70°	302	302	856	1460	1762
75°	399	399	1131	1530	1930
80°	0	595	1686	1686	1686
85°	0	1186	3359	1186	2371

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 269620 cd/sqm



TEST NUMBER: P1319973

CATALOG NUMBER: LDSQA3D09R359840DE010 3LSQCA30R 1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	11.8	1.8
10°-20°	92.8	14.4
20°-30°	195.8	30.3
30°-40°	222.2	34.4
40°-50°	109.4	16.9
50°-60°	9.5	1.5
60°-70°	1.9	0.3
70°-80°	1.8	0.3
80°-90°	0.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	300.4	46.5
0°-40°	522.6	80.9
0°-60°	641.4	99.3
0°-90°	646.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	646.0	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	68	68	68	68	68	
5°	230	150	63	27	20	38
15°	1464	499	34	4	2	416
25°	1970	567	12	1	1	917
35°	2024	254	1	1	1	1248
45°	1107	38	1	2	3	818
55°	17	1	1	3	4	66
65°	1	1	2	3	4	1
75°	1	1	2	2	3	0
85°	0	1	2	1	1	0
90°	0	0	0	0	0	



TEST NUMBER: P1319973

CATALOG NUMBER: LDSQA3D09R359840DE010 3LSQCA30R 1MW

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	67.5°
0°	67.8	67.8	67.8	67.8	67.8	67.8	67.8	67.8	67.8	67.8	67.8
2.5°	117.7	120.6	119.5	118.9	118.3	116.0	110.8	110.2	105.0	101.5	84.1
5°	230.2	225.6	226.7	220.4	212.2	200.6	193.1	176.9	163.5	149.6	98.0
7.5°	433.8	427.4	415.2	396.6	377.5	352.6	314.9	284.7	249.9	216.9	109.0
10°	732.4	728.9	713.3	665.7	624.0	557.3	494.6	428.5	363.6	299.8	116.6
12.5°	1131.4	1107.6	1079.2	1016.0	933.6	850.1	726.6	612.4	508.6	401.9	117.1
15°	1463.6	1448.6	1408.6	1326.2	1227.0	1106.4	959.7	806.0	649.5	498.7	111.3
17.5°	1731.0	1707.8	1656.2	1575.6	1461.3	1304.8	1133.1	945.8	755.0	567.7	101.5
20°	1882.9	1870.7	1831.3	1750.7	1626.0	1454.9	1259.5	1041.5	821.1	604.2	88.7
22.5°	1959.4	1950.8	1921.8	1857.4	1740.8	1568.6	1344.8	1091.4	840.3	600.2	75.4
25°	1970.5	1968.1	1943.2	1894.5	1797.1	1626.6	1381.9	1100.6	824.6	566.6	62.6
27.5°	2008.7	2000.6	1971.0	1922.3	1824.3	1636.5	1369.1	1068.7	774.2	507.4	52.2
30°	2054.0	2048.2	2018.6	1968.1	1852.2	1627.2	1323.9	998.0	693.5	431.4	38.9
32.5°	2050.5	2048.2	2023.2	1969.9	1832.5	1572.7	1243.3	891.9	583.9	340.4	24.4
35°	2024.4	2016.3	1985.0	1902.6	1720.0	1432.3	1090.2	748.1	462.2	254.0	15.7
37.5°	1961.8	1944.4	1891.6	1751.8	1518.7	1216.0	887.8	577.6	327.1	169.9	9.9
40°	1796.5	1774.5	1668.3	1499.6	1255.5	958.0	660.5	397.2	215.7	103.8	4.1
42.5°	1490.3	1445.7	1339.5	1166.2	937.1	677.3	433.8	257.5	127.0	62.6	1.2
45°	1107.0	1072.8	961.5	804.3	614.1	434.3	262.7	139.2	70.2	38.3	0.6
47.5°	644.8	624.0	566.6	463.3	339.2	227.9	134.5	74.8	41.2	18.6	0.6
50°	337.5	311.4	267.9	203.0	149.6	105.0	65.5	40.0	20.3	5.8	0.6
52.5°	118.3	116.6	106.1	80.0	64.9	47.0	31.9	17.4	5.8	1.2	0.6
55°	16.8	16.8	15.7	17.4	18.6	16.8	11.0	4.6	1.2	0.6	0.6
57.5°	1.2	1.2	1.2	1.7	2.3	2.3	1.7	0.6	0.6	0.6	1.2
60°	1.2	1.2	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	1.2
62.5°	1.2	1.2	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	1.2
65°	1.2	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	1.2
67.5°	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	1.2
70°	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	1.7
72.5°	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	1.7
75°	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	1.7
77.5°	0.0	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	1.7
80°	0.0	0.0	0.0	0.0	0.0	0.0	0.6	0.6	0.6	0.6	1.2
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.6	0.6	0.6	0.6	1.2
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.6	0.6	0.6	0.6	1.2
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.6	0.6	0.6	1.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1319973

CATALOG NUMBER: LDSQA3D09R359840DE010 3LSQCA30R 1MW

**CANDELA DISTRIBUTION (continued):**

	90°	112.5°	135°	157.5°	180°
0°	67.8	67.8	67.8	67.8	67.8
2.5°	67.3	53.9	42.9	37.7	36.0
5°	63.2	40.6	26.7	20.9	19.7
7.5°	56.2	29.0	16.2	11.6	11.0
10°	49.3	20.9	9.9	7.0	6.4
12.5°	41.2	14.5	6.4	4.1	3.5
15°	34.2	9.9	3.5	2.9	2.3
17.5°	27.3	6.4	2.3	1.7	2.3
20°	21.5	4.1	1.2	1.2	1.2
22.5°	16.2	2.3	1.2	1.2	1.2
25°	11.6	1.2	0.6	0.6	1.2
27.5°	8.1	0.6	0.6	0.6	1.2
30°	4.6	0.6	0.6	0.6	1.2
32.5°	2.3	0.6	0.6	1.2	1.2
35°	1.2	0.6	0.6	1.2	1.2
37.5°	0.6	0.6	0.6	1.2	1.7
40°	0.6	0.6	1.2	1.7	1.7
42.5°	0.6	0.6	1.2	1.7	2.3
45°	0.6	1.2	1.7	2.3	2.9
47.5°	1.2	1.2	2.3	2.9	3.5
50°	1.2	1.7	2.3	3.5	3.5
52.5°	1.2	1.7	2.9	3.5	4.1
55°	1.2	2.3	2.9	4.1	4.1
57.5°	1.7	2.3	2.9	4.1	4.1
60°	1.7	2.3	2.9	4.1	4.1
62.5°	1.7	2.3	2.9	4.1	4.1
65°	1.7	2.3	2.9	4.1	4.1
67.5°	1.7	2.3	2.9	3.5	4.1
70°	1.7	2.3	2.9	3.5	3.5
72.5°	2.3	2.3	2.9	3.5	3.5
75°	1.7	2.3	2.3	2.9	2.9
77.5°	1.7	1.7	1.7	2.3	2.3
80°	1.7	1.7	1.7	1.7	1.7
82.5°	1.7	1.2	1.2	1.7	1.7
85°	1.7	1.2	0.6	1.2	1.2
87.5°	1.2	1.2	0.6	0.6	0.6
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)