

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1320021

Luminaire Tested: LDSQA3D09R559840DE010 3LSQCDR1MB

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1320021
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-28)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LDSQA3D09R559840DE010 3LSQCDR1MB
Description: 3in Adjustable LED luminaire with, R55 optic, 4000K CCT AND, 98CRI , 3LSQCDR1MB TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 755.0 lumens
Efficiency: N/A
Efficacy: 68.6 lumens/watt
Spacing Criteria (0/90/45): 0.93 / 0.93 / 0.81
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1320021
CATALOG NUMBER: LDSQA3D09R559840DE010 3LSQCDR1MB

Luminous Intensity Polar Plot





TEST NUMBER: P1320021
 CATALOG NUMBER: LDSQA3D09R559840DE010 3LSQCDR1MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	114	112	109	107	112	109	107	106	105	104	102	102	100	99	98	97	96	96	96	96	95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	91	91	91	89
3	104	99	94	91	103	97	93	90	95	91	89	92	90	87	90	88	86	86	86	86	84
4	100	93	88	84	98	92	87	84	90	86	83	88	85	82	86	83	81	81	81	81	80
5	96	88	83	79	94	87	82	79	85	81	78	84	80	77	82	79	77	77	77	77	75
6	91	83	78	74	90	83	78	74	81	77	74	80	76	73	79	75	73	73	73	73	71
7	87	79	74	70	86	79	73	70	77	73	69	76	72	69	75	72	69	69	69	69	67
8	84	75	70	66	83	75	70	66	74	69	66	73	69	65	72	68	65	65	65	65	64
9	80	72	66	63	79	71	66	63	70	66	62	69	65	62	69	65	62	62	62	62	61
10	77	68	63	59	76	68	63	59	67	62	59	66	62	59	66	62	59	59	59	59	58

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	171034	171034	171034
5°	169077	168576	167677
10°	177223	175089	173865
15°	174268	172414	171790
20°	158735	159376	158845
25°	127356	129332	127356
30°	73103	74933	75509
35°	20835	25103	21445
40°	5351	7689	5463
45°	560	2679	414
50°	0	455	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°
 Vertical Angle: 45°
 Luminance: 2679 cd/sqm



TEST NUMBER: P1320021

CATALOG NUMBER: LDSQA3D09R559840DE010 3LSQCDR1MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	94.3	12.5
10°-20°	269.1	35.6
20°-30°	296.3	39.3
30°-40°	88.5	11.7
40°-50°	6.8	0.9
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	659.7	87.4
0°-40°	748.2	99.1
0°-60°	755.0	100.0
0°-90°	755.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	755.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	993	993	993	993	993	
5°	978	976	975	971	970	95
15°	977	970	967	963	964	271
25°	670	670	681	679	670	293
35°	99	106	119	109	102	82
45°	2	6	11	6	2	4
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P1320021
 CATALOG NUMBER: LDSQA3D09R559840DE010 3LSQCDR1MB

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	993.1	993.1	993.1	993.1	993.1
1°	992.5	992.5	991.3	990.8	992.5
2°	989.6	989.6	986.7	986.1	987.9
3°	983.2	982.7	980.3	978.6	979.8
4°	978.0	976.9	975.1	972.2	972.8
5°	978.0	976.3	975.1	971.1	969.9
6°	982.7	981.5	979.2	975.1	974.0
7°	990.8	988.4	986.1	980.9	979.8
8°	999.5	997.7	993.1	987.9	985.5
9°	1008.2	1004.1	998.3	993.1	992.5
10°	1013.4	1007.6	1001.2	994.8	994.2
11°	1012.8	1007.6	1000.0	994.2	993.7
12°	1010.5	1002.9	996.6	989.6	990.2
13°	1002.4	995.4	989.0	983.8	982.7
14°	991.3	985.0	979.2	974.0	974.5
15°	977.4	970.5	967.0	962.9	963.5
17.5°	928.2	926.4	928.2	923.5	925.3
20°	866.1	864.4	869.6	867.3	866.7
22.5°	779.7	782.1	791.9	789.0	783.8
25°	670.2	670.2	680.6	679.4	670.2
27.5°	527.6	531.6	538.0	540.9	533.9
30°	367.6	376.8	376.8	382.6	379.7
32.5°	205.2	224.9	229.6	232.5	220.9
35°	99.1	105.5	119.4	109.0	102.0
37.5°	47.5	50.4	64.4	52.2	48.7
40°	23.8	27.2	34.2	28.4	24.3
42.5°	9.9	14.5	18.0	14.5	9.9
45°	2.3	5.8	11.0	5.8	1.7
47.5°	0.0	0.6	5.2	1.2	0.0
50°	0.0	0.0	1.7	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1320021
CATALOG NUMBER: LDSQA3D09R559840DE010 3LSQCDR1MB

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)