

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1320107

Luminaire Tested: LDSQA3D13R309840DE010 3LSQCDR1MMS

Issue Date: 1/29/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1320107  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-24)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LDSQA3D13R309840DE010 3LSQCDR1MMS  
Description: 3in Adjustable LED luminaire with, R30 optic, 4000K CCT AND, 98CRI , 3LSQCDR1MMS TRIM  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 989.0 lumens  
Efficiency: N/A  
Efficacy: 68.2 lumens/watt  
Spacing Criteria (0/90/45): 0.51 / 0.51 / 0.46  
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 14.5  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1320107  
CATALOG NUMBER: LDSQA3D13R309840DE010 3LSQCDR1MMS

### Luminous Intensity Polar Plot





TEST NUMBER: P1320107

CATALOG NUMBER: LDSQA3D13R309840DE010 3LSQCDR1MMS

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	115	113	111	110	113	111	109	108	107	106	105	103	102	101	100	99	99	99	99	99	97
2	112	108	105	103	109	106	104	102	103	101	99	100	99	97	98	96	95	95	94	94	94
3	108	104	100	97	106	102	99	97	100	97	95	98	95	94	95	94	92	92	92	92	91
4	105	100	96	93	103	99	95	92	97	94	91	95	92	90	93	91	89	89	89	89	88
5	102	96	92	89	101	95	92	89	94	91	88	92	90	87	91	89	87	87	87	87	86
6	99	93	89	86	98	92	89	86	91	88	85	90	87	85	89	86	84	84	84	84	83
7	96	90	86	83	95	90	86	83	89	85	83	87	85	82	87	84	82	82	82	82	81
8	94	88	84	81	93	87	83	81	86	83	80	85	82	80	84	82	80	80	80	80	79
9	91	85	81	78	91	85	81	78	84	80	78	83	80	78	82	80	78	78	78	78	77
10	89	83	79	76	88	82	79	76	82	78	76	81	78	76	80	78	76	76	76	76	75

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	660095	660095	660095
5°	644014	644810	648388
10°	550031	547478	544242
15°	339426	335450	336680
20°	128293	128989	128843
25°	39469	43269	41217
30°	15909	20185	16526
35°	4688	8578	4857
40°	1911	3462	1911
45°	365	1120	365
50°	0	214	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 45°  
 Vertical Angle: 45°  
 Luminance: 1120 cd/sqm



TEST NUMBER: P1320107  
 CATALOG NUMBER: LDSQA3D13R309840DE010 3LSQCDR1MMS

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	338.1	34.2
10°-20°	500.5	50.6
20°-30°	124.1	12.6
30°-40°	23.3	2.4
40°-50°	2.9	0.3
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	962.7	97.3
0°-40°	986.0	99.7
0°-60°	989.0	100.0
0°-90°	989.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	989.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	3833	3833	3833	3833	3833	
5°	3725	3724	3730	3736	3750	338
15°	1904	1885	1881	1896	1888	503
25°	208	222	228	227	217	120
35°	22	29	41	30	23	19
45°	2	2	5	3	2	2
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P1320107

CATALOG NUMBER: LDSQA3D13R309840DE010 3LSQCDR1MMS

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	3832.8	3832.8	3832.8	3832.8	3832.8
1°	3834.4	3831.3	3831.3	3826.7	3835.1
2°	3820.5	3817.5	3822.8	3819.0	3829.8
3°	3799.8	3795.9	3803.6	3805.9	3811.3
4°	3769.0	3765.9	3774.4	3779.0	3793.6
5°	3725.2	3723.6	3729.8	3735.9	3750.5
6°	3665.2	3662.9	3666.7	3674.4	3683.6
7°	3578.2	3573.6	3576.7	3578.2	3580.5
8°	3468.2	3461.3	3457.5	3465.9	3470.6
9°	3326.7	3319.0	3310.6	3307.5	3318.3
10°	3145.2	3133.7	3130.6	3122.9	3112.1
11°	2934.4	2925.2	2922.9	2909.1	2902.9
12°	2692.9	2688.3	2693.7	2685.2	2682.1
13°	2461.4	2432.2	2428.3	2412.2	2403.7
14°	2187.6	2160.6	2159.9	2151.4	2162.9
15°	1903.7	1885.3	1881.4	1896.0	1888.3
17.5°	1213.8	1226.1	1223.0	1215.3	1202.2
20°	700.0	691.5	703.8	706.9	703.0
22.5°	373.1	376.1	378.4	387.7	393.8
25°	207.7	221.5	227.7	226.9	216.9
27.5°	129.2	137.7	149.2	141.5	133.1
30°	80.0	86.9	101.5	87.7	83.1
32.5°	43.1	54.6	65.4	54.6	44.6
35°	22.3	29.2	40.8	30.0	23.1
37.5°	14.6	16.9	26.2	16.9	14.6
40°	8.5	10.8	15.4	10.8	8.5
42.5°	3.8	6.2	8.5	6.2	3.8
45°	1.5	2.3	4.6	3.1	1.5
47.5°	0.0	0.8	2.3	0.8	0.0
50°	0.0	0.0	0.8	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1320107  
CATALOG NUMBER: LDSQA3D13R309840DE010 3LSQCDR1MMS

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)