

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1319686

Luminaire Tested: LDSQA3D02R359840DE010 3LSQCDR1MMS

Issue Date: 1/29/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1319686  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-25)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LDSQA3D02R359840DE010 3LSQCDR1MMS  
Description: 3in Adjustable LED luminaire with, R35 optic, 4000K CCT AND, 98CRI , 3LSQCDR1MMS TRIM  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 239.0 lumens  
Efficiency: N/A  
Efficacy: 66.4 lumens/watt  
Spacing Criteria (0/90/45): 0.57 / 0.58 / 0.52  
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 3.6  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1319686  
CATALOG NUMBER: LDSQA3D02R359840DE010 3LSQCDR1MMS

### Luminous Intensity Polar Plot



— 0°-180°    - - 45°-225°    - - - 90°-270°



TEST NUMBER: P1319686

CATALOG NUMBER: LDSQA3D02R359840DE010 3LSQCDR1MMS

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	115	113	111	109	113	111	109	107	107	105	104	103	102	101	100	99	98	98	96	96	96
2	111	107	104	102	109	106	103	100	102	100	98	100	98	96	97	96	94	94	93	93	93
3	107	102	99	96	105	101	98	95	99	96	94	96	94	92	94	92	91	91	89	89	89
4	104	98	94	91	102	97	93	90	95	92	89	93	91	88	92	89	87	87	86	86	86
5	100	94	90	87	99	93	90	87	92	88	86	90	87	85	89	86	84	84	83	83	83
6	97	91	86	83	96	90	86	83	89	85	83	88	84	82	86	84	82	82	80	80	80
7	94	88	83	80	93	87	83	80	86	82	80	85	82	79	84	81	79	79	78	78	78
8	91	85	80	77	91	84	80	77	83	80	77	82	79	77	81	79	76	76	75	75	75
9	89	82	78	75	88	81	77	75	81	77	74	80	77	74	79	76	74	74	73	73	73
10	86	79	75	72	85	79	75	72	78	75	72	78	74	72	77	74	72	72	71	71	71

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	123621	123621	123621
5°	119875	120722	121379
10°	109544	111853	113777
15°	78772	82213	82891
20°	40101	42117	42227
25°	15221	15544	15107
30°	5906	6861	5767
35°	2039	3175	1913
40°	674	1237	629
45°	49	414	49
50°	0	54	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 45°

Vertical Angle: 45°

Luminance: 414 cd/sqm



TEST NUMBER: P1319686

CATALOG NUMBER: LDSQA3D02R359840DE010 3LSQCDR1MMS

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	65.0	27.2
10°-20°	121.1	50.7
20°-30°	43.5	18.2
30°-40°	8.5	3.6
40°-50°	1.0	0.4
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
<hr/>		
0°-30°	229.6	96.0
0°-40°	238.1	99.6
0°-60°	239.0	100.0
0°-90°	239.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	239.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	718	718	718	718	718	
5°	693	695	698	702	702	64
15°	442	449	461	464	465	117
25°	80	81	82	81	80	42
35°	10	11	15	11	9	7
45°	0	1	2	1	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P1319686

CATALOG NUMBER: LDSQA3D02R359840DE010 3LSQCDR1MMS

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	717.8	717.8	717.8	717.8	717.8
1°	715.7	716.7	716.9	718.2	716.7
2°	712.7	713.3	714.0	715.2	714.4
3°	706.8	708.0	709.7	711.2	711.2
4°	700.6	702.1	704.2	706.8	706.7
5°	693.4	695.3	698.3	701.5	702.1
6°	684.3	686.6	691.5	696.1	696.8
7°	674.7	678.1	682.8	689.4	691.1
8°	663.3	666.0	672.8	680.5	682.4
9°	646.6	650.6	659.3	666.5	667.7
10°	626.4	629.2	639.6	647.2	650.6
11°	600.3	604.4	614.7	622.4	624.7
12°	566.9	573.0	584.9	590.6	592.5
13°	531.0	536.1	545.4	552.4	553.9
14°	490.5	495.4	505.0	510.7	509.4
15°	441.8	449.2	461.1	464.3	464.9
17.5°	326.4	331.1	341.7	346.8	350.4
20°	218.8	223.4	229.8	233.2	230.4
22.5°	133.1	136.9	140.3	140.1	139.1
25°	80.1	80.8	81.8	81.2	79.5
27.5°	46.8	48.8	51.7	49.8	46.9
30°	29.7	31.4	34.5	31.2	29.0
32.5°	15.7	19.9	23.1	18.7	16.5
35°	9.7	11.0	15.1	11.2	9.1
37.5°	5.9	6.8	9.5	6.6	5.3
40°	3.0	4.4	5.5	4.0	2.8
42.5°	0.9	2.1	3.0	1.9	0.9
45°	0.2	0.6	1.7	0.6	0.2
47.5°	0.0	0.0	0.8	0.2	0.0
50°	0.0	0.0	0.2	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1319686  
CATALOG NUMBER: LDSQA3D02R359840DE010 3LSQCDR1MMS

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)